

EER Cores (9595354202)



Part Number: 9595354202

95 EER CORE SET

EER cores, similar to ETD cores, have been designed to make optimum use of a given volume of ferrite material for maximum throughput power. The structure, which includes a round center post, approaches a nearly uniform cross-sectional area throughout the core and provides a winding area that minimizes winding losses.

EER cores can be supplied with the center post gapped to a mechanical dimension or an A_L value.

Weight indicated is per pair or set.

Weight: 46 (g)

Dim	mm	mm tol	nominal inch	inch misc.
A	35	± 0.65	1.378	—
B	21	± 0.20	0.827	—
C	11.3	± 0.30	0.445	—
D	15	± 0.20	0.591	—
E	25.3	min	0.997	min
F	11.3	± 0.30	0.445	—





Chart Legend

$\Sigma l / A$: Core Constant, l_e : Effective Path Length, A_e : Effective Cross- Sectional Area, V_e : Effective Core Volume

A_L : Inductance Factor 

Explanation of Part Numbers: Digits 1 & 2 = product class and 3 & 4 = material grade.

Electrical Properties	
A_L (nH)	3200 ±25%
A_e (cm ²)	1.11
$\Sigma l / A$ (cm ⁻¹)	8.2
l_e (cm)	9.11
V_e (cm ³)	10.14
A_{min} (cm ²)	1

A_L value is measured at 1 kHz, $B < 10$ gauss.