

Antenna YG0043AA Datasheet

Antenna Services

Version: 1.3

Date: 2022-02-10

Status: Released





At Quectel, our aim is to provide timely and comprehensive services to our customers. If you require any assistance, please contact our headquarters:

Quectel Wireless Solutions Co., Ltd.

Building 5, Shanghai Business Park Phase III (Area B), No.1016 Tianlin Road, Minhang District, Shanghai 200233, China

Tel: +86 21 5108 6236 Email: <u>info@quectel.com</u>

Or our local offices. For more information, please visit:

http://www.quectel.com/support/sales.htm.

For technical support, or to report documentation errors, please visit:

http://www.quectel.com/support/technical.htm.

Or email us at: support@quectel.com.

Legal Notices

We offer information as a service to you. The provided information is based on your requirements and we make every effort to ensure its quality. You agree that you are responsible for using independent analysis and evaluation in designing intended products, and we provide reference designs for illustrative purposes only. Before using any hardware, software or service guided by this document, please read this notice carefully. Even though we employ commercially reasonable efforts to provide the best possible experience, you hereby acknowledge and agree that this document and related services hereunder are provided to you on an "as available" basis. We may revise or restate this document from time to time at our sole discretion without any prior notice to you.

Use and Disclosure Restrictions

License Agreements

Documents and information provided by us shall be kept confidential, unless specific permission is granted. They shall not be accessed or used for any purpose except as expressly provided herein.

Copyright

Our and third-party products hereunder may contain copyrighted material. Such copyrighted material shall not be copied, reproduced, distributed, merged, published, translated, or modified without prior written consent. We and the third party have exclusive rights over copyrighted material. No license shall be granted or conveyed under any patents, copyrights, trademarks, or service mark rights. To avoid ambiguities, purchasing in any form cannot be deemed as granting a license other than the normal non-exclusive, royalty-free license to use the material. We reserve the right to take legal action for noncompliance with abovementioned requirements, unauthorized use, or other illegal or malicious use of the material.

Antenna Datasheet 1 / 14



Trademarks

Except as otherwise set forth herein, nothing in this document shall be construed as conferring any rights to use any trademark, trade name or name, abbreviation, or counterfeit product thereof owned by Quectel or any third party in advertising, publicity, or other aspects.

Third-Party Rights

This document may refer to hardware, software and/or documentation owned by one or more third parties ("third-party materials"). Use of such third-party materials shall be governed by all restrictions and obligations applicable thereto.

We make no warranty or representation, either express or implied, regarding the third-party materials, including but not limited to any implied or statutory, warranties of merchantability or fitness for a particular purpose, quiet enjoyment, system integration, information accuracy, and non-infringement of any third-party intellectual property rights with regard to the licensed technology or use thereof. Nothing herein constitutes a representation or warranty by us to either develop, enhance, modify, distribute, market, sell, offer for sale, or otherwise maintain production of any our products or any other hardware, software, device, tool, information, or product. We moreover disclaim any and all warranties arising from the course of dealing or usage of trade.

Privacy Policy

To implement module functionality, certain device data are uploaded to Quectel's or third-party's servers, including carriers, chipset suppliers or customer-designated servers. Quectel, strictly abiding by the relevant laws and regulations, shall retain, use, disclose or otherwise process relevant data for the purpose of performing the service only or as permitted by applicable laws. Before data interaction with third parties, please be informed of their privacy and data security policy.

Disclaimer

- a) We acknowledge no liability for any injury or damage arising from the reliance upon the information.
- b) We shall bear no liability resulting from any inaccuracies or omissions, or from the use of the information contained herein.
- c) While we have made every effort to ensure that the functions and features under development are free from errors, it is possible that they could contain errors, inaccuracies, and omissions. Unless otherwise provided by valid agreement, we make no warranties of any kind, either implied or express, and exclude all liability for any loss or damage suffered in connection with the use of features and functions under development, to the maximum extent permitted by law, regardless of whether such loss or damage may have been foreseeable.
- d) We are not responsible for the accessibility, safety, accuracy, availability, legality, or completeness of information, advertising, commercial offers, products, services, and materials on third-party websites and third-party resources.

Copyright © Quectel Wireless Solutions Co., Ltd. 2022. All rights reserved.

Antenna Datasheet 2 / 14



About the Document

Revision History

Version	Date	Author	Note
-	2020-12-28	Kenny YIN/ Xiaodong YANG	Creation of the document
1.0	2020-12-28	Kenny YIN/ Xiaodong YANG	First official release
1.1	2021-07-13	Aria CHU	Added Chapters 3 and 7.
1.2	2021-12-03	Aria CHU	Updated the product description in Chapter 1.
1.3	2022-02-10	Xiaodong YANG	Updated the data (Chapter 2) and the frequency (Chapter 4).

Antenna_Datasheet 3 / 14



Contents

Ab	out the	e Document	3
1	Prod	uct Description	5
2	Prod	uct Features	5
3	GNS	S Frequency Band Checklist	6
4	Prod	uct Specifications	8
5	Over	all Performance	9
	5.1.	Test Environment	9
	5.2.	VSWR	10
	5.3.	Efficiency	11
	5.4.	Gain	11
	5.5.	Radiation Pattern	12
6	Prod	uct Size	13
7	РСВ	Footprint Recommendation	14



1 Product Description

This Quectel GNSS antenna adopts a diversity of forms to guarantee the most suitable polarization type. Quectel's positioning products support single-band or multi-band operation modes to meet various high-precision positioning requirements of customers' products. Quectel also provides both passive and active antennas to satisfy the customer demand for high gain. Such antenna supports different installation or connection methods such as pin mount, surface mount, magnetic mount, internal cable, and external SMA. Customized connector type and cable length are provided according to requirements.

2 Product Features

- GNSS L1
- High efficiency
- Excellent performance



Antenna_Datasheet 5 / 14




3 GNSS Frequency Band Checklist

GNSS Frequency Bands (MHz)					
	L1	L2	L5		
GPS	Centre 1575.42	Centre 1227.6	Centre 1176.45		
	(1565–1586)	(1217–1238)	(1164–1189)		
	•	-	-		
	G1/L10C/L10F	G2/L2OC/L2OF	G3/L3OC		
GLONAS S	Centre 1601	Centre 1248.06	Centre 1202.025		
3	(1595–1606)	(1241–1255)	(1189–1213)		
	•	-	-		
	E1	E5a	E5b	E6	
GALILEO	Centre 1575.42	Centre 1176.45	Centre 1207.14	Centre 1278.75	
	(1563–1588)	(1166–1187)	(1197–1218)	(1258–1300)	
	•	-	-	-	
	B1I	B1C (BeiDou-3)	B2a/B2I	B2b	В3
BEIDOU	Centre 1561.098	Centre 1575.42	Centre 1176.45	Centre 1207.14	Centre 1268.52
	(1559–1564)	(1559–1592)	(1166–1187)	(1197–1217)	(1258–1279)
	•	•	-	-	-
	L1	L2C	L5	L6	
QZSS	Centre 1575.42	Centre 1227.6	Centre 1176.45	Centre 1278.75	
	(1573–1578)	(1226–1229)	(1166–1187)	(1257–1300)	
	•	-	-	-	
	L5				
IRNSS	Centre 1176.45				
	(1164–1189)				
	-				

Antenna_Datasheet 6 / 14





Antenna_Datasheet 7 / 14



4 Product Specifications

• This antenna is tested on a 100 mm x 80 mm PCB.

Passive Electrical Specifications			
Frequency	GPS L1: 1575.42 MHz BD B1: 1561.098 MHz GLONASS L1: 1602 MHz GALILEO E1:1575.42MHz		
Input Impendence	50 Ω		
VSWR	≤ 2.53		
Gain	< 3.0 dBi		
Polarization Type	RHCP		
Mechanical Specifications			
Antenna Size	15 mm × 15 mm × 4 mm		
Casing	Ceramic		
Working Temperature	-40 °C to +85 °C		
Radome Color	-		

Antenna_Datasheet 8 / 14



5 Overall Performance

5.1. Test Environment


- KEYSIGHT ENA Network Analyzer E5063A 100 kHz 8.5 GHz
- RayZone® 2800 Chamber 5G (FR1) SISO/MIMO, 600 MHz 8.5 GHz



Antenna_Datasheet 9 / 14



5.2. VSWR




Frequency (MHz)	1561	1575	1602
VSWR	1.46	1.59	2.53

Antenna_Datasheet 10 / 14




5.3. Efficiency



Frequency (MHz)	1561	1575	1602
Efficiency (%)	49.89	44.46	41.21

5.4. Gain





Frequency (MHz)	1561	1575	1602
Gain (dBi)	2.87	2.88	2.04

Antenna_Datasheet 11 / 14



5.5. Radiation Pattern







Antenna_Datasheet 12 / 14



6 Product Size






RoHS

BOTTOM

Antenna_Datasheet 13 / 14



7 PCB Footprint Recommendation



Antenna_Datasheet 14 / 14