



TEL: 973-328-3200 FAX: 973-328-3130

[Home](#) > [Tubing](#) > [Non-Shrinkable Tubing](#) > #DTT500 DAFLON Thin Wall PTFE Tubing, MIL-I-22129, AMS 3655

#DTT500 DAFLON Thin Wall PTFE Tubing, MIL-I-22129, AMS 3655

Description: Daflon 500 tubing is extruded from PTFE resin and is unmatched by any other tubing for use in applications for hi-frequencies and hi-temperatures. Rated for continuous operation of 250°C, it retains its toughness and flexibility throughout. It has high resistance to fatigue and stress, with superior dielectric strength at high frequencies. It will not shrink back during soldering operation. Daflon tubing is flexible and non-flammable, it permits miniaturization of design and compactness and has the lowest coefficient of friction. In addition, it is inert to all fungus growth.

It conforms to MIL-I-22129C Spec. AMS 3654, AMS 3655, ASTM-D-3295.

This series is RoHS compliant.

DAFLON Catalog No.	Size	Nom. I.D.		Wall Thickness		Standard Spool or Coil (Note 1)
		IN.	MM.	IN.	MM.	
DTT500-30	30	0.012	0.30	0.009	0.23	100', 500', 1000'
DTT500-28	28	0.015	0.38	0.009	0.23	100', 500', 1000'
DTT500-26	26	0.018	0.46	0.010	0.25	100', 500', 1000'
DTT500-24	24	0.022	0.56	0.010	0.25	25', 50', 100', 500', 1000'
DTT500-22	22	0.027	0.69	0.010	0.25	25', 50', 100', 500', 1000'
DTT500-20	20	0.034	0.86	0.012	0.30	25', 50', 100', 500', 1000'
DTT500-19	19	0.038	0.96	0.012	0.30	100', 1000'
DTT500-18	18	0.042	1.07	0.012	0.30	25', 50', 100', 500', 1000'
DTT500-17	17	0.047	1.19	0.012	0.30	100', 1000'
DTT500-16	16	0.053	1.35	0.012	0.30	25', 50', 100', 500', 1000'
DTT500-15	15	0.059	1.50	0.012	0.30	100', 1000'
DTT500-14	14	0.066	1.68	0.012	0.30	25', 50', 100', 500'
DTT500-13	13	0.076	1.93	0.012	0.30	100', 500'
DTT500-12	12	0.085	2.16	0.012	0.30	25', 50', 100', 500'
DTT500-11	11	0.095	2.41	0.012	0.30	100', 500'
DTT500-10	10	0.106	2.69	0.012	0.30	25', 50', 100', 500'
DTT500-9	9	0.118	3.00	0.015	0.38	100', 500'
DTT500-8	8	0.133	3.38	0.015	0.38	25', 50', 100', 500', 1000**
DTT500-7	7	0.148	3.76	0.015	0.38	100, 500, 1000**
DTT500-6	6	0.166	4.22	0.015	0.38	25', 50', 100', 1000**
DTT500-5	5	0.186	4.72	0.015	0.38	100', 1000**
DTT500-4	4	0.208	5.28	0.015	0.38	50', 100', 1000**
DTT500-3	3	0.234	5.94	0.015	0.38	100', 1000**
DTT500-2	2	0.263	6.68	0.015	0.38	25', 50', 100', 1000**
DTT500-1	1	0.294	7.47	0.015	0.38	100', 1000**
DTT500-0	0	0.330	8.38	0.015	0.38	25', 50', 100', 1000**
DTT500-1/8	1/8"	0.125	3.18	0.015	0.38	50', 100'
DTT500-1/4	1/4"	0.250	6.35	0.015	0.38	50', 100', 1000**
DTT500-5/16	5/16"	0.312	7.93	0.015	0.38	50', 100', 1000**
DTT500-3/8**	3/8"	0.390	9.91	0.015	0.38	50', 100'
DTT500-7/16**	7/16"	0.453	11.51	0.018	0.46	50', 100'
DTT500-1/2**	1/2"	0.515	13.08	0.018	0.46	25', 50', 100'
DTT500-5/8**	5/8"	0.640	16.26	0.020	0.51	25', 50', 100'
DTT500-3/4**	3/4"	0.765	19.43	0.025	0.64	25, 50, 100'

* Random lengths in coils. ** Random Straight lengths.

Stock Colors: Natural. Call for Red, Black, Yellow, Blue, Brown, Green, Orange, Gray, Violet, White. If no color is specified, Natural will be supplied.

Nos. DTT500-3/8 thru 1" available from stock in Natural.

Additional colors, sizes made to order.

Note 1: Please call to order quantities less than 100'.

Test	ASTM Method	Result
Tensile Strength, 73°F	D638-52T	1500-300 Lb/Square Inch
Elongation, 73°F	D638-52T	100-200%
Deformation Under Load-122°F		
1200 Lb/SQ IN., 24hrs	D621-51	4-8%
2000 Lb/SQ IN., 24hrs	D621-51	25%
Hardness Durometer	D676-49T	D50-D65
Heat Distortion Temp, 6 LB/SQ IN.	D648B-45T	250° C

Dielectric Strength .080"	D149-44	400-500 V/Mil
Surface Arc-Resistance	D495-48T	SEC.
Volume Resistivity	D257-52T	10 ¹⁵ Ohms-CM
Surface Resistivity, 100%RH	D257-52T	3.6X10 ⁸ MegOhms
Dielectric Constant, 60 to 10⁸Cyc	D150-54T	2.00
Power Factor, 60 to 10⁸ Cycles	D150-54T	0.0003
Specific Gravity	D792-50	2.1-2.2

PTFE light wall tubing (DTT501 series) and standard wall tubing (DTT550 series) are available.

© 2015 Daburn Electronics & Cable E-Commerce Web Site