

**SAIS-4-IDC M8 SMALL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female sockets for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M8 round plug-in connectors are particularly suited to applications where space is limited.

The IDC is simple and quick to assemble since this technology allows the conductor to be inserted directly into the terminal point, without crimping or having to strip the insulation. It also has excellent functional security.

**General ordering data**

Version	Field attachable connector, M8, pin, straight
Order No.	<a href="#">1784060001</a>
Type	SAIS-4-IDC M8 SMALL
GTIN (EAN)	4032248429912
Qty.	1 pc(s).

## SAIS-4-IDC M8 SMALL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight 7 g

## Technical data customisable plug-in connectors

Cable diameter	3.2...5.4 mm	Cable diameter, max.	5.4 mm
Cable diameter, min.	3.2 mm	Coding	none
Conductor cross-section, max.	0.34 mm <sup>2</sup>	Conductor cross-section, min.	0.14 mm <sup>2</sup>
Connection cross-section, max.	0.34 mm <sup>2</sup>	Connection cross-section, min.	0.14 mm <sup>2</sup>
Contact surface	tinned	Housing main material	CuZn
Insulation strength	10 <sup>8</sup> Ω	Number of poles	4
Plugging cycles	≥ 50	Pollution severity	3
Protection degree	IP67	Rated current	4 A
Rated voltage	32 V	Shield connection	No
Temperature range of housing	-25...+85 °C	Threaded ring material	Diecast zinc
Type of connection	Insulation displacement connection		

## Standards

Connector standard IEC 61076-2-104

## Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27440102

## Approvals

ROHS Conform

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>