### CH20M22 S PSCSC LGY 2018



### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

### **Product image**





# Superior efficiency, flexibility and design - the "standard tailor-made fit"

When selecting a housing design, flexibility is a key factor. Other important criteria are: scalability, customised design, innovative functionality and cost efficiency. You need a choice which offers the maximum performance with the minimum overhead.

The CH20M22 modular electronics housing is the standard format from amongst the different housing widths. It has the optimal width for most typical electronics applications.

The entire system is characterized by excellence: outstanding scalability and flexibility, a high security level, innovative application functionality and a variety of practical details.

- Quicker installation with features such as "Wire ready" the universal multi-tool screw head
- **User-friendly operations:** with clear and permanent labelling and extra marking possibilities, integrated release clip or transparent cover
- Maximum interference immunity with ESDcompliant construction featuring deeply overlapping module joint edges made from high-performance plastic
- **High operational reliability** with the unique Auto-Set coding system and featuring double-sided touch protection on the pin header and socket blocks

CH20M - a compact name for the most flexible system available on the market. It doesn't just stand for "Component Housing IP20 Modular". CH20M also stands for efficiency and innovation throughout design, production and use.

#### **General ordering data**

Version	Modular housing, OMNIMATE Housing - series	
	CH20M Light Grey, Side element, Width: 22.5 mm	
Order No.	<u>1432860000</u>	
Туре	CH20M22 S PSCSC LGY 2018	
GTIN (EAN)	4050118237603	
Qty.	10 pc(s).	
Information regarding whole assembly, see referenced articles	<u>1104450000</u>	

## CH20M22 S PSCSC LGY 2018



### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## **Technical data**

Depth	105.5 mm	Depth (inches)	4.154 inch
Height	22.8 mm	Height (inches)	0.898 inch
Width	22.5 mm	Width (inches)	0.886 inch
Net weight	9.3 g		
Temperatures			
Operating temperature range	-40 °C120 °C	Humidity	5 - 93% rel. humidity, Tu = 40°C, no condensation
Material data			
Comparative Tracking Index (CTI)	600 ≤ CTI	Insulating material	PA 66 GF 30
Insulating material group	1	UL 94 flammability rating	V-0
General data			
Colour	Light Grey	Colour chart (similar)	RAL 7035
Encapsulation option	No	Protection degree	IP20 in installed state
Cut out as preperation for functional integrated	port No	Number of connection levels	1
Number of poles, max.	4	Number of slots for female plugs	1
Number of ventilation openings	2		
Classifications			
ETIM 6.0	EC001031	ETIM 7.0	EC001031
	EC001031	ETIM 7.0	EC001031
ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 8.0 ECLASS 9.0	EC001031 27-18-27-90	ETIM 9.0 ECLASS 9.1	EC001031 27-18-27-90
ETIM 8.0 ECLASS 9.0 ECLASS 10.0	EC001031	ETIM 9.0	EC001031
ETIM 8.0 ECLASS 9.0 ECLASS 10.0 ECLASS 12.0	EC001031 27-18-27-90 27-18-27-92	ETIM 9.0 ECLASS 9.1 ECLASS 11.0	EC001031 27-18-27-90 27-18-27-92
ETIM 8.0 ECLASS 9.0 ECLASS 10.0 ECLASS 12.0	EC001031 27-18-27-90 27-18-27-92	ETIM 9.0 ECLASS 9.1 ECLASS 11.0	EC001031 27-18-27-90 27-18-27-92
ETIM 8.0 ECLASS 9.0 ECLASS 10.0 ECLASS 12.0 Approvals ROHS	EC001031 27-18-27-90 27-18-27-92 27-18-27-92	ETIM 9.0 ECLASS 9.1 ECLASS 11.0	EC001031 27-18-27-90 27-18-27-92
ECLASS 10.0 ECLASS 12.0 Approvals	EC001031 27-18-27-90 27-18-27-92 27-18-27-92	ETIM 9.0 ECLASS 9.1 ECLASS 11.0	EC001031 27-18-27-90 27-18-27-92

## CH20M22 S PSCSC LGY 2018

## Drawings

### **Product image**





#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

### Product image



### **Dimensioned drawing**

