



Micro Commercial Components 20736 Marilla Street Chatsworth CA 91311

Phone: (818) 701-4933 Fax: (818) 701-4939

MB22S THRU MB210S

Features

- High Temperature Soldering Guaranteed:260 ℃/10 Second
- Saves Space On Printed Circuit Board
- Halogen free available upon request by adding suffix "-HF"
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Lead Free Finish/Rohs Compliant (Note1) ("P"Suffix designates Compliant. See ordering information)

Mechanical Data

- Teminals: Plated leads Solderable per MIL-STD-750, Method 2026
- Moisture Sensitiviy:Level 1 per J-STD-020C


MCC Part Number	Device Marking	Maximum Recurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
MB22S	MB22S	20V	14V	20V
MB24S	MB24S	40V	28V	40V
MB26S	MB26S	60V	42V	60V
MB28S	MB28S	80V	56V	80V
MB210S	MB210S	100V	70V	100V

Electrical Characteristics @ 25°C Unless Otherwise Specified

iocu icai onai actoristica 🤟 20-0 onica ottici miac opecinica					
Average Forward Current	I _{F(AV)}	2A			
Peak Forward Surge Current	I _{FSM}	50A	8.3ms, half sine		
Maximum Instantaneous Forward Voltage MB22S~MB24S MB26S MB28S~MB210S	V _F	0.50V 0.70V 0.85V	I _{FM} = 2A; T _A = 25 ^o C		
Maximum DC Reverse Current At Rated DC Blocking Voltage	I _R	0.5mA 20mA	$T_A = 25^{\circ}C$ $T_A = 100^{\circ}C$		
Typical Thermal Resistance	$R_{ ext{thJA}}$ $R_{ ext{thJL}}$	85°C/W 20°C/W	per leg		
Operating Junction and Storage Temperature Range	T _J T _{STG}	-55 to+150 °C			

Notes:1.High Temperature Solder Exemption Applied, see EU Directive Annex Notes 7a

2 Amp Surface Mount Schottky Bridge Rectifier 20 to 100 Volts



DIMENSIONS						
	INC HES		ММ			
DIM	MIN	MAX	MIN	MAX	NOTE	
Α	.252	.276	6.40	7.00		
В	.095	.106	2.41	2.70		
С	.142	.165	3.60	4.20		
D	.179	.195	4.55	4.95		
Е	.019	.031	0.50	0.80		
F	.090	.106	2.30	2.70		
G	.002	.008	0.05	0.20		
Н	.027	.043	0.70	1.10		
J	.058	.062	1.47	1.57		
K	.195	.205	4.95	5.21		
М	.039	.049	0.99	1.24		
N	.006	.016	0.15	0.41		

Mounting Pad Layout



MB22S thru MB210S

RATING AND CHARACTERISTIC CURVES




Fig. 2 - Maximum Non-Repetitive Peak
Forward Surge Current

(V) 100

By 100


Number of Cycles at 60 Hz


Fig. 3 - Typical Instantaneour Forward Characteristics


10
pulse width =300 µS
1% duty cycle, T j=25 °C

MB22S-MB24S

0.01
0 0.2 0.4 0.6 0.8 1.0
Instantaneous Forward Voltage (Volts)









Ordering Information

Device	Packing
(Part Number)-TP	Tape&Reel3Kpcs/Reel

Note: Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.