
SPECIFICATIONS

VALUES	UNITS
110	Vac/Vdc
30 ~ 120	Vac/Vdc
17	mA
98	dBA
2,800 ± 500	Hz
CONTINUOUS	0 pulse/sec
-20 ~ +60	°C
-30 ~ +70	S°
ABS	-
Ni PLATED	
BRASS	-
43	grams
	110 30 ~ 120 17 98 2,800 ± 500 CONTINUOUS -20 ~ +60 -30 ~ +70 ABS Ni PLATED BRASS

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.

©2003, Projects Unlimited Inc.

	1	
REVISION HISTORY		
LTR DESCRIPTION	DATE	APPROVED
- RELEASED FROM ENGINEERING	3/22/2000	6
A REVISED TONE OR PULSE RATE	1/29/2007	
B REVISED OPERATING VOLTAGE RANGE	11/30/200	
C REVISED TO INVETOR 3-D DRAWING TEMPLATE	3/7/2008	
D REVISED OPERATING VOLTAGE RANGE	4/27/2012	
E REVISED RATED VOLTAGE	2/24/2020	0 M.V.
Image: wide interview Designed by Date Checked by Date Approx	ved by Date	Drawn Date
	P. 3/22/20	06 3/7/2008
SI7F T.G. 3/22/2006 B.R. 3/22/2006 E.		
A3 PUI AI-4328	-P-C120	
A3 FILE SIZE T.G. 3/22/2006 B.R. 3/22/2006 E.I A32 A32 A32 A32 A32 A32 A32 A32 A32 A32		DD-R Edition Sheet
RE IN RS, SIZE T.G. 3/22/2006 B.R. 3/22/2006 E.T. AI-4328-		



- 2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
- 3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

