

5

4

3

2

1

D

D



Description: TNC crimp plug RG8X  
 Part No: CPMCTNC17  
 Application: For RG8X Cable  
 Crimp Tool: 24-9959P  
 Impedance: 50 Ohms  
 Frequency Range: 0-11 GHz  
 Material:  
 Body Zinc Nickel plated  
 Contact Brass Ni/Au plated  
 Insulator PTFE  
 Crimp sleeve Brass Nickel plated  
 Coupling nut Zinc Nickel plated

RoHS Compliance: Yes  
 Technical Detail: Refer to Emerson Document P/N 28-0000

DRAWING NO.

CPMCTNC17-CUST

REVISIONS




01	OFFICAL RELEASE					
	08-17-09	J	T	T		
02	RELEASE FOR SUPPLIER ALTER					
	07-27-11	Y	Y	M		<i>Lin</i>

C

C

B

B



**DIM OUTLINE**

受控 CONTROLLED DOCUMENT				
编号 P/N	CPMCTNC17-CUST	版本 Rev	02	日期 Rel'd Date
				Aug4,11

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS	mm	YUGE HU	07-27-11
X	± 0.5	CHECKED BY	DATE
X.X	± 0.2	YUGE HU	07-27-11
X.XX	± 0.1	APPROVED BY	DATE
ANGLES	± 0.5°	LIN MA	07-27-11
		U/M	mm

CUSTOMER COPY



TITLE  
**TNC CRIMP PLUG RG8X**

THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.

SHEET	DRAWING NO.	SIZE
1 OF 1	CPMCTNC17-CUST	A

5

4

3

2

1

A

A