# **EVERLIGHT**

# DATASHEET

5mm Photodiode PD1503-3B/L2

# Features

- Fast response time
- High photo sensitivity
- Small junction capacitance
- Pb free
- The product itself will remain within RoHS compliant version

# Description

• PD1503-3B/L2 is a high speed and high sensitive PIN photodiode in a standard 5Φ plastic package. Due to its black epoxy the device is sensitive to infrared radiation

# **Applications**

- High speed photo detector
- Security system
- Camera

# **Device Selection Guide**

Chip Materials	Lens Color
Silicon	Black

# Absolute Maximum Ratings (Ta=25℃)


Parameter	Symbol	Rating	Unit
Reverse Voltage	V <sub>R</sub>	32	V
Operating Temperature	T <sub>opr</sub>	-40 ~ +85	°C
Storage Temperature	T <sub>stg</sub>	-40 ~ +100	°C
Soldering Temperature	T <sub>sol</sub>	260	°C
Power Dissipation at (or below)	Pc	150	mW
$25^{\circ}$ C Free Air Temperature			




# Electro-Optical Characteristics (Ta=25°C)


Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Range Of Spectral Bandwidth	λ <sub>0.5</sub>	840		1100	nm	
Wavelength Of Peak Sensitivity	$\lambda_{P}$		940		nm	
Open-Circuit Voltage	V <sub>oc</sub>		0.44		V	Ee=5mW/cm <sup>2</sup> λp=940nm
Short- Circuit Current	I <sub>SC</sub>		16		μA	Ee=1mW/cm <sup>2</sup> λp=940nm
Reverse Light Current	ΙL	35	41		μA	Ee=1mW/cm <sup>2</sup> λp=940nm V <sub>R</sub> =5V
Reverse Dark Current	I <sub>D</sub>			30	nA	Ee=0mW/cm <sup>2</sup> V <sub>R</sub> =10V
Reverse Breakdown Voltage	V <sub>BR</sub>	32	170		V	Ee=0mW/cm <sup>2</sup> I <sub>R</sub> =100µA
Total Capacitance	C <sub>t</sub>		18	-	pF	Ee=0mW/cm <sup>2</sup> V <sub>R</sub> =5V f=1MHz
Rise Time/ Fall Time	t <sub>r/</sub> /t <sub>f</sub>		45/45		ns	V <sub>R</sub> =10V R <sub>L</sub> =100Ω
EVE						

# **Typical Electro-Optical Characteristics Curves**






# EVERLIGHT






# **Package Dimension**







### Label Form Specification



- CPN: Customer's Product Number
- P/N: Product Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Dom. Wavelength Rank
- REF: Forward Voltage Rank
- LOT No: Lot Number
- X: Month
- Reference: Identify Label Number

#### Packing Quantity Specification

1.500PCS/1Bag 5Bags/1Box 2.10Boxes/1Carton

#### Notes

### Lead Forming

- 1.
- During lead formation, the leads should be bent at a point at least 3mm from the base of the epoxy bulb.
- Lead forming should be done before soldering.
- Avoid stressing the LED package during leads forming. The stress to the base may damage the LED's characteristics or it may break the LEDs.
- Cut the LED lead frames at room temperature. Cutting the lead frames at high temperatures may cause failure of the LEDs.
- When mounting the LEDs onto a PCB, the PCB holes must be aligned exactly with the lead position of the LED. If the LEDs are mounted with stress at the leads, it causes deterioration of the epoxy resin and this will degrade the LEDs.

#### 2. Storage


The LEDs should be stored at 30°C or less and 70%RH or less after being shipped from Everlight and the storage life limits are 3 months. If the LEDs are stored for 3 months or more, they can be stored for a year in a sealed container with a nitrogen atmosphere and moisture absorbent material.

## DATASHEET 5mm Photodiode PD1503-3B/L2

- Please avoid rapid transitions in ambient temperature, especially, in high humidity environments where condensation can occur.
- 3. Soldering
  - Careful attention should be paid during soldering. When soldering, leave more then 3mm from solder joint to epoxy bulb, and soldering beyond the base of the tie bar is recommended.
  - Recommended soldering conditions:

Hand Soldering		DIP Soldering			
Temp. at tip of iron	300°C Max. (30W Max.)	Preheat temp.	100°C Max. (60 sec Max.)		
Soldering time	3 sec Max.	Bath temp. & time	260 Max., 5 sec Max		
Distance	3mm Min.(From solder joint to epoxy bulb)	Distance	3mm Min. (From solder		
	Joint to epoxy build)		joint to epoxy bulb)		

Recommended soldering profile



- Avoiding applying any stress to the lead frame while the LEDs are at high temperature particularly when soldering.
- Dip and hand soldering should not be done more than one time
- After soldering the LEDs, the epoxy bulb should be protected from mechanical shock or vibration until the LEDs return to room temperature.
- A rapid-rate process is not recommended for cooling the LEDs down from the peak temperature. Although the recommended soldering conditions are specified in the above table, dip or hand soldering at the lowest possible temperature is desirable for the LEDs.
- Wave soldering parameter must be set and maintain according to recommended temperature and dwell time in the solder wave.
- 4. Cleaning
  - When necessary, cleaning should occur only with isopropyl alcohol at room temperature for a duration of no more than one minute. Dry at room temperature before use.
  - Do not clean the LEDs by the ultrasonic. When it is absolutely necessary, the influence of ultrasonic cleaning on the LEDs

depends on factors such as ultrasonic power and the assembled condition. Ultrasonic cleaning shall be pre-qualified to ensure this will not cause damage to the LED

#### 5. Heat Management

- Heat management of LEDs must be taken into consideration during the design stage of LED application. The current should be de-rated appropriately by referring to the de-rating curve found in each product specification.
- The temperature surrounding the LED in the application should be controlled. Please refer to the data sheet de-rating curve.

## 6. ESD (Electrostatic Discharge)

- Electrostatic discharge (ESD) or surge current (EOS) can damage LEDs.
- An ESD wrist strap, ESD shoe strap or antistatic gloves must be worn whenever handling LEDs.
- All devices, equipment and machinery must be properly grounded.
- Use ion blower to neutralize the static charge which might have built up on surface of the LEDs plastic lens as a result of friction between LEDs during storage and handing.

# DISCLAIMER

- 1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
- 2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
- 3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
- 6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.