

QLPD01DXMB (PHOTO DIODE)





Product Outline:

QLPD01DXMB is an Photodiode in Black housing color. It's wide viewing angle makes it ideal for many different light curtain application. This Photodiode works well with our QLIR01DXGD

Features:

- Black resign
- 50° Viewing angle (± 10°)
- RoHS compliant
- Custom Bin available upon special request

Application:


- Access Control & Security
- Home & Building Automation
- Appliances & Tools
- Light curtain
- Elevator & Industrial Applications

Compliance and Certification:





Mechanical Property: (Dimension)



SING: 1. Cathode

2. Anode

Tolerance is ±0.25mm unless otherwise specified

ELEMENT APPEARANCE

Model No.	Material	Lighting Color	Resin Color
QLPD01DXMB	-	Non-Visible	Black

ABSOLUTE MAXIMUM RATINGS AT Ta= 25° C

Characteristic	Symbol	Rating	Unit
Operating temperature	Topr	-40 to +85	°C
Storage temperature	Tstg	-25 to +85	°C



ELECTRO-OPTICAL CHARACTERISTICS AT Ta=25°C

Characteristic	Symbol	Condition	Min.	Тур.	Max.	Unit
Open circuit voltage	V _{oc}	C⊤=2870K, Ee = 5mW/cm²		390		mV
Short circuit current	lsc	C⊤=2870K, Ee = 5mW/cm²		40		μA
Reverse dark current	ID	VR=10V , Ee=0 mW/cm ²		5	30	nA
Reverse Light current	١L	Ee= 0.5 mW/cm² λ p= 940 nm	48	56		μA
Rise Time	Tr	V_R =10V RL=1K Ω		50		Ns
Fall Time	Tf	V_{R} =10V RL=1K Ω		50		ns
Wavelength of the sensitivity	λρ		850		980	nm
Reverse Breakdown Voltage	V _{(BR)R}	I_R = 100µA, Ee = 0mW/cm ²	33	170		V
Total Capacitance	Ct	Vr = 5V, f = 1MHZ, Ee = 0mW/cm ²		11		pF
Viewing angle	20 1/2			50		Deg

*Radiant Intensity Measurement allowance is ±15% ** Forward voltage Measurement allowance is ±0.05V

*** Peak emission wavelength Measurement allowance is ±1nm

Reverse light current bin:


Ee=0.5mW/cm ² (mA)				
Color	Code name	Min.	Max.	
	1	48	56	
	2	56	70	
	3			
PD(µA)	4			
	5			
	6			

Measurement tolerance is +/- 15%





Characteristic Curves



ANGULAR DISPIACEMENT



Reliability test:

No	ltem	Condition	Time/Cycle	Criteria	Ac / Re	Sample size
1	Soldering Heat Test	260 ℃	5 sec	Open / Short	0 / 1	60 pcs
2	Thermal Shock	0 (5min) ℃ ~100 (5min) ℃	20 cycle	Open / Short	0 / 1	60 pcs
3	High Temp. Storage	100 ℃	1000 Hrs	Open / Short	0 / 1	60 pcs
4	Low Temp. Storage	-40 ℃	1000 Hrs	Open / Short	0 / 1	60 pcs
5	Temperature Cycle Test	-40 ~85 ℃	100 Cycles , 200Hrs	Open / Short	0 / 1	60 pcs
6	High Temp. High Humidity Test	60 , 90% RH $^\circ\!\!\!C$	1000 Hrs	Open / Short	0 / 1	60 pcs
7	DC Operation Life Test	IF=100mA	1000 Hrs	Power decay	≦30%	60 pcs

QLPD01DXMB V1.0

APPLICATION NOTES :

Static Electricity and Surge

Static electricity and surge damage LEDs. It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs. All devices, equipment and machinery must be electrically grounded.

Lead Forming

The leads should be bent at a point at least 3mm from the epoxy resin of the LEDs. Bending should be performed with the base firmly fixed by means of a jig or radio pliers.

Mounting Method

The leads should be formed so they are aligned exactly with the holes on the PC board. This will eliminate any stress on the LEDs.

Use LEDs with stoppers or resin spacer to accurately position the LEDs. The epoxy resin base should not be touching the

PC board when mounting the LEDs.

Mechanical stress to the resin may be caused by the warping of the PC board when soldering.


The LEDs must not be designed into a product or system where the epoxy lens is

pressed into a plastic or metal board. The lens part of the LED must not be glued onto plastic or metal. The mechanical stress to the lead-frame must be minimized.

Soldering

Solder the LEDs no closer than 3mm from the base of the epoxy resin. For solder dipping, it may be necessary to fix the LEDs for correct positioning. When doing this, any mechanical stress to the LEDs must be avoided. When soldering, do not apply any mechanical force to the leadframe while heating. Repositioning after soldering must be avoided.










Solder Profile:

-The recommended reflow soldering profile is as follows (temperatures indicated are as measured on the surface of the LED resin):


Shape	Lead Frame Type / Holder Type
Hand soldering	 Temp.at tip of iron : 300 °C MAX. Soldering time : 3 sec MAX. Distance : 3 mm MIN (from solder joint to case)
DIP soldering	 Preheat temp : 100 °C MAX , 60 sec MAX. Bath temp : 260 °C MAX. Bath time : 5 sec MAX. Distance : 3 mm MIN (From solder joint to case).
Reflow soldering	NO
Shape	SMD Type
Shape Hand soldering	SMD Type 1.Temp.at tip of iron : 300 °C MAX. 2.Soldering time : 3 sec MAX.
-	1.Temp.at tip of iron : 300 °C MAX.







The boxes are not water resistant and they must be kept away from water and moisture. The LEDs are packed in cardboard boxes after packaging in normal or anti-electrostatic bags. Cardboard boxes will be used to protect the LEDs from mechanical shocks during transportation.







Labeling

Quantity: XXXX	QueLighting		
Quelighting P/N: XXXXXX			
Lot number: XXXXX			
lv Bin: XX Color Bin: XX Vf Bin: XX	Date Code: XXXX		

Ordering Information:

Part #	Multiple Quantities	Quantity per bag
QLPD01DXMB		1000pcs



Revision History:

Revision Date:	Changes:	Version #:
10-08-2023	Initial release	1.0

