



QLSP28YD  
PLCC 4  
30 degree



## Product Outline:

This high output reflector type 3528 LEDs are available in Yellow color. This special package is ideal for customer's application in traffic signal and sign boards. With special binning technology, Quelighting is able to provide special binning for customer's needs

## Features:

- High brightness output @ 50mA
- Package Dimension = 3.5mmX2.8mmX3.3mm
- PLCC-4 30 degree viewing angle
- RoHS compliant
- Custom Bin available upon special request


## Application:

- Sign board backlighting
- Emergency vehicle lighting
- Traffic signal lighting

## Compliance and Certification:




**Mechanical Property:  
(Dimension)**



Units: mm

**Back side layout for Solder footprint purpose:**



Units: mm



## Electrical / Optical Characteristic

(T=25 °C)

Product	Color	I <sub>F</sub> (mA)	V <sub>F</sub> (V)		λD (nm)			I <sub>v</sub> (mcd)	
			Typ.	max	Min.	Typ.	Max.	min	typ.
QLSP28YD	Yellow	50	1.9	2.5	588	591	594	4000	6500

- (1) The Forward Voltage tolerance is  $\pm 0.1V$
- (2) The λD tolerance is  $\pm 1nm$
- (3) The I<sub>v</sub> tolerance is  $\pm 7\%$

## Absolute Maximum Rating

(T=25 °C)

Part #	P <sub>d</sub> (mW)	I <sub>F</sub> (mA)	I <sub>FP</sub> (mA)*	V <sub>R</sub> (V)	T <sub>OP</sub> (°C)	T <sub>ST</sub> (°C)	T <sub>SOL</sub> (°C)**
QLSP28YD	100	50	70	5	-40 – 85	-40 - 100	260

\*Duty 1/10 @ 10Khz

\*\* Junction Temperature

\*\*\* IR Reflow for no more than 10 sec @ 260 °C

\*\*\*\* Thermal resistance is calculated from junction to solder



### Forward Voltage ( $V_F$ ) Bin:

VF rank @ 50mA			
Code name	Min.	Max.	Unit
QR	1.9	2.1	V
ST	2.1	2.3	
UV	2.3	2.5	

The forward voltage tolerance is  $\pm 0.1V$

### Luminous Intensity Bin:

Iv rank @ 50mA			
Code name	Min.	Max.	Unit
X48	4000	9000	mcd


luminous intensity tolerance is  $\pm 7\%$

### Dominant Wavelength Bin:


$\lambda_D$ @ IF=50mA			
Code name	Min.	Max.	Unit
A11	588	590	nm
A21	590	592	
A31	592	594	



## Characteristic Curves




Forward Voltage vs. Forward Current




Forward current vs. Relative luminous intensity






Radiation Pattern




WAVELENGTH λ (nm)

Spectrum Distribution





Relative Forward Voltage vs Ambient Temperature




Relative Luminous Intensity vs Ambient Temperature







## Solder Profile:

- The recommended reflow soldering profile is as follows (temperatures indicated are as measured on the surface of the LED resin):
- When soldering LEDs,
- Do not solder/reflow the same LED over two times.
- Recommend soldering conditions:
  - Hand soldering: 300 °C max , 3 sec. max.
  - Reflow soldering: Pre-heat 150 max , 180 sec. max. °C
  - Peak 260 ma °C x , 5 sec. max.
- Reflow temperature profile as below: (lead-free solder)




### Taping & Packing:




Unit : mm







## Labeling




Quantity: XXXX



Quelighting P/N: XXXXXX



Lot number: XXXXX



Iv Bin: XX
Color Bin: XX
Vf Bin: XX
Date Code: XXXX

## Ordering Information:

Part #	Multiple Quantities	Quantity per Reel
QLSP28YD		2000 pcs



**Revision History:**

Revision Date:	Changes:	Version #:
11-01-2020	Initial release	1.0

