

# Tflex 600 Series Thermal Gap Filler



\*Ready for 5G

## **Product Description**

Tflex $^{\text{TM}}$  600 is an exceptionally soft, highly compliant gap filling interface pad with a thermal conductivity of 3 W/mK. These outstanding properties are the result of a proprietary boron nitride filler in the composition.

The high conductivity, in combination with extreme softness produces incredibly low thermal resistances.

Tflex 600 is naturally tacky and requires no additional adhesive coating that can inhibit thermal performance. Tflex 600 is electrically insulating, stable from –45°C to 200°C and meets UL 94 VO rating.

#### **FEATURES AND BENEFITS**

- Very high compliancy for low stress applications
- 3 W/mK thermal conductivity
- Available in thicknesses from 0.020" 0.200" (0.5mm 5.0mm)
- Naturally tacky, needs no further adhesive coating


#### **SPECIFICATIONS**


TYPICAL PROPERTIES	VALUE	TEST METHOD
<b>Construction &amp; Composition</b>	Ceramic filled silicone sheet	N/A
Color	Blue-Violet	Visual
Thickness Range	0.50mm (0.020") - 5.08mm (0.20")	N/A
Thermal Conductivity (W/mK)	3.0	ASTM D5470
Density (g/cc)	1.34	Helium Pyncometer
Hardness (Shore 00)	51	ASTM D2240
Outgassing TML (weight %)	0.65	ASTM E595
Outgassing CVCM (weight %)	0.21	ASTM E595
Temperature Range	-45°C to 200°C	N/A
Rth@ 40 mils, 10 psi, 50°C	0.62°C-in2/W	ASTM D5470 (modified)
Dielectric Constant @ 10GHz	4.0	ASTM D150
<b>UL Flammability Rating</b>	V-0	UL 94
Volume Resistivity (ohm-cm)	2 x 10^13	ASTM D257

Americas: +1.866.928.8181 Europe: +49.(0).8031.2460.0 Asia: +86.755.2714.1166



# Tflex 600 Series Thermal Gap Filler





#### **AVAILABILITY**

#### STANDARD THICKNESSES

- 0.5mm (0.020") to 5.0mm (0.200") thick material available in 0.25mm (0.010") increments
- Available in standard sheet sizes of 18" x 18" and 9" x 9" or custom die cut parts

### OPTIONS

DC1 proprietary tack eliminated coating

#### **PART NUMBER SYSTEM**

Tflex™ indicates Laird elastomeric thermal gap filler product line. 6xx indicates Tflex 600 product line with thickness in mils (0.001") EXAMPLES:

- Tflex™ 640 = 0.040 inch thick Tflex™ 600 material
- Tflex™ 680DC1 = 0.080 inch thick Tflex™ 600 material with DC1 coating

#### Tflex 600 DS 011923

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Technologies materials rests with the end user. Laird Technologies makes no warranties as to the fitness, merchantability, suitability or non- infringement of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential damages of any kind. All Laird Technologies products are sold pursuant to the Laird Technologies, Technologies for the carried product or service to the fitness, morthly and the consequential damages of any kind. All Laird Technologies, the Laird Technologies are sold pursuant to the Laird Technologies, the Laird Technologies, the Laird Technologies, the Laird Technologies, the Laird Technologies are sold pursuant to the Laird Technologies, the Laird Technologies, the Laird Technologies, the Laird Technologies, the Laird Technologies are sold pursuant to the Laird Technologies, the Laird Technologies are sold pursuant to the Laird Technologies, the Laird Technologies are sold pursuant to the Laird Technologies, the Laird Technologies, the Laird Technologies are sold pursuant to the Laird Technologies are sold pursuant to the Laird Technologies, the Laird Tec