
TFM-1XX-XX-X-S-XX-X-XX **REVISION AQ** NOTES: **PACKAGING** REPRESENTS A CRITICAL DIMENSION. BLANK: TUBES (SEE NOTE 7)
-TR: TAPE & REEL (SEE NOTES 8 & 9) © 2. MINIMUM PUSHOUT FORCE: 16 OZ FOR TERMINALS, 12 OZ FOR WELD TABS, No OF POSITIONS AND 8 OZ FOR LOCKING CLIPS. DO NOT ALL POSITIONS AVAILABLE (SEE SHT 3, TAPE & REEL VIEW) 3. MEASURED FROM BEND. SCALE FROM -02 THRU -50 4. MAXIMUM TERMINAL BURR: .003 [.08] (NOT AVAILABLE WITH -01 ÓR THIS PRINT 5. MAXIMUM HEIGHT VARIATION BÈTWÉEN ANY TWO PINS: .005 [.13]. 6. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION -03 LEAD STYLE) -FR: FULL REEL QTY TAPE & REEL IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION. **LEAD STYLE** (SEE NOTES 8 & 9) (SEE SHT 3, TAPE & REEL VIEW) -01: T-1R16-01-X-2 7. TUBES ARE STANDARD PACKAGING. THROUGH HOLE ÍNOT AVAILABLE WITH -01 OR 8. ORDERS WILL BE PACKAGED ACCORDING TO THE SAMTEC PACKAGING EFFICIENCY -02: T-1R16-01-X-2 -03 LEAD STYLE) STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM.
9. ATTACH LABEL TO EACH REEL. SURFACE MOUNT -03: T-1R16-10-X THROUGH HOLE PICK & PLACE OPTION
-P: PICK AND PLACE PAD (USE PPP-15) ((No OF POSITIONS x .050[1.27]) (SEE FIG 6, SHT 2) + .125[3.18])REF **PLATING SPECIFICATIONS** ONLY AVAILABLE ON -08 THRU -50 POSITIONS. -S: 30µ" SELECTIVE GOLD IN CONTACT AREA -07 thru -50 positions with -wt option) -K: POLYIMIDE FILM (SEE FIG 3, SHT 2) ((No OF POSITIONS x .050[1.27]) MÂTTE TIN ON TAIL (USE K-DOT-.217-.313-.005) -F: 3µ" FLASH GOLD IN CONTACT AREA + .025[.64])REF MATTE TIN ON TAIL -L: 15µ" LIGHT GOLD IN CONTACT AREA, OPTION .100 [2.54] REF MATTE TIN ON TAIL -A: ALIGNMENT PIN (USE TFM-XX-S-01-A) -H: 30µ" HEAVY GOLD IN CONTACT AREA, (NOT AVAILABLE WITH -WT OPTION) 3u" GOLD ON TAIL (SEE FIG 5, SHEET 2)
-LC: LOCKING CLIP (USE LC-05-TM) .105 [2.67] REF .065 [1.65 (NOT AVAILABLE WITH -WT OPTION) SEE FIG 7, SHEET 3) (SEE NOTE 6) 01 **BODY SPECIFICATION** -WT: WELD TABS (USE WT-25-07-T) (SEE FIG 4, SHEET 2) (AVAILABLE ON -02 THRU -30 POS ONLY) -S: SINGLE ROW .083 [2.11] (USE TFM-XX-S-XX-XX) .050 [1.27] REF .175 [4.45] REF (NOT AVAILABLE WITH -A OR -LC OPTIONS) **-SN: SOLDER NAIL (USE WT-27-03) (NOT AVAILABLE WITH -A, -LC, OR ((No OF POSITIONS \times .050[1.27]) -WT OPTIONS) (SEE FIG 8, SHEET 3) - .050[1.27]) ** NOT TOOLED 2° MAX SWAY 2° MAX SWAY (TYP) (TYP) $\emptyset.018[0.46]$ REF "A" 1635 [4.153] REF .2200 [5.588] "B" REF "A"±.003["A"±0.08] 🖒 .010[0.25] REF "C"±.003 (C) .014[0.36] REF MAX SWAY 2° MAX SWAY (TYP) (C) ((No OF POSITIONS \times .050[1.27]) - .050[1.27]) SECTION "A"-"A" TABLE 1 $\langle \mathbb{C} \rangle$ **IN-PROCESS** POSITION **COPLANARITY** -02 THRU -29 .004 [.10] FIG 1 PROPRIETARY NOTE UNLESS OTHERWISE SPECIFIED. -030 THRU -39 .006 [.15] (TFM-115-01-X-S-XX SHOWN) THIS DOCUMENT CONTAINS CONFIDENTIAL AND DIMENSIONS ARE IN INCHES. PROPRIETARY INFORMATION AND ALL DESIGN. -40 THRU -50 .008 [.20] MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS TOLERANCES ARE: AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLI DECIMALS **ANGLES** OR PART TO ANY LINAUTHORIZED PERSON OR ENTITY NOR .XX: ±.01 [.3] .XXX: ±.005 [.13] 2° 520 PARK EAST BLVD, NEW ALBANY, IN 47150 REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY PHONE: 812-944-6733 FAX: 812-948-5047 OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS TABLE 2 .XXXX: ±.0020 [.051] WRITTEN CONSENT OF SAMTEC, INC. e-Mail info@SAMTEC.com code 55322 LEAD STYLE "C" "F" **BODY** "A' "B" DO NOT SCALE DRAWING SHEET SCALE: 1:0.4 -01 TFM-XX-S-01-XX .078 [1.98] .131 [3.33] .428 [10.87] .303 [7.70] INSULATOR: LCP, UL 94 V0, COLOR: BLACK .050 C.L. SINGLE ROW SHROUDED TERMINAL STRIP

-02 TFM-XX-S-01-XX .131 [3.33] .428 [10.87] .231 [5.87 N/A -03 TFM-XX-S-01-XX .111 [3.33] .139 [3.53] |.645 [16.83]|.356 [9.04]

TERMINAL: PHOSPHOR BRONZE

TFM-1XX-XX-X-S-XX-X-XX BY: D. SCHMELZ 8/21/2008 SHEET 1 OF 3

F:\DWG\MISC\MKTG\TFM-1XX-XX-X-S-XX-X-XX-MKT.SLDDRW



R.025 [0.64]

FIG 5 -A OPTION

(TFM-115-02-X-S-A SHOWN) (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)

 $\emptyset.050[1.27]$

REF

(No OF POSITIONS \times .050[1.27])

+ .075[1.91])

MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED. IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC. DO NOT SCALE DRAWING


SHEET SCALE: 2:1

PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

.050 C.L. SINGLE ROW SHROUDED TERMINAL STRIP


TFM-1XX-XX-X-S-XX-X-XX

BY: D. SCHMELZ 8/21/2008 SHEET 2 OF 3



(No. OF POSITIONS \times .050[1.27])


+ .075[1.91])±.005[.13]



NOTES:

- 1. USE PT-1-24-11-09 TUBE AND (2) TP-09. 2. USE PT-1-24-03-09 TUBE AND
- (2) TP-09 FOR -P AND -K OPTIONS.

 3. LOAD TUBE WITH 1ST POSITION IN SAME DIRECTION AS ARROW



-SN OPTION (TFM-110-02-X-S-SN SHOWN)

(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)

5 .050 [1.27] (C) -LC-05-TM .056 [1.42] REF .010[0.25] REF **MAX SWAY** MAX SWAY (TYP)

> FIG 7 -LC OPTION (TFM-115-02-X-S-LC SHOWN) (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 2)

* INSPECT ONLY WHEN APPLICABLE WITH RESPECT TO ASSEMBLY OPTION

PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC. INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 2:1

DO NOT SCALE DRAWING

DESCRIPTION

PHONE: 812-944-6733

e-Mail info@SAMTEC.com

.050 C.L. SINGLE ROW SHROUDED TERMINAL STRIP

520 PARK EAST BLVD, NEW ALBANY, IN 47150

FAX: 812-948-5047

code 55322

TFM-1XX-XX-X-S-XX-X-XX BY: D. SCHMELZ 8/21/2008 SHEET 3 OF 3

F:\DWG\MISC\MKTG\TFM-1XX-XX-X-S-XX-X-XX-MKT.SLDDRW