



175°C P-CHANNEL ENHANCEMENT MODE MOSFET PowerDI5060-8

Product Summary

BV _{DSS}	RDS(ON) Max	I _D Tc = +25°C
-40V	10mΩ @V _{GS} = -10V	-50A
-40 V	14mΩ @V _{GS} = -4.5V	-40A

Features and Benefits

- Rated to +175°C Ideal for High Ambient Temperature Environments
- 100% Unclamped Inductive Switch (UIS) Test in Production Low On-Resistance
- Fast Switching Speed
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The DMPH4015SPSQ is suitable for automotive applications requiring specific change control; this part is AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/quality/product-definitions/

Description and Applications

This MOSFET is designed to meet the stringent requirements of automotive applications. It is qualified to AEC-Q101, supported by a PPAP and is ideal for use in:


- Reverse-polarity protections
- BLDC motor controls
- Power-management functions


Mechanical Data

- Package: PowerDI[®]5060-8
- Package Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections: See Diagram
- Terminals: Finish 100% Matte Tin Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 (§3)
- Weight: 0.097 grams (Approximate)










Site2:


PowerDI5060-8/SWP (Type UX)

Pin 1

Top View

Bottom View





Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Load free
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.




Ordering Information (Note 4)


Part Number	Dookogo	Packing		
Part Number	Package	Qty.	Carrier	
DMPH4015SPSQ	PowerDI5060-8	2500	Reel	
DMPH4015SPSQ	PowerDI5060-8/SWP (Type UX)	2500	Reel	

Note:

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information





☐ → Hanufacturer's Marking

H4015SS = Product Type Marking Code

YYWW or YYWW = Date Code Marking

YY or YY = Year (ex: 23 = 2023)

WW = Week (01 to 53)

Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Drain-Source Voltage	VDSS	-40	V		
Gate-Source Voltage	V _{GSS}	±25	V		
Continuous Drain Current V _{GS} = -10V (Note 7)	Steady State	$T_{C} = +25^{\circ}C$ $T_{C} = +100^{\circ}C$	lσ	-50 -35	А
Continuous Drain Current V _{GS} = -10V (Note 6)	Steady State	T _A = +25°C T _A = +100°C	I _D	-12.0 -9.0	А
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%)	I _{DM}	-100	Α		
Maximum Body Diode Continuous Current (Note 7)			Is	-50	Α
Avalanche Current L = 1mH			IAS	-22	Α
Avalanche Energy L = 1mH			E _{AS}	260	mJ

Thermal Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)	T _A = +25°C	PD	1.5	W
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	$R_{\theta JA}$	98	°C/W
Total Power Dissipation (Note 6)	T _A = +25°C	PD	2.6	W
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	Reja	57	°C/W
Thermal Resistance, Junction to Case (Note 7)		R ₀ JC	0.9	°C/W
Operating and Storage Temperature Range		TJ, TSTG	-55 to +175	°C

Notes

- 5. Device mounted on FR-4 PC board, with minimum recommended pad layout, single sided.
- 6. Device mounted on FR-4 substrate PC board, 2oz copper, with thermal bias to bottom layer 1inch square copper plate.
- 7. Thermal resistance from junction to soldering point (on the exposed drain pad).




Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 8)							
Drain-Source Breakdown Voltage	BVDSS	-40		_	V	$V_{GS} = 0$, $I_{D} = -250\mu A$	
Zero Gate Voltage Drain Current	IDSS		_	-1	μΑ	$V_{DS} = -40V, V_{GS} = 0$	
Gate-Source Leakage	I _{GSS}	_	_	±100	nA	$V_{GS} = \pm 25V, V_{DS} = 0$	
ON CHARACTERISTICS (Note 8)							
Gate Threshold Voltage	Vgs(TH)	-1.5	-2	-2.5	V	$V_{DS} = V_{GS}$, $I_D = -250\mu A$	
Static Drain-Source On-Resistance	Dagger		8	10	mΩ	$V_{GS} = -10V, I_{D} = -9.8A$	
Static Diani-Source On-Resistance	RDS(ON)		11	14	11122	$V_{GS} = -4.5V, I_{D} = -9.8A$	
Diode Forward Voltage	V_{SD}	_	-0.7	-1	V	$V_{GS} = 0$, $I_{S} = -1A$	
DYNAMIC CHARACTERISTICS (Note 9)							
Input Capacitance	Ciss		4234	_		V _{DS} = -20V, V _{GS} = 0, f = 1MHz	
Output Capacitance	Coss		1036	_	pF		
Reverse Transfer Capacitance	Crss	_	526	_			
Gate Resistance	R_g	_	7.8	_	Ω	$V_{DS} = 0$, $V_{GS} = 0$, $f = 1MHz$	
Total Gate Charge (V _{GS} = -4.5V)	Qg		42.7	_			
Total Gate Charge (V _{GS} = -10V)	Q_g		91	_	nC	$V_{DS} = -20V,$ $I_{D} = -9.8A$	
Gate-Source Charge	Q_{gs}	1	14.2	_	IIC		
Gate-Drain Charge	Q_{gd}		13.5	_			
Turn-On Delay Time	t _{D(ON)}	_	13.2	_			
Turn-On Rise Time	t _R	_	10	_		$V_{GS} = -10V, V_{DD} = -20V,$ $R_{G} = 6\Omega, I_{D} = -1A$	
Turn-Off Delay Time	tD(OFF)	_	303	_	ns		
Turn-Off Fall Time	tF	_	138	_			
Reverse-Recovery Time	t _{RR}	_	26	_	ns	IF = -9.8A, di/dt = -100A/µs	
Reverse-Recovery Charge	Q _{RR}		20	_	nC	I _F = -9.8A, di/dt = -100A/µs	

8. Short duration pulse test used to minimize self-heating effect. 9. Guaranteed by design. Not subject to product testing. Notes:















Figure 5. Typical On-Resistance vs. Drain Current and **Temperature**










Figure 6. On-Resistance Variation with Temperature






Figure 7. On-Resistance Variation with Temperature





Figure 9. Diode Forward Voltage vs. Current



2.2 $V_{GS(TH)},$ GATE THRESHOLD VOLTAGE (V) 2 $I_D = -1mA$ 1.8 $I_{D} = -250 \mu A$ 1.6 1.4 1.2 -50 -25 0 25 50 75 100 125 150 T_J, JUNCTION TEMPERATURE (°C)

Figure 8. Gate Threshold Variation vs. Junction Temperature




Figure 10. Typical Junction Capacitance




Figure 12. SOA, Safe Operation Area






Figure 13. Transient Thermal Resistance




Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

Site1:


PowerDI5060-8



PowerDI5060-8				
Dim	Min	Max	Тур	
Α	0.90	1.10	1.00	
A1	0.00	0.05	-	
b	0.33	0.51	0.41	
b2	0.200	0.350	0.273	
b3	0.40	0.80	0.60	
С	0.230	0.330	0.277	
D	,	5.15 BSC	;	
D1	4.70	5.10	4.90	
D2	3.70	4.10	3.90	
D3	3.90	4.30	4.10	
Е	6.15 BSC			
E1	5.60	6.00	5.80	
E2	3.28	3.68	3.48	
E3	3.99	4.39	4.19	
е	1.27 BSC			
G	0.51	0.71	0.61	
K	0.51	_	-	
L	0.51	0.71	0.61	
L1	0.100	0.200	0.175	
М	3.235	4.035	3.635	
M1	1.00	1.40	1.21	
Θ	10°	12°	11°	
Θ1	6°	8°	7°	
All	All Dimensions in mm			

Site2:

PowerDI5060-8/SWP (Type UX)



PowerDI5060-8/SWP				
(Type UX)				
Dim	Min	Max	Тур	
Α	0.90	1.10	1.00	
A 1	0	0.05		
b	0.30	0.50	0.41	
b2	0.20	0.35	0.25	
b4	().25REF	=	
C D	0.230	0.330	0.277	
	5	.15 BS0	2	
D1	4.70	5.10	4.90	
D2	3.56	3.96	3.76	
D2a	3.78	4.18	3.98	
Е	6.40 BSC			
E1	5.60	6.00	5.80	
E2	3.46	3.86	3.66	
E2a	4.195	4.595	4.395	
е	1	.27BSC)	
k	1.05			
L	0.635	0.835	0.735	
La	0.635	0.835	0.735	
L1	0.200	0.400	0.300	
L4	0.025	0.225	0.125	
M	3.205	4.005	3.605	
θ	10°	12°	11°	
θ1	6°	8°	7°	
All Dimensions in mm				




Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

Site1:


PowerDI5060-8



Dimensions	Value (in mm)
С	1.270
G	0.660
G1	0.820
Х	0.610
X1	4.100
X2	0.755
Х3	4.420
X4	5.610
Υ	1.270
Y1	0.600
Y2	1.020
Y3	0.295
Y4	1.825
Y5	3.810
Y6	0.180
Y7	6.610

Site2:

PowerDI5060-8/SWP (Type UX)



Dimensions	Value (in mm)
C	1.270
G	0.660
G1	0.820
X	0.610
X1	4.100
X2	5.190
Х3	4.420
Y	1.270
Y1	1.020
Y2	3.810
Y3	6.610



IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners.

© 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com