

RoHS Compliant Directive 2011/65/EU Directive (EU) 2015/863

# **SPECIFICATION**

### Customer : DIGI-KEY ELECTRONICS.

		Receipt
Item:	Crystal Unit	
	oryotal offic	—
_		
Туре:	NX3225GD	
Nominal Frequency:	8.000 MHz	
		—
Quatamar's Snaa Na		
Customer's Spec. No.:		
NDK Spec. No.:	EXS00A-CG04874	
•		—

	Revision Record							
Rev.	Date	Items	Contents	Approved	Checked	Drawn		
	14. Feb. 2024	Issue		M.Sato	M.Harada	H.Arimi		

# 1. Customer's Spec. No.

#### 2. NDK Spec. No.

## : EXS00A-CG04874

3. Туре

: NX3225GD

:---

#### 4. Electrical Specifications

	Parameters		Electrical Spec.				Notes	
	r arameters	SYM.	min	typ	max	Units	NOIES	
1	Nominal frequency	<b>f</b> nom		8.000		MHz		
2	Overtone order	-	Fu	ndamer	ntal	-		
3	Frequency tolerance	-	-20	-	+20	×10 <sup>-6</sup>	at +25°C	
4	Frequency versus temperature characteristics	-	-50	-	+50	×10 <sup>-6</sup>	at -40~+85°C The reference temperature shall be +25°C	
5	Equivalent resistance	-	-	-	500	Ω	IEC PI-network/Series	
6	Shunt capacitance	C <sub>0</sub>	-30%	1.08	+30%	pF	Not grounded	
7	Motional capacitance	C <sub>1</sub>	-30%	1.11	+30%	fF	Not grounded	
8	Motional inductance	L <sub>1</sub>	-30%	356	+30%	mH	Not grounded	
9	Load capacitance	CL	-	8	-	pF	IEC PI-network	
10	Level of drive	-	-	10	200	μW		
11	Operating temperature range	T <sub>opr</sub>	-40	-	+85	°C		
12	Storage temperature range	T <sub>str</sub>	-40	-	+150	°C		
13	Insulation resistance	-	500	-	-	MΩ	When terminal to terminal and terminal to cover were applied at DC100V ±15V.	
14	Air-tightness	-	-	-	3.0×10 <sup>-9</sup>	Pa m³/s		

#### 5. Examination results document

The examination results document is submitted every shipment lot.

# 6. Application drawing

6.1 External dimension	: EXD14B-00474
6.2 Taping and reel figure	: EXK17B-00247
6.3 Holder marking	: EXH11B-00392
6.4 Reliability assurance Item	: EXS30B-00821
6.5 Recommendation reflow profile	: EXS30B-00344

7.Notes on use

- 7-1 Even if the appearance color etc. of the product differs by purchasing the component parts by more than two companies, there is no influence on the characteristics and reliability.
- 7-2 Since the crystal unit is a passive component, it is important to have appropriate circuit conditions. Please be sure to check the circuit conditions before using the crystal units, and ensure the necessary circuit margin, and confirm that the desired frequency is output. Moreover, please check the circuit conditions when using an existing crystal unit for another model or board. If the circuit conditions are not appropriate, there is a risk of oscillation stop or frequency deviation.
- 7-3 IN THE CASE OF THE FOLLOWING ITEMS, WE ARE NOT RESPONSIBLE FOR WARRANTY / COMPENSATION.
- (1) WHEN PRODUCTS OF THIS SPECIFICATION ARE USED FOR EQUIPMENT RELATED TO HUMAN LIFE OR PROPERTY, IT IS THE RESPONSIBILITY OF THE CUSTOMER TO CONFIRM THE INFLUENCE ON THIS PRODUCT AND EQUIPMENT TO BE USED BEFOREHAND, CONDUCT NECESSARY SAFETY DESIGN (INCLUDING REDUNDANT DESIGN, MALFUNCTION PREVENTION DESIGN, etc.), AND PLEASE USE IT AFTER SECURING SUFFICIENT SAFETY OF EQUIPMENT.
  - 1. SAFETY-RELATED EQUIPMENT SUCH AS AUTOMOBILES, TRAINS, SHIPS, etc., OR EQUIPMENT DIRECTLY INVOLVED IN OPERATION
  - 2. AIRCRAFT EQUIPMENT
  - 3. SPACE EQUIPMENT
  - 4. MEDICAL EQUIPMENT
  - 5. MILITARY EQUIPMENT
  - 6. DISASTER PREVENTION / CRIME PREVENTION EQUIPMENT
  - 7. TRAFFIC LIGHT
  - 8. OTHER EQUIPMENT REQUIRING THE SAME PERFORMANCE AS THE ABOVE-MENTIONED EQUIPMENT
- (2) IN CASES WHERE IT IS NOT INDICATED IN THE REQUESTED STANDARD AND IS USED UNDER CONDITIONS OF USE (INCLUDING CIRCUIT MARGIN etc.) THAT CAN NOT BE PREDICTED AT THE PRODUCTION STAGE.
- (3) WHEN USING ULTRASONIC WELDING MACHINE. (THERE IS A POSSIBILITY THAT THE CHARACTERISTIC DEGRADATION IS CAUSED BY THE RESONANCE PHENOMENON OF THE PIEZOELECTORIC MATERIAL.

(EXAMPLE; CRYSTAL PIECE))

WE WILL NOT TAKE ANY RESPONSIBILITY FOR THE INFLUENCE OF THE CUSTOMERS' PROCESS.

SO, PLEASE SUFFICIENTLY EVALUATE AT A SAMPLE STEP WHEN YOU USE ULTRASONIC WELDING MACHINE.

(4) USING RESIN MOLD MAY AFFECT THE PRODUCT CHARACTERISTIC.

PLEASE MAKE SURE TO TELL OUR SALES CONTACT WHEN YOU USE RESIN MOLD. WE WILL PERFORM INDIVIDUAL CORRESPONDENCE ABOUT A DELIVERY SPECIFICATION AND AN EVALUATION METHOD.

IN ADDITION, IF YOU USE RESIN MOLD WITHOUT CONTACTING US, AND CAUSES DAMAGES AGAINST A CUSTOMER OR A THIRD PARTY, WE WILL NOT BE LIABLE FOR THE DAMAGES AND OTHER RESPONSIBILITIES BECAUSE WE CONSIDER IT IS UNDER SELF-RESPONSIBILITY USING RESIN MOLD.

WE WILL NOT TAKE ANY RESPONSIBILITY FOR THE INFLUENCE OF THE CUSTOMERS' PROCESS. PLEASE SUFFICIENTLY EVALUATE AT A SAMPLE STEP WHEN YOU USE RESIN MOLD.

(5) WHEN PERFORMING IMPROPER HANDLING THAT EXCEEDS THE GUARANTEED RANGE.

8.Notes on storage

- 8-1 When storing the product in high temperature and high humidity condition for a long time, product characteristics (solderability etc.) and packaging condition may be deteriorated. Please store product at temperature + 5°C ~ + 35°C, humidity 85% RH or less. The product is an electronic component, so please do not storage and use, under a dewing state.
- 8-2 The product storage deadline is 12 months after delivery in unopened state. Please use within storage deadline. If you exceed storage deadline, please check the product characteristics etc, please use.

#### 9.Other Requests

- 9-1 Please use this specification only for confirmation of the specification of this product.
- 9-2 If there is a change request, please contact within three weeks from issue date. If there is no communication, we will deliver the product under the contents of this specification. In addition, if the product delivery date is within 3 weeks and there is a change request, we will consult the processing separately.
- 9-3 NOTES THAT ARE DESCRIBED IN THIS DOCUMENT, IF YOU DID NOT COMPLY WITH THE PROHIBITIONS, AND OTHER PLEASE, INCLUDING THE FAILURE CORRESPONDENCE OR COMPENSATION OR DAMAGES, WE CAN NOT ASSUME THE RESPONSIBILITY, PLEASE UNDERSTAND.

#### 10. Prohibited items


Be sure to use the product under the following conditions. Otherwise, the characteristics deterioration or destruction of the product may result.

- (1) Reflow soldering heat resistance Peak temperature: 265°C, 10 sec Heating: 230°C or higher, 40 sec Preheating: 150°C to 180°C, 120 sec Reflow passage times: twice
- (2) Manual soldering heat resistance


Pressing a soldering iron of 400°C on the terminal electrode for four seconds (twice).


When using a soldering iron, press its tip on the part below the sealed part, avoiding the glass-sealed part

(otherwise, the glass will melt and air-tightness may be lost)



Appr	roved	13.May.2010	K.Ueki	Dimension	Drawin	g   CAD14D-	EXD14B-00474	
Cheo	cked	13.May.2010	K.Komada	NX3225GD		EVD44B 00474		D
Desi	gned	13.May.2010	R.Shariman	Title		Drawing No.		Rev.
Draw	vn	13.May.2010	R.Shariman	Dimension:mm		±0.1	1/	15
		Date	Name	Third Angle Projection		Tolerance	Sc	ale
D	7.	Oct. 2019	H.Arimi	M.Sato	M.Sato Change: Land pattern notation.			
	Da	te of Revise	Charge	Approved	Reason			






3000pcs-Product Tape

	改訂 日.	/ Date of Revise	担当/ Charge	承認/ Approved	理由/ Rea	son			
D	21	Sep. 2022	K. Kawashima	H. Murakoshi	H. Murakoshi 誤記訂正 / Correction of error.				
		Date	Name	三角法/ Third Angle Projection 公差/ Tolerance 尺			尺度/	Scale	
Drav	wn	30.Jun.2006	H.Yagishita	単位/ Dimension:mm			- ,	/ -	
Des	signed	30.Jun.2006	H.Yagishita	名称/Title			図番/ Drawing No	).	改訂/ Rev.
Che	ecked	30.Jun.2006	K.Kubota	NX3225 シリーズ テービング・ リ ール図 NX3225 Series Taping and Reel Spec.			EXK17B-00247		
Арр	oroved	30.Jun.2006	T.Ishii			EXK1/B	-00247	D	
						~			

End



NOTE 1. Frequency Code

Marking Frequency is consist of five digits, first five digits of Nominal Frequency

# Example

Nominal Frequency	28.636363 MHz			
Frequency Code	28.636			

# 2. Month Code Table

Month	1	2	3	4	5	6	7	8	9	10	11	12
	Jan.	Feb.	Mar.	Apr.	May.	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
Month Code	1	2	3	4	5	6	7	8	9	Х	Y	Z

# 3. Marking contents

Example

Administrative symbol S

\*Marking digits are not include a decimal point and dot mark.

ate of Revise	Charge	Approved R	leason			
Date	Name	Third Angle Projection 1		olerance	Sca	ale
19.May.2008	R.Shariman	Dimension:mm	Dimension:mm		/	1
19.May.2008	R.Shariman	Title		Drawing No.		Rev.
19.May.2008	M.Harada	Crystal Holder Marking		EXH11B-00392		
19.May.2008	K.Kubota					
	19.May.2008 19.May.2008 19.May.2008	Date Name   19.May.2008 R.Shariman   19.May.2008 R.Shariman   19.May.2008 M.Harada	Date Name Third Angle Projection   19.May.2008 R.Shariman Dimension:mm   19.May.2008 R.Shariman Title   19.May.2008 M.Harada Crystal Holder	Date Name Third Angle Projection T   19.May.2008 R.Shariman Dimension:mm T   19.May.2008 R.Shariman Title   19.May.2008 M.Harada Crystal Holder Marking	Date Name Third Angle Projection Tolerance   19.May.2008 R.Shariman Dimension:mm Drawing No.   19.May.2008 M.Harada Crystal Holder Marking FXH11B-	Date Name Third Angle Projection Tolerance Sca   19.May.2008 R.Shariman Dimension:mm //   19.May.2008 R.Shariman Title Drawing No.   19.May.2008 M.Harada Crystal Holder Marking FXH11B-00392

		Reliability assurance item	(0000014/0)
No	Teatitom	Toot mothodo	(page: 1/2)
No.	Test item	Test methods	Spec. code
1	Drop	Devices are dropped from the height 75 cm onto iron plate. Execution 3 times random drops.	А
2	Shock	Acceleration: 49000 m/s <sup>2</sup> Duration: 0.15 ms Half-Sine pulse 1 Shocks in 6 mutually perpendicular planes, Total 6 shocks	A
3	Vibration	Frequency range: 10 to 2000 Hz Amplitude or Acceleration: 1.52 mm or 196 m/s <sup>2</sup> Sweep time: 20 min Test time: 4 $h \times 3$	A
4	Electrode adherent strength	See remark (1)	В
5	Solderability	Pre-heat temperature: 150 °CPre-heat Time: 60 ~ 120 sPeak temperature: 240 $\pm$ 5 °C215 °C Over time: 10 ~ 30 s	С
6	Resistance to soldering heat	Pre-heat temperature: $150 ^{\circ}\text{C}$ Pre-heat time: $60 \sim 120 \text{s}$ Test temperature: $260 \pm 5 ^{\circ}\text{C}$ Test time: $10 \pm 1 \text{s}$	A,B
7	Resistance to cold	Leave at -40 $\pm$ 2 °C for 1000 h	А
8	Resistance to heat	Leave at +150±2 °C for 1000 h	A
9	Humidity	Device are left in temperature at +85 $\pm$ 2 °C with relative humidity of 80~85 % for 1000 h	A,D
10	Thermal shock	Device are left into the following temperature cycle as shown in (Figure 1) for 1000 consecutive cycle. $150\pm5 \ ^{\circ}C$ $-40\pm5 \ ^{\circ}C$ $-40\pm5 \ ^{\circ}C$ $-60$	A,B
		(Figure1)	


	(page: 2/2)
Spec. code	Specification
Δ	$\Delta f/f \le \pm 20 \text{ ppm}$
A	$\Delta$ CI/CI $\leq$ ± 40 % or 5 $\Omega$ make use larger value
В	After testing unless cracking of materials view of eyes
В	and unless break of seal.
C	The leads shall acquire a new solder coat cover at 90 % of immersed
6	area.
D	Insulation resistance shall be greater than 500 M $\Omega$
_	

# **Reliability assurance item**

Remark (1) Electrode adherent strength.

1) Test method condition

Using the solder, soldering Iron or reflow soldering bath shall be used for soldering on test fixture (Glass fiber epoxy laminate : Thickness 1.6mm+/-0.2mm) shown below.



Glass fiber epoxy laminate

2) Specified value

No peel of electrode, no crack, no other abnormality

# **Recommendation reflow condition**

- MAX. 10s  $260 \pm 5^{\circ}C$ (°C) 250 Over 230°C 200-150°C~180°C TEMP. 150 100 60s ~ 120s 30±10s 50 0 ≻ (s) TIME
- 1.IR reflow condition