DIALIGHT PART NO.	POS.I	POS.2
552-0201F	**BLANK**	RED DIFFUSED
552-0202F	**BLANK**	GREEN DIFFUSED
552-0203F	**BLANK**	YELLOW DIFFUSED
552-0210F	RED DIFFUSED	**BLANK**
552-0211F	RED DIFFUSED	RED DIFFUSED
552-0212F	RED DIFFUSED	GREEN DIFFUSED
552-0213F	RED DIFFUSED	YELLOW DIFFUSED
552-0220F	GREEN DIFFUSED	**BLANK**
552-0221F	GREEN DIFFUSED	RED DIFFUSED
552-0222F	GREEN DIFFUSED	GREEN DIFFUSED
552-0223F	GREEN DIFFUSED	YELLOW DIFFUSED
552-0227F	GREEN DIFFUSED	ORANGE DIFFUSED
552-0230F	YELLOW DIFFUSED	**BLANK**
552-0231F	YELLOW DIFFUSED	RED DIFFUSED
552-0232F	YELLOW DIFFUSED	GREEN DIFFUSED
552-0233F	YELLOW DIFFUSED	YELLOW DIFFUSED
552-0277F	ORANGE DIFFUSED	ORANGE DIFFUSED

RoHS Compliant 552-02XXF Bi-level CBI Part Numbers with the "F" suffix ending are RoHS Compliant.

Example: 552-0210F

Packaging is marked with "RoHS Compliant" label or equivalent markings. Parts can be wave soldered, dip soldered or hand soldered using typical lead-free soldering process with max 260°C temp. for 5 sec.

REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE	
Α		NEW RELEASE	SM	N.O.	MES	10-5-06	
В		ADDED P/N'S 552-0202F,-0203F,-021IF,-0212F,-0213F, -0220F,-022IF,-0222F,-0223F,-0227F,-0230F,-0231F, -0232F,-0233F,-0277F; REMOVED PIN OUTS COLUMN; ADDED METRIC DIMS; ADDED GREEN AND YELLOW LED SPECS; UPDATED LED SCHEMATIC; ".180±.020" WAS ".173"; REMOVED "RED DIFFUSED" FROM TITLE BLOCK; CHANGED NOTE 3; ADDED NOTE 5.	KLJ				
С	92288	REVISED YELLOW SPEC	LD	NO		5-5-22	

.430 REF -

[10,92]

-HOUSING

.493 REF

[12,52]

TOP LED

.180±.020


 $[4,57\pm0,5]$


POS.1

POS.2-


LENS COLOR	PEAK EMISSION WAVELENGTH (nm)	VIEW ANGLE	(°) (mcd) IF = 10 mA (V) IF = 20 mA (YELLOW) (μ A);		(V) IF = 10 mA V) IF = 20 mA (YELLOW)		REVERSE CURRENT (µA); 25°C
	(,		MIN	TYP	TYP	MAX	MAX
RED DIFFUSED	650	50	2.2	6.3	2.2	2.55	10 @ VR = 3V
GREEN DIFFUSED	563	60	3.6	10.0	2.1	3.0	10 @ VR = 3V
YELLOW DIFFUSED	585	50	19	40	2.1	2.6	100 @ VR = 5V
ORANGE DIFFUSED	600	60	4.0	7.0	1.9	2.4	100 @ VR = 5V

ABSOLUTE MAXIMUM RATINGS AT 25°C AMBIENT		COLOR				
		GREEN	YELLOW	ORANGE	UNITS	
POWER DISSIPATION	60	75	52	135	mW	
CONTINUOUS FORWARD CURRENT	20	25	20	30	mA	
PEAK FORWARD CURRENT (I/5 DUTY PULSE, Ims WIDTH FOR RED & GRN) (IOµs PULSE WIDTH FOR ORG) (DUTY CYCLE ∠ = I/IO, PULSE WIDTH∠ = IOus FOR YEL	60	80	60	500	mA	
REVERSE VOLTAGE		3		5	V	
SOLDERING TEMPERATURE (.063 IN FROM BODY FOR 5 SEC)			260		°C	
OPERATING TEMPERATURE	-25 T	0 +85	-40 TO +8	5 - 55 TO + 100		
STORAGE TEMPERATURE	- 30 T	0 + 0 0	-40 TO +IC	00-55 TO +100	°C	










.220±.020 [5,59±0,5]

NOTES:

- I. LEADS TO FIT INTO HOLES SPACED AS PER HOLE PATTERN.
- 2. LEAD DIMENSIONS SHOWN ARE MEASURED AT HOUSING EXIT.
- 3. DIALIGHT PART NUMBERS: 552-02XXF.
- 4. THIS ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE DEVICES (ESDS). MAINTAIN ALL PRECAUTIONARY MEASURES DURING ASSEMBLY, HANDLING, AND STORAGE IN ACCORDANCE WITH IPC-A-610.
- 5. PIN NUMBERS FOR REFERENCE ONLY, DESIGNATION NON-EXISTENT ON PART.





PROPERTY OF DIA CONSTRUCTION OF ANY	HE CONTENTS HEREIN ARE CONFIDENTIAL AND THE ALIGHT CORP. REPRODUCTION OF THIS DRAWING Y PARTS WITHIN THIS DRAWING ARE FORBIDDEN W WRITTEN CONSENT OF DIALIGHT CORP.	OR			
SCALE: DRAWING SCALE	DRAWING NUMBER	REV			
ALL DIM's: INCH (mm)	C-17423	\cap			
TOLERANCES: UNLESS OTHERWISE SPECIFIED	C-11423				
FRACTIONS: ±1/64 DECIMALS (.XX): ±.01 DECIMALS (.XXX): ±.005	TITLE 5mm CBI BI-LEVEL RoHS COMPLIANT				
DECIMALS (.XXXX): ±.0005 ANGLES: ±1°	MATERIAL				
FINISH	FARMINGDAL (732)	E 34 SOUTH E, NJ 07727 919-3119 light.com			
FSCM 83330	SHEET I OF I FAMILY TABLE:				