This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited. ©2024, PUI Audio Inc.





Data Sheet

AB4122B


Features:


- Ultrathin and lightweight 41mm bender
- 2,200 Hz resonant frequency
- Low power consumption

Specifications

Parameters	Values	Units
Resonant Frequency	2,200 ± 300	Hz
Resonant Impedance (Max)	250	Ohms
Max Input Voltage	30	Vp-p
Capacitance (@ 120 Hz)	30,000 ± 30%	pF
Plate Material	Brass	_
Storage Temperature	-30 ~ 80	°C
Operating Temperature	-20 ~ 70	°C
Environmental Compliances	RoHS/REACH	Exempt. 7c-1

Dimensions





Packaging

100pcs/roll, foam packaging 20 rolls/layer = 2000pcs total 5 layers = 10,000pcs

Specifications Revisions

Revision	Description	Date	Approved
А	Released from Engineering	3/6/2024	JD

Note:

- 1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are ± 0.5 mm and angles are $\pm 3^{\circ}$.
- 2. Specifications subject to change or withdrawal without notice.