TTL OUTPUT HALF SIZE DIP CRYSTAL CLOCK OSCILLATOR

AHT Series



100.000kHz ≤F<160.000MHz



FEATURES:

- Hermetically sealed metal package
- TTL output
- Case ground for EMI protection
- Tri-state Enable/Disable options

> **APPLICATIONS**:


- Provide clock signals for microprocessors and digital circuits
- TTL output for low EMI applications

STANDARD SPECIFICATIONS:

| PARAMETERS | |
|-------------------------------|---|
| ABRACON P/N | AHT Series |
| Frequency: | 400kHz to 160MHz |
| Operating temperature: | 0°C to +70°C (see options) |
| Storage temperature: | - 55°C to + 125°C |
| Overall frequency stability*: | ± 100ppm max. (see options) |
| Supply voltage (Vdd): | $5.0 \text{Vdc} \pm 10\%$ |
| Input current: | See Table 1 |
| Symmetry: | 40/60% max. (see option) |
| Rise and Fall Times (Tr/Tf): | See Table 1 |
| Output load: | 10 TTL max. |
| Output Voltage: | VOH = 0.9 * Vdd min. $VOL = 0.1* Vdd max.$ |
| Tri State Function: | "1" (VIH \geq 2.4 Vdc) or open: Oscillation "0" (VIL \leq 0.4V): Hi Z |
| Output Disable/ Enable time: | 100 ns max. (for Option "-A" ONLY) |
| Start-up-time: | 10 to 35 ms max |

80

OPTIONS & PART IDENTIFICATION:



^{*}Temp option I, D, and E only

±50 ppm max.

C





^{*} Overall frequency stability includes initial tolerance, temperature stability, and aging.


TTL OUTPUT HALF SIZE DIP CRYSTAL CLOCK OSCILLATOR

AHT Series





OUTLINE DIMENSIONS:



ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.



