



Our Hybrid Stepper Motors are a precise motion control solution providing excellent holding torque. They come in a various sizes and step angles. With endless performance combinations, we have a fully tailor solution for you.




[View Alternative Solutions!](#)

Specifications

Gearhead Type:	Planetary	Step Angle:	1.8 °
Motor Type:	Hybrid Stepper	Phase Inductance:	1.5 mH (+/- 20%) @ 1kHz
Rated Voltage:	4.32V DC	Number of Leads:	4
Number of Phases:	2	Phase Resistance:	5.4 Ω (+/- 10% @ 20° C)
Rated Current:	0.8 A	Insulation Class:	B
Holding Torque:	31 kg.cm	Reduction Ratio:	139:1

Dimensions



Wiring Diagram

Wiring Diagram

Exciting Sequence

CW DIRECTION	STEP	A	C	B	D
↓	1	+		+	
	2		+	+	
	3		+		+
	4	+			+
	1	+		+	

Clockwise view from mounting side

Torque Curve (Motor Alone)

