




Table 2 (Hole Arrangement, Mating Face)

2 Pos	3 Pos	4 Pos	5 Pos	6 Pos
300 v 10 A	300 v 10 A	125 v 10 A	60 v 5 A	60 v 5 A

(2+4)Pos	(3+4)Pos	8 Pos	10 Pos	12 Pos
60 v 10+5 A	60 v 10+2 A	60 v 5 A	30 v 2 A	30 v 2 A

REV.	ECN NO.	DESCRIPTION	SIGN	DATE
D1	N/A	INITIAL DRAWING	Peng	2013/04/08

Table 1

Position No.	Connector Part No.	4 Housing Part No.	3 Contact		
			Contact Part No.	Q'ty	Contact Description
2	22002515-03	105-00066-00	301-00068-02	2	MZP1.5
3	22003515-03	105-00072-00	301-00068-02	3	MZP1.5
4	22004515-03	105-00081-00	301-00068-02	4	MZP1.5
5	22005515-03	105-00090-00	301-00052-02	5	MZBP1.0
6	22006515-03	105-00095-00	301-00052-02	6	MZBP1.0
2+4	22204515-03	105-00204-00	301-00068-02	2	MZP1.5
			301-00052-02	4	MZBP1.0
3+4	22304515-03	105-00228-00	301-00068-02	3	MZP1.5
			301-00067-02	4	MZP0.8
8	22008515-03	105-00100-00	301-00052-02	8	MZBP1.0
10	22010515-03	105-00105-00	301-00067-02	10	MZP0.8
12	22012515-03	105-00109-00	301-00067-02	12	MZP0.8

Specification:

- 1.Operation temperature:-45℃~105℃.
- 2.Insulation resistance:100MΩ at DC500V.
- 3.Contact resistance:<10mΩ.
- 4.Waterproof:IP68.
- 5.RoHS compliant.
- 6.Mating Waterproof Cap P/N:806-00030-00.
- 7.Mating Connector P/N:22XXX211-XX or 22XXX213-XX-001 or 22XXX214-XX-001.

Material List

No.	Material No.	Q'ty	Material Description	Remark
1	112-00007-00	1	Standard Panel Nut	
2	503-00018-00	1	Standard Gasket	
3	See above table 1		Contact	
4	See above table 1	1	Standard-XX Pos Housing	

**CHOGORI
USA Inc.**

UNIT:mm		Description
TOLERANCE		Standard Series Rear Mount, Screw Type, Pin Solder
.X ±0.25		
.XX ±0.15		
.XXX ±0.05		
ANGLES ±1°		
REV. D1	SIZE A4	QC : Inspection Item

PART NO	22XXX515-03	DRAWN BY	PENG	DATE	2013-04-08
DWG NO		CHECKED BY		DATE	
CUSTOMER		APPROVED BY		DATE	