# **DH-G series** Electo

# Electoric Double Layer Capacitor "DYNACAP"



### 5.5V Wider Temperature range Capacitors

GREEN

85° C


- The wetprooting is improved by wearing the resin court to the sealing part.
- Wider temperature range (-40°C to +85°C) than battery.
- φ13.5×9.8L size can encase up at 0.22F.
- Advanced in rapid charge and dischage.
- Ideal for backing up of CMOS IC's, microcomputers, RAM's, RTC's and the like used in Electric power meter, Outdoor installation equipment, Automotive applications, Industrial equipment



#### ■ Specifications

Item	Performance				
Category temperature range(°C)	-40 to +85				
Tolerance at rated capacitance(%)	-20 to +80				
Internal resistance at 1kHz(Ω)	Rated capcitance(F)  Internal resistance ( $\Omega$ )	0.047 40	0.1 40	0.22 40	
Characteristics at high and low temperature	Percentage of capacitance change  Internal resistance	Within ±30% of the value at 20°C -40°C: Less than 7 times of the value at 20°C 85°C: Less than 5 times of the value at 20°C			
Endurance(85°C)	Test time Percentage of capacitance change Internal resistance	1000 hc Within ±30% of the init Within 4 times of the in			
Shelf life(85°C)	Test time:1000 hours;Same as endurance.				
Applicable standards	Conform to JIS C 5160-1 2009				

# **■** Outline Drawing



# ■ Part numbering system (example:5.5V0.1F)

DHL	- <u>5R5</u>	D	<u>104</u> GT	
Series code	Max.operating voltage symbol	Rated capacitance symbol		

Part number is refer to below tabale.

## ■ Caution for Cleaning after Soldering

- ·Recommended cleaning method
- (1)cleaning solutions:
  - (a) CLEANTHROUGH 710M, 750H, 750L
  - (b) PINEALPHA ST-100S
  - (c) Techno Care FRW-4~17
  - (d) Isopropyl alcohol (2-propanol)

(2)Cleaning conditions:

- (a) The temperature of cleaning solution shall be less than 60°C.
- (b) Use immersion or ultrasonic waves within two minutes.
- (c) After cleaning, capacitors and PCB's shall thoroughly be rinsed and dried with hot blast for more than 10 minutes. The temperature of such breeze should be less than the upper category temperature.
- (d) After cleaning, do not keep capacitors in cleaning solution atmosphere or airtight containers.
- During cleaning, control the cleaning solution against contamination.

### ■ Standard Ratings

Max operating voltage(V)	Rated capacitance(F)	ELNA Parts No.	φD×L (mm)
5.5	0.047	DHL-5R5D473GT	13.5×9.8
5.5	0.1	DHL-5R5D104GT	13.5×9.8
5.5	0.22	DHL-5R5D224GT	13.5×9.8

NOTE

Design,Specifications are subject to change without notice.

Ask factory for technical specifications before purchase and/or use.

ELNA CO., LTD.

3-8-11 Shin-yokohama,kouhoku-ku,yokohama-city,kanagawa,222-0033 JAPAN TEL. +81-45-470-7254 FAX. +81-45-470-7260