

NBC-4X2X26-OE-OE-94B-100,0 SH - Cable reel



1422113

<https://www.phoenixcontact.com/us/products/1422113>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable reel, 8-position, PUR halogen-free, water blue RAL 5021, shielded (Aluminum-coated foil, tinned copper braided shield), cable length: 100 m

Commercial data

Item number	1422113
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF16
Product key	BF1IIC
GTIN	4055626325637
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85444290
Country of origin	DE

1422113

<https://www.phoenixcontact.com/us/products/1422113>

Technical data


Product properties

Product type	Data cable by the meter
Number of positions	8
Application	Connector

Cable/line

Cable length	100 m
--------------	-------

Ethernet flexible CAT5, 4-pair [94B]

Dimensional drawing	
Cable weight	47 kg/km
UL AWM Style	20963 (80°C/30 V)
Number of positions	8
Shielded	yes
Cable type	Ethernet flexible CAT5, 4-pair [94B]
Conductor structure	4x2xAWG26/7, SF/UTP
Signal runtime	5.3 ns/m
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	4x 2x 0.14 mm ²
Wire diameter incl. insulation	0.98 mm
External cable diameter	6.40 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021
Conductor material	Bare Cu litz wires
Material wire insulation	PE
Single wire, color	white/blue-blue, white/orange-orange, white/green-green, white/brown-brown
Thickness, insulation	0.25 mm
Thickness, outer sheath	1.00 mm
Twisted pairs	2 cores to the pair
Overall twist	4 pairs for core
Optical shield covering	70 %
Max. conductor resistance	≤ 290 Ω/km
Insulation resistance	≥ 500 MΩ*km

NBC-4X2X26-OE-OE-94B-100,0 SH - Cable reel



1422113

<https://www.phoenixcontact.com/us/products/1422113>

Coupling resistance	≤ 100.00 mΩ/m (at 10 MHz)
Wave impedance	100 Ω ±5 Ω (at 100 MHz)
Working capacitance	48 nF (at 1 kHz)
Nominal voltage, cable	≤ 100 V 300 V (Outer cable sheath)
Test voltage Core/Core	700 V (50 Hz, 1 min.)
Test voltage Core/Shield	700.00 V (50 Hz, 1 min.)
Smallest bending radius, fixed installation	25.6 mm
Smallest bending radius, movable installation	51.2 mm
Tensile strength	≤ 100 N
Halogen-free	according to IEC 60754-1
Flame resistance	IEC 60332-1-2
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -20 °C ... 80 °C (Cable, flexible installation)
Ambient temperature (installation)	-20 °C ... 80 °C

NBC-4X2X26-OE-OE-94B-100,0 SH - Cable reel



1422113

<https://www.phoenixcontact.com/us/products/1422113>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1422113>



UL Recognized

Approval ID: FILE E 344675

1422113

<https://www.phoenixcontact.com/us/products/1422113>

Classifications

ECLASS

ECLASS-11.0	27061801
ECLASS-12.0	27061801
ECLASS-13.0	27061801

ETIM

ETIM 8.0	EC003249
----------	----------

NBC-4X2X26-OE-OE-94B-100,0 SH - Cable reel



1422113

<https://www.phoenixcontact.com/us/products/1422113>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

NBC-4X2X26-OE-OE-94B-100,0 SH - Cable reel



1422113

<https://www.phoenixcontact.com/us/products/1422113>

Accessories

WIREFOX SAC - Stripping tool

1212623

<https://www.phoenixcontact.com/us/products/1212623>



Stripping pliers, for halogen-free sensor/actuator cables (SAC cables), with PUR and PVC insulation, from Ø of 4.4 to 7 mm, any stripping length

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com