THIS PRODUCT MANUFACTURED WITH LEAD-FREE PROCESSING

HDRL-XX

(SEE TABLE 2) (SEE NOTE 5) (TOP CABLE REMOVED

FOR CLARITY)

STS-04

(SEE NOTE 7)

(SEE TABLE 2)

01

No OF POSITIONS

-013 (8 PAIR) -025 (16 PAIR) -049 (32 PAIR) (PER ROW)

**LENGTH** 

-XX.XX (INCHES) (01.72[43.7] MIN) (SEE NOTE 8) (SEE NOTE 9)

FIRST END

-TTR: TERMINAL, TOP, RIGHT

-TTL: TERMINAL, TOP, LEFT -TBR: TERMINAL, BOTTOM, RIGHT

-TBL: TERMINAL, BOTTOM, LEFT

-STR: SOCKET, TOP, RIGHT -STL: SOCKET, TOP, LEFT -SBR: SOCKET, BOTTOM, RIGHT

-SBL: SOCKET, BOTTOM, LEFT -TEU: TERMINAL, EDGEMOUNT, UP -TED: TERMINAL, EDGEMOUNT, DOWN

SOME CENTER FEATURES ON CONNECTORS REMOVED FOR CLARITY

N-1 (SEE TABLE 2)

\*OPTION ONLY AVAILABLE WITH -TEX OPTIONS

(SEE NOTE 10)
\*\*LATCH OPTION REQUIRED, PART NUMBER MUST BE COMPLETE TO BE VALID

\*\*\*SQUEEZE LATCH TEX OPTIONS ONLY \*\*\*\*: AVAILABLE TO EXISTING CUSTOMERS ONLY

**FIRST END** 


738 [18.75]

0

**SECOND END** 

0

Ν (SEE TABLE 2)



(SEE TABLE 2)

XX.XX + "B" REF (SEE TABLE 3)

(OVERALL LENGTH) (SEE NOTE 14)

CABLE LENGTH

FIG 1 (ERDP-025-XX.XX-STL-TTR-1-D SHOWN)

TABLE 2									
# OF POSITIONS	N	N-1	HDRL-XX						
-013	26	25	HDRL-11						
-025	50	49	HDRL-11						
-049	98	97	HDRL-13						

TABLE 3	
END TO END	"B"
DV TO DV	.924[23.47]
DV TO EM (-TXX)	1.051[26.69
EM (-TXX) TO EM (-TXX)	1.178[29.92

TABLE 1											
				CABLE	CALLOUT						
# OF POSITIONS	DF POSITIONS "A" XCD-XX-01 XCD-XX-02 WIRING OPTION				GOPTION		SUB-ERDP-X-XXX-XX-XX-X (SEE TABLE 7)				
# OF POSITIONS	<b>A</b>	ACD-AA-01	ACD-AA-02	-1, -2, -3, -4	-5, -6, -7, -8	QTY	(OLL TABLE 1)				
-013	1.018[25.86]	ECD-13-01	ECD-13-02	SUB-TTF-30100-04-01-XX.XX	SUB-TTF-30100CU-04-01-XX.XX	2	SUB-ERDP-X-013-XX-XX-X				
-025	1.3645[34.66]	ECD-25-01	ECD-25-02	SUB-TTF-30100-08-01-XX.XX	SUB-TTF-30100CU-08-01-XX.XX	2	SUB-ERDP-X-025-XX-XX-X				
-049	2.120[53.85]	ECD-49-01	ECD-49-02	SUB-TTF-30100-16-01-XX.XX	SUB-TTF-30100CU-16-01-XX.XX	2	SUB-ERDP-X-049-XX-XX-X				
				SEE TABLE 8 (SHEET 6)							

F:\DWG\MISC\MKTG\ERDP-XXX-XXX-XXX-XXX-XXX-XXKT.SLDDRW

ERDP-XXX-XX.XX-XXX-XXX-X-X

REPRESENTS A CRITICAL DIMENSION.

2. PARTS TO BE PROCESSED PER SAMTEC ACCEPTABILITY REQUIREMENTS: HDR-PI-01 "CABLE ASSEMBLY WORKMANSHIP STANDARDS".

3. ALL ASSEMBLIES TO BE 100% ELECTRICALLY TESTED.

4. ALL ASSEMBLIES TO BE 100% HI-POT TESTED AT 300V

5. LABEL TO BE CENTERED ON LOWER CABLE AS SHOWN. LABEL TO CONTAIN:

LINE 1 - PART NUMBER "ERDP-XXX-XX.XX-XXX-XXX-XXX

LINE 2 - SHOP ORDER NUMBER "XXXXXXX"

LINE 3 - DATE CODE "XXXXXX"

6. FOR PACKAGING REQUIREMENTS REFERENCE PACKAGING STANDARDS. 7. TIGHTEN STS-04 FASTENERS TO 1.4-1.7 IN-LBS (4 PLCS).

8. SUB-TCF LENGTH IS EQUAL TO ERCD LENGTH.

9. CABLE LENGTHS LONGER THAN 40.00 INCHES ARE NOT SUPPORTED BY S.I. TEST DATA.

10. -B & -1 OPTION ONLY AVAILABLE WITH -TEX ON BOTH ENDS. -L, -2, -G & -4 OPTIONS ONLY AVAILABLE WITH -TEX ON 2ND END. -R, -3, -T & -5 OPTION ONLY AVAILABLE WITH -TEX ON FIRST END.

11. THE RECOMMENDED MATING CONNECTOR IS THE ERF8 OR ERM8 WITH -L LATCHING

12. WIRING OPTION -5 THROUGH -8 USE 30100CU.

13. REFER TO PREP-SPEC DRAWING FOR CABLE PREP DIMENSIONS. ASSEMBLY USES STANDARD PCB PREP.

14. FOR CABLE LENGTHS LESS THAN 5 INCHES, CABLE LENGTH AND OVERALL LENGTH TOLERANCE IS  $\pm 0.05$ INCHES, FOR CABLE LENGTHS GREATER THAN 5 INCHES, USE ±1% FOR BOTH.

TOLERANCES DO NOT APPLY TO REFERENCE DIMENSIONS. UNLESS OTHERWISE SPECIFIED,

DIMENSIONS ARE IN INCHES. TOLERANCES ARE: DECIMALS ANGLES .XX: ±.01[.3] .XXX: ±.005[

.XXXX: ±.0020[.051]

PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING REPRODUCTION USE PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED. IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC INC

THIS DOCUMENT CONTAINS CONFIDENTIAL AND

PROPRIETARY NOTE

DO NOT SCALE DRAWING SHEET SCALE: 1:1 MATERIAL: PLATING

0.8MM EDGE RATE TWIN-AX CABLE ASSEMBLY

520 PARK EAST BLVD, NEW ALBANY, IN 47150

FAX: 812-948-5047

PHONE: 812-944-6733

e-Mail info@SAMTEC.com

**-LATCH OPTION\*\*** (SEE NOTE 11) \*-L: 1ST END STD LATCH, 2ND END SQUEEZE LATCH \*-R: 1ST END SQUEEZE LATCH, 2ND END STD LATCH

-F: 1ST END SCREW OPTION, 2ND END FRICTION LATCH -S: 1ST END FRICTION LATCH, 2ND END SCREW OPTION

-C: BOTH ENDS SCREW OPTION.

"G: IST END SCREW OPTION, 2ND END SQUEEZE LATCH

"-T: IST END SQUEEZE LATCH, 2ND END SCREW OPTION

"1: BOTH ENDS EXTENDED HOUSING SQUEEZE LATCH

"2: FIRST END FRICTION LATCH, 2ND END EXTENDED

HOUSING SQUEEZE LATCH

"3: FIRST END EXTENDED HOUSING SQUEEZE LATCH, 2ND

END, FRICTION LATCH

"4: FIRST END SCREW OPTION, 2ND END EXTENDED

HOUSING SQUEEZE LATCH

"5: FIRST END EXTENDED HOUSING SQUIEZE LATCH 2ND

\*\*\*-5: FIRST END EXTENDED HOUSING SQUEEZE LATCH, 2ND FND SCREW OPTION

-5: PIN 1 TO PIN 1 -6: PIN 1 TO PIN 2 -7: PIN 1 TO PIN N-1 -8: PIN 1 TO PIN N

-N: NO CAPS (BOTH ENDS HAVE STD LATCH)

-D: BOTH ENDS STD LATCH

**WIRING OPTION** 

\*\*\*\*-1: PIN 1 TO PIN 1 \*\*\*\*-2: PIN 1 TO PIN 2

\*\*\*\*-3: PIN 1 TO PIN N-1 \*\*\*\*-4: PIN 1 TO PIN N (SEE TABLE 7, SHEET 6) (SEE NOTE 12)

SECOND END

- SEC. OND END
-TIR: TERMINAL, TOP, RIGHT
-TIL: TERMINAL, TOP, LEFT
-TBR: TERMINAL, BOTTOM, RIGHT
-STR: SOCKET, TOP, RIGHT
-STR: SOCKET, TOP, LEFT
-SBR: SOCKET, BOTTOM, RIGHT
-SBR: SOCKET, BOTTOM, RIGHT

-SBL: SOCKET, BOTTOM, LEFT -TEU: TERMINAL, EDGEMOUNT, UP -TED: TERMINAL, EDGEMOUNT, DOWN

\*-B: BOTH END'S SQUEEZE LATCH

C: BOTH ENDS SCREW OPTION


ERDP-XXX-XX.XX-XXX-XXX-X


BY: J. BORGELT 1/21/2008 | SHEET 1 OF 6


-S GOLD: 30µ" CONTACT


### **REVISION Z**


## **FIRST END**


























### PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRETARY INFORMATION AND ALL DESIGN. AMAUNTACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMITEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENS OF SAMITEC, IN

samlec

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

DO NOT SCALE DRAWING


CUSTOM HDR CABLE ASSEMBLY


VG. NO.


ERDP-XXX-XX.XX-XXX-XXX-X-X


# **SECOND END**





























### PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS


520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

DO NOT SCALE DRAWING

CUSTOM HDR CABLE ASSEMBLY


ERDP-XXX-XX.XX-XXX-XXX-X-X BY: J. BORGELT 1/21/2008 SHEET 3 OF 6


SHEET SCALE: 1:1



						-L	-03-XX
						-R	-03-XX
			TABLE4			-D	-03-X
			SUB-ERDP-X-XXX-03-XX-X	WIRING	OPTION	-B	-03-XX
# OF POSITIONS	"C"	XCD-XX-03				-N	-03-X
			(SEE TABLE 9 FOR LATCH CONFIG.)	-1, -2, -3, -4	-5, -6, -7, -8	-F	-03-XX
-013	.977[24.82]	ECD-13-03	SUB-ERDP-X-013-03-XX-X	SUB-TTF-	SUB-TTF-	-S	-03-X
-025	1.324[33.63]	ECD-25-03	SUB-ERDP-X-025-03-XX-X	30100XX-XX-01		-C	-03-XX
-049	2.080[52.83]	ECD-49-03	SUB-ERDP-X-049-03-XX-X	XX.XX	01-XX.XX	-G	-03-XX
							00.10

	SUB-ER	DP-T-XXX-03-XX-	XXX	DOW-0469-1250-01	LCT-16-01	CPS-4-40-11-X
	END OPTION	END 1	END 2	QTY	QTY	QTY
	-L	-03-XX-DSL	-03-XX-DSB	2	2	0
	-R	-03-XX-DSB	-03-XX-DSL	2	2	0
	<b>-</b>	-03-XX-DSL	-03-XX-DSL	0	0	0
	-B	-03-XX-DSB	-03-XX-DSB	4	4	0
4	-N	-03-XX-DSL	-03-XX-DSL	0	0	0
3	-F	-03-XX-DSB	-03-XX-DSL	0	0	2
	-S	-03-XX-DSL	-03-XX-DSB	0	0	2
K-	- O	-03-XX-DSB	-03-XX-DSB	0	0	4
	-G	-03-XX-DSB	-03-XX-DSB	2	2	2
	-Τ	-03-XX-DSB	-03-XX-DSB	2	2	2





ECD-25-03-CPS

ECD-49-03-CPS

## PROPRIETARY NOTE PROPRIETARY INFORMATION AND ALL DESIGN. MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,

1.562 [39.6748]

2.318 [58.8772]

-025

-049

OR PART. TO ANY UNAUTHORIZED PERSON OR ENTITY NO REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

30100XX-XX-

01-XX.XX

30100CU-XX-

01-XX.XX

DO NOT SCALE DRAWING

CUSTOM HDR CABLE ASSEMBLY

1.798 [45.6692]

2.554 [64.8716]

ERDP-XXX-XX.XX-XXX-XXX-X BY: J. BORGELT 1/21/2008 | SHEET 4 OF 6

SHEET SCALE: 1:1





	TABLE 11											
# OF POSITIONS	"J"	TOP HOUSING (PIN 1 SIDE)	BOTTOM HOUSING	SUB-ERDP-X-XXX-03-XX-X (SEE TABLE 7 FOR PINOUT AVAILABILITY) (SEE TABLE 12 FOR LATCH	WIRING	G OPTION						
				CONFIG)	-12, -3, -4	-5, -6, -7, -8						
-013	1.064[27.03]	ERH-13-03-T	ERH-13-03-B	SUB-ERDP-X-013-03-XX-X	SUB-TTF-	SUB-TTF-						
-025	1.442[36.64]	ERH-25-03-T	ERH-25-03-B	SUB-ERDP-X-025-03-XX-X	30100XX-XX-	30100CU-XX-01-						
-049	2.197[55.83]	ERH-49-03-T	ERH-49-03-B	SUB-ERDP-X-049-03-XX-X	01-XX.XX	XX.XX						

	TABLE 12											
	SUB-XRDP	-X-XXX-03-XX-X	LTC-16-01	CPS-4-40-11-X								
LATCH OPTION	FND 1	END 2	QUANTITY	QUANTITY								
-1	-03-XX-DSB	-03-XX-DSB	4	0								
-2	-03-XX-DSL	-03-XX-DSB	2	0								
-3	-03-XX-DSB	-03-XX-DSL	2	0								
-4	-03-XX-DSB	-03-XX-DSB	2	2								
-5	-03-XX-DSB	-03-XX-DSB	2	2								



**REVISION Z** 

							TABLE7										
FIRST	FIRST END	WIRING	FIRST	SECOND	WRE			SECOND END OF	TION (SUB-ERDF	-x-xxx-xx-x	X-XXX)						
END OPTION	SUB-ERDP-X-XXX-XX-01- XXX	OPTION	END PIN#	END PIN#	#	-TTR	-™	-TBR	-TBL	-STR	-STL	-SBR	-SBL	-TEU	-TED		
		-1/-5	1	1	T1	-T-XXX-02-02-XXX	N/A	N/A	-T-XXX-01-02-XXX	N/A	-S-XXX-01-01-L	-S-XXX-02-01-L	N/A	N/A	-T-XXX-03-02-XXX		
	T VVV 04 04 VVV	-2/-6	1	2	T1	-T-XXX-02-01-XXX	N/A	N/A	-T-XXX-01-01-XXX	N/A	-S-XXX-01-02-L	-S-XXX-02-02-L	N/A	N/A	-T-XXX-03-01-XXX		
-TTR	-T-XXX-01-01-XXX	-3/-7	1	N-1	T1	N/A	-T-XXX-01-01-XXX	-T-XXX-02-01-XXX	N/A	-S-XXX-02-02-L	N/A	N/A	-S-XXX-01-02-L	-T-XXX-03-01-XXX	N/A		
		-4/-8	1	N	T1	N/A	-T-XXX-01-02-XXX	-T-XXX-02-02-XXX	N/A	-S-XXX-02-01-L	N/A	N/A	-S-XXX-01-01-L	-T-XXX-03-02-XXX	N/A		
		-1/-5	1	1	B20	N/A	-T-XXX-01-02-XXX	-T-XXX-02-02-XXX	N/A	-S-XXX-02-01-L	N/A	N/A	-S-XXX-01-01-L	-T-XXX-03-02-XXX	N/A		
	T VVV 02 04 VVV	-2/-6	1	2	B20	N/A	-T-XXX-01-01-XXX	-T-XXX-02-01-XXX	N/A	-S-XXX-02-02-L	N/A	N/A	-S-XXX-01-02-L	-T-XXX-03-01-XXX	N/A		
-TTL	-T-XXX-02-01-XXX	-3/-7	1	N-1	B20	-T-XXX-02-01-XXX	N/A	N/A	-T-XXX-01-01-XXX	N/A	-S-XXX-01-02-L	-S-XXX-02-02-L	. N/A	N/A	-T-XXX-03-01-XXX		
		-4/-8	1	N	B20	-T-XXX-02-02-XXX	N/A	N/A	-T-XXX-01-02-XXX	N/A	-S-XXX-01-01-L	-S-XXX-02-01-L	. N/A	N/A	-T-XXX-03-02-XXX		
		-1/-5	1	1	B20	N/A	-T-XXX-01-02-XXX	-T-XXX-02-02-XXX	N/A	-S-XXX-02-01-L	N/A	N/A	-S-XXX-01-01-L	-T-XXX-03-02-XXX	N/A		
TDD	T VVV 04 04 VVV	-2/-6	1	2	B20	N/A	-T-XXX-01-01-XXX	-T-XXX-02-01-XXX	N/A	-S-XXX-02-02-L	N/A	N/A	-S-XXX-01-02-L	-T-XXX-03-01-XXX	N/A		
-TBR	-T-XXX-01-01-XXX	-3/-7	1	N-1	B20	-T-XXX-02-01-XXX	N/A	N/A	-T-XXX-01-01-XXX	N/A	-S-XXX-01-02-L	-S-XXX-02-02-L	N/A	N/A	-T-XXX-03-01-XXX		
		-4/-8	1	N	B20	-T-XXX-02-02-XXX	N/A	N/A	-T-XXX-01-02-XXX	N/A	-S-XXX-01-01-L	-S-XXX-02-01-L	N/A	N/A	-T-XXX-03-02-XXX		
		-1/-5	1	1	T1	-T-XXX-02-02-XXX	N/A	N/A	-T-XXX-01-02-XXX	N/A	-S-XXX-01-01-L	-S-XXX-02-01-L	. N/A	N/A	-T-XXX-03-02-XXX		
-TBL	T VVV 02 04 VVV	-2/-6	1	2	T1	-T-XXX-02-01-XXX	N/A	N/A	-T-XXX-01-01-XXX	N/A	-S-XXX-01-02-L	-S-XXX-02-02-L	. N/A	N/A	-T-XXX-03-01-XXX		
- IBL	-T-XXX-02-01-XXX	-1-XXX-02-01-XXX	-1-XXX-02-01-XXX	-3/-7	1	N-1	T1	N/A	-T-XXX-01-01-XXX	-T-XXX-02-01-XXX	N/A	-S-XXX-02-02-L	N/A	N/A	-S-XXX-01-02-L	-T-XXX-03-01-XXX	N/A
		-4/-8	1	N	T1	N/A	-T-XXX-01-02-XXX	-T-XXX-02-02-XXX	N/A	-S-XXX-02-01-L	N/A	N/A	-S-XXX-01-01-L	-T-XXX-03-02-XXX	N/A		
		-1/-5	1	1	T20	N/A	-T-XXX-01-01-XXX	-T-XXX-02-01-XXX	N/A	-S-XXX-02-02-L	N/A	N/A	-S-XXX-01-02-L	-T-XXX-03-01-XXX	N/A		
OTD	-S-XXX-01-01-L	-2/-6	1	2	T20	N/A	-T-XXX-01-02-XXX	-T-XXX-02-02-XXX	N/A	-S-XXX-02-01-L	N/A	N/A	-S-XXX-01-01-L	-T-XXX-03-02-XXX	N/A		
-STR		-3/-7	1	N-1	T20	-T-XXX-02-02-XXX	N/A	N/A	-T-XXX-01-02-XXX	N/A	-S-XXX-01-01-L	-S-XXX-02-01-L	N/A	N/A	-T-XXX-03-02-XXX		
		-4/-8	1	N	T20	-T-XXX-02-01-XXX	N/A	N/A	-T-XXX-01-01-XXX	N/A	-S-XXX-01-02-L	-S-XXX-02-02-L	N/A	N/A	-T-XXX-03-01-XXX		
		-1/-5	1	1	B1	-T-XXX-02-01-XXX	N/A	N/A	-T-XXX-01-01-XXX	N/A	-S-XXX-01-02-L	-S-XXX-02-02-L	. N/A	N/A	-T-XXX-03-01-XXX		
ОТ.	0 777 00 04 1	-2/-6	1	2	B1	-T-XXX-02-02-XXX	N/A	N/A	-T-XXX-01-02-XXX	N/A	-S-XXX-01-01-L	-S-XXX-02-01-L	N/A	N/A	-T-XXX-03-02-XXX		
-STL	-S-XXX-02-01-L	-3/-7	1	N-1	B1	N/A	-T-XXX-01-02-XXX	-T-XXX-02-02-XXX	N/A	-S-XXX-02-01-L	N/A	N/A	-S-XXX-01-01-L	-T-XXX-03-02-XXX	N/A		
		-4/-8	1	N	B1	N/A	-T-XXX-01-01-XXX	-T-XXX-02-01-XXX	N/A	-S-XXX-02-02-L	N/A	N/A	-S-XXX-01-02-L	-T-XXX-03-01-XXX	N/A		
		-1/-5	1	1	B1	-T-XXX-02-01-XXX	N/A	N/A	-T-XXX-01-01-XXX	N/A	-S-XXX-01-02-L	-S-XXX-02-02-L	. N/A	N/A	-T-XXX-03-01-XXX		
-SBR	-S-XXX-01-01-L	-2/-6	1	2	B1	-T-XXX-02-02-XXX	N/A	N/A	-T-XXX-01-02-XXX	N/A	-S-XXX-01-01-L	-S-XXX-02-01-L	. N/A	N/A	-T-XXX-03-02-XXX		
-SBK	-5-XXX-01-01-L	-3/-7	1	N-1	B1	N/A	-T-XXX-01-02-XXX	-T-XXX-02-02-XXX	N/A	-S-XXX-02-01-L	N/A	N/A	-S-XXX-01-01-L	-T-XXX-03-02-XXX	N/A		
		-4/-8	1	N	B1	N/A	-T-XXX-01-01-XXX	-T-XXX-02-01-XXX	N/A	-S-XXX-02-02-L	N/A	N/A	-S-XXX-01-02-L	-T-XXX-03-01-XXX	N/A		
		-1/-5	1	1	T20	N/A	-T-XXX-01-01-XXX	-T-XXX-02-01-XXX	N/A	-S-XXX-02-02-L	N/A	N/A	-S-XXX-01-02-L	-T-XXX-03-01-XXX	N/A		
-SBL	-S-XXX-02-01-L	-2/-6	1	2	T20	N/A	-T-XXX-01-02-XXX	-T-XXX-02-02-XXX	N/A	-S-XXX-02-01-L	N/A	N/A	-S-XXX-01-01-L	-T-XXX-03-02-XXX	N/A		
-SBL	-S-XXX-02-01-L	-3/-7	1	N-1	T20	-T-XXX-02-02-XXX	N/A	N/A	-T-XXX-01-02-XXX	N/A	-S-XXX-01-01-L	-S-XXX-02-01-L	. N/A	N/A	-T-XXX-03-02-XXX		
		-4/-8	1	N	T20	-T-XXX-02-01-XXX	N/A	N/A	-T-XXX-01-01-XXX	N/A	-S-XXX-01-02-L	-S-XXX-02-02-L	. N/A	N/A	-T-XXX-03-01-XXX		
		-1/-5	1	1	T1	-T-XXX-02-02-XXX	N/A	N/A	-T-XXX-01-02-XXX	N/A	-S-XXX-01-01-L	-S-XXX-02-01-L	N/A	N/A	-T-XXX-03-02-XXX		
-TEU	T VVV 02 04 VVV	-2/-6	1	2	T1	-T-XXX-02-01-XXX	N/A	N/A	-T-XXX-01-01-XXX	N/A	-S-XXX-01-02-L	-S-XXX-02-02-L	N/A	N/A	-T-XXX-03-01-XXX		
- 120	-T-XXX-03-01-XXX	-3/-7	1	N-1	T1	N/A	-T-XXX-01-01-XXX	-T-XXX-02-01-XXX	N/A	-S-XXX-02-02-L	N/A	N/A	-S-XXX-01-02-L	-T-XXX-03-01-XXX	N/A		
		-4/-8	1	N	T1	N/A	-T-XXX-01-02-XXX	-T-XXX-02-02-XXX	N/A	-S-XXX-02-01-L	N/A	N/A	-S-XXX-01-01-L	-T-XXX-03-02-XXX	N/A		
		-1/-5	1	1	B20	N/A	-T-XXX-01-02-XXX	-T-XXX-02-02-XXX	N/A	-S-XXX-02-01-L	N/A	N/A	-S-XXX-01-01-L	-T-XXX-03-02-XXX	N/A		
T-0	T VVV 02 04 VVV	-2/-6	1	2	B20	N/A	-T-XXX-01-01-XXX	-T-XXX-02-01-XXX	N/A	-S-XXX-02-02-L	N/A	N/A	-S-XXX-01-02-L	-T-XXX-03-01-XXX	N/A		
-TED	-T-XXX-03-01-XXX	-3/-7	1	N-1	B20	-T-XXX-02-01-XXX	N/A	N/A	-T-XXX-01-01-XXX	N/A	-S-XXX-01-02-L	-S-XXX-02-02-L	. N/A	N/A	-T-XXX-03-01-XXX		
		-4/-8	1	N	B20	-T-XXX-02-02-XXX	N/A	N/A	-T-XXX-01-02-XXX	N/A	-S-XXX-01-01-L	-S-XXX-02-01-L	. N/A	N/A	-T-XXX-03-02-XXX		

	TABLE 8											
DI	DIFFERENTIAL PAIR PINOUT (DOES NOT ACCOUNT FOR CABLE WIRING OPTION)											
1	3	5	7	9	11	13		N-7	N-5	N-3	N-1	
GND	DIFF	PAIR	GND DIFF PAIR		GND		GND	DIFF	PAIR	GND		
GND	DIFF PAIR		GND	DIFF PAIR		GND		GND	DIFF	PAIR	GND	
2	4	6	8	10	12	14		N-6	N-4	N-2	N	

NOTE: CONNECTOR LATCHES ARE TIED TO GROUND SQUEEZE LATCHES ARE NOT GROUND

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTE, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ARY UNAUTHORIZED PERSON OR ENTITY YOUR REPRODUCED, TRANSFERRED OR HOORPOORATE IN MANY OTHER PROJECT IN ANY MANINER WITHOUT THE EXPRESS WRITTEN CONSINT OF SAMTE, IN.

Sam lec

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

DO NOT SCALE DRAWING

DESCRIPTION: CUSTOM HDR CABLE ASSEMBLY

....

ERDP-XXX-XX.XX-XXX-XXX-X

SHEET SCALE: 1:1

BY: J. BORGELT 1/21/2008 SHEET 6 OF 6