

- 1. PARTS MAY BE CUT TO POSITION; .010 MAX CUT FLASH © 2. SHEAR TAILS TO DIMENSION SHOWN; .003 MAX BURR.
 - NOTE DELETED.
 - 4. © REPRESENTS A CRITICAL DIMENSION.
 - 5. NOTE DELETED.
 - 6. NOTE DELETED.
 - 7. POSITIONS -02 THRU -04 TO BE LAYER PACKAGED, AND POSITIONS -05 THRU -50 TO BE TUBE PACKAGED.
 - 8. PARTS WITH -S OPTION ARE TO APPEAR AS SHOWN IN FIG 2
- OR FIG 6 AT SAMTEC'S DISCRETION.

 9. 4 POSITIONS MUST BE ADDED TO PART CALL OUT TO ALLOW FOR PUSH ON SHROUDS. EX: FTM-125-02-L-DV-S REQUIRES A 29 POSITION STRIP.

 10. MINIMUM PUSHOUT FORCE: .5 LB (8 OZ)
- 11. TUBES ARE STANDARD PACKAGING.
- 12. ORDERS WILL BE PACKAGED ACCORDING TO THE SAMTEC PACKAGING EFFICIENCY STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM.
- 13. ATTACH LABÈL TO EACH REEL.

TABLE 1		
LEAD STYLE	"A"	TERMINAL
-02	.075 [1.91]	T-1S16-03-XX-2
-03	.065 [1.65]	T-1S16-04-XX-2

FIG 1 FTM-1XX-02-X-DV SHOWN

PATENT NUMBERS 5655914 / 5785536

CKITICAL DIMENSION INSTECTION INSTRUCTION TABLE			
ASSEMBLY OPERATION	IN PROCESS INSPECTION		
AUTO FILL T-1S16-XX-XX-2	C1, C3, C5, C6, C8		
HAND FILL	C1, C3		
SHEAR	C8		
RE-PRESS	C1, C3, C5, C6		
CUT TO POSITION	C2, C7		
INSTALL FEM	C9, C10, C16		
INSTALL FEM-A	C12		
INSTALL PICK AND PLACE PAD	C13		

CPC'S INTENTIALLY DELETED: C4, C11, C14, C15

UNLESS OTHERWISE SPECIFIED. DIMENSIONS ARE IN INCHES. TOLERANCES ARE:

DECIMALS

MATERIAI -

TERMINAL: PHOS BRONZE

ANGLES .XX: ±.01 [.3] .XXX: ±.005 [3° .13] .XXXX: ±.0020 [.051]

PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC INC

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com

DO NOT SCALE DRAWING

BODY: VECTRA E130 COLOR: BLACK

MAX FLASH ALLOWED: .002 [.05] MAX GATE VESTIGE ALLOWED: .002 [.05]

1mm x 1mm LOW PROFILE SMT STRIP ASM

FTM-1XX-XX-XX-DV-XX-X-XX

BY: B MENEAR 2/13/2006 SHEET 1 OF 3

F:\DWG\MISC\MKTG\FTM-1XX-XX-XX-DV-XX-X-XX-MKT.SLDDRW







FIG 4 (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1) REVISION BW (SEE NOTE) "P" (SEE NOTE) .200 [5.08] REF .125 [3.18]








IN-PROCESS 3


PACKAGING VIEW


(SEE NOTE 7)


PACKAGING TABLE **OPTIONS** PACKAGING TUBE PLUGS W/0 OPTION PT-1-24-01-49 TP-30 PT-1-24-01-43 TP-24 -S, -S-P, -SA, -SA-P PT-1-24-13-09 TP-24

ONLY POSITIONS -05 THRU -50 ARE TO BE TUBED. POSITIONS -02 THRU -04 TO BE LAYER PACKAGED ONLY. INSERT PLUG TP-30 AT AN ANGLE INTO PT-1-24-01-49, PLUG MUST SUPPORT THE INSULATOR.









F:\DWG\MISC\MKTG\FTM-1XX-XX-XX-DV-XX-X-XX-MKT.SIDDRW

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com

SHEET SCALE: 4:1

1mm x 1mm LOW PROFILE SMT STRIP ASM

FTM-1XX-XX-XX-DV-XX-X-XX

BY: B MENEAR 2/13/2006 SHEET 3 OF 3