






c







CREATED

971110385 8,0 7,0 M3.0 SW8 11 971120385 12 8,0 9.0 M 3.0 SW 8 971130385 13 8,0 9.0 M 3.0 SW 8 9,0 14 SW 8 971140385 8,0 M 3.0 971150385 15 10,0 M 3.0 SW 8 8,0 SW 8 971600385 60 8.0 10.0 M 3.0 971070485 8,0 3,5 M 4.0 SW 8 SW 8 971080485 8 8,0 5,0 M 4.0 9 8,0 6,0 M 4.0 SW 8 971090485 971100485 10 8,0 M 4.0 SW 8 7,0 971110485 11 8,0 8,0 M 4.0 SW 8 971120485 12 8,0 9,0 M 4.0 SW 8 971130485 13 8,0 10,0 M 4.0 SW 8 971150485 15 8,0 10,0 M 4.0 SW 8 971200485 20 8,0 10,0 M 4.0 SW 8 971250485 25 8,0 10,0 M 4.0 SW 8 971300485 30 10,0 8,0 M 4.0 SW 8 971350485 35 8,0 10,0 M 4.0 SW 8 SW 8 971400485 40 8,0 10,0 M 4.0 SW 8 45 M 4.0 971450485 8,0 10,0 SW 8 971500485 50 8,0 10,0 M 4.0 971650485 65 8,0 10,0 M 4.0 SW 8 GENERAL TOLERANCE PROJECTION METHOD SCALE 4 . 1 DIN 100 0700 4

ΤI

(mm)

3,5

4,0

5,0

6,0

7,0

8,0

9,0

10,0

10,0

10,0

10,0

10,0

10,0

3.0

3,5

5,0

7,0

7,0

9,0

9,0

9,0

10,0

10,0

10,0

10,0

10,0

10,0

10,0

10,0

10,0

10.0

3,5

3,5

5,0

5.0

7.0

Thread

Size M 2.5

M 3.0

SW

SW 5

SW₆

SW 6

SW 6 SW₆

SW 6

SW₆ SW 6

SW 6

SW 6

SW 6

SW 6

SW 6

SW 8

SW 8

SW 8

SW 8

SW 8

G

(mm)

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8,0

8.0

8,0

8,0

8,0

8.0

8.0

(mm)

5

6

7

8

9

10

11

12

15

20

18

20

45

5

6

8

10

11

12

13

14

15

16

17

18

20

25

30

35

40

50

6

8

9

10

Order Code

971050155

971060155

971070155

971080155

971090155

971100155

971110155

971120155

971150155

971160155

971180155

971200155

971450155

971050365

971060365

971080365

971100365

971110365

971120365

971130365

971140365

971150365

971160365

971170365 971180365

971200365

971250365

971300365

971350365 971400365

971500365

971060385

971070385

971080385

971090385

971100385

Würth Elektronik eiSos GmbH & Co. KG **EMC & Inductive Solutions**

Flammability according to: UL94-HB

Max-Eyth-Str. 1 74638 Waldenburg Germany com. +49 79 42 945 - 0

www.we-online.de eiSos@we-online.de



	Dar	SKI	DIN 150 2768-	ım			4:1
	DESCRIPTION	•		MATERIAL			
	AsSPalE Plastic Spacer Stud			PA66, black			
				ORDER CODE			
<u>-</u>	Metric Thread int./ext.			971 xxx xx5			
<u>-</u>	SIZE	WEIGHT	STATUS	DATE		BUSINESS UNIT	PAGE
)- IK	xxx xxx xxx	xxx	Released	2014-12	-08	eiCan	1 /1

CHECKED

CIZI