


DO NOT SCALE FROM THIS PRINT






TABLE 2			
STYLE	OPTION	TERMINAL	CONTACT
-01		T-1S13-20-XXX-2	C-79-01-XXX
	-RA1	T-1S13-03-XXX-2	C-79-12-XXX
	-RA2	T-1S13-10-XXX-2	C-79-12-XXX
-02		T-1S13-13-XXX-2	C-79-12-XXX

NOTES:

- 1. © REPRESENTS A CRITICAL DIMENSION.
- 2. BURR ALLOWANCE: .003[.08] MAX.
- 3. MAXIMUM CUT FLASH: .015[.38].
 4. MINIMUM PUSHOUT FORCE; TERMINALS: 2 LBS, CONTACTS: .5 LBS.
- 5. MAXIMUM ALLOWABLE BOW: .002 INCH/INCH AFTER ASSEMBLY. 6. SEE APPLICATION VIEWS (SHEET 3) FOR POSITION 01 LOCATION.
- . ALL PIN TO PIN DIMENSIONS TO BÉ MEASURED FROM TIP TO TIP.
- 8. DIMENSION TO BE MEASURED AT BEND. 9. SHEAR TAILS TO DIMENSION SHOWN.
- 10. TUBES ARE STANDARD PACKAGING.
- 11. ORDERS WILL BE PACKAGED ACCORDING TO THE SAMTEC
- PACKAGING EFFICIENCY STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM 12. ATTACH LABEL TO EACH REEL

LS2-1XX-XX-XX-D-XXX-X-XX

No OF POSITIONS -05, -10, -15, -20, -25, -30 (PER ROW)

LEAD STYLE

-01: THROUGH HOLE -02: SURFACE MOUNT

PLATING SPECIFICATION

(USE T-1S13-XX-F-2 & C-79-XX-F) -FM: FLASH SELECTIVE GOLD

(USE T-1S13-XX-F-2 & C-79-XX-F) -L: LIGHT SELECTIVE GOLD

(USE T-1S13-XX-L-2 & C-79-XX-L) -LM: LIGHT SELECTIVE GOLD

MATTE TIN REMAINDER (USE T-1S13-XX-L-2 & C-79-XX-L) -S: SELECTIVE GOLD (USE T-1S13-XX-S-2 & C-79-XX-S)

-SM: SELECTIVE GOLD MATTE TIN REMAINDER

(USE T-1S13-XX-S-2 & C-79-XX-S) G: GOLD


(USE T-1S13-XX-G-2 & C-79-XX-G) -H: HEAVY GOLD (USE T-1S13-XX-H-2 & C-79-XX-H)

-TR: TAPE & REEL (SEE NOTE 11 & 12) -FR: FULL REEL QTY TAPE & REEL (SEE NOTE 11 & 12) PICK & PLACE -K: POLYIMIDE FILM PAD (USE K-DOT-.246-.375-.005, SEE FIG 5) [LEAD STYLE -02 ONLY] (SEE FIG 2) **OPTION** -A: ALIGNMENT PIN (USE LS2-XX-D-XX-A, SEE FIG 6) -F: FLASH SELECTIVE GOLD ÎLEAD STYLE -02 ONLYI TAIL OPTION MATTE TIN REMAINDER -RA1: RIGHT ANGLE-SHROUD DOWN (SEE FIG 3) -RA2: RIGHT ANGLE-SHROUD UP (SEE FIG 4) [AVAILABLE ONLY ON LEAD STYLE -01]

> **ROW SPECIFICATION** -D: DOUBLE (USE LS2-XX-D-XX)

PACKAGING

BLANK: TUBES (SEE NOTE 10)



SECTION "A"-"A"

UNLESS OTHERWISE SPECIFIED. DIMENSIONS ARE IN INCHES. TOLERANCES ARE:

DECIMALS **ANGLES** .XX: ±.01 [.3] .XXX: ±.005 [.13] .XXXX: ±.0020 [.051]

PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS

AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS

DO NOT SCALE DRAWING

F:\DWG\MISC\MKTG\LS2-1XX-XX-D-XXX-X-X-XX-MKT.SLDDRW

INSULATOR: LCP, COLOR: BLACK SOCKET: PHOS BRONZE TERMINAL: PHOS BRONZE

SHEET SCALE: 3:1

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com


DESCRIPTION


2mm TERMINAL/SOCKET COMBO


LS2-1XX-XX-XX-D-XXX-X-XX

BY: DEAN P


4/24/2002 SHEET 1 OF 4








PACKAGING VIEWS




TUBE: PT-1-24-04-09 PLUG: TP-07

STYLE -02




TUBE: PT-1-24-01-123 PLUG: TP-03

STYLE -01-RA1



TUBE: PT-1-24-01-124 PLUG: TP-07

STYLE -01-RA2



TUBE: PT-1-24-01-124 PLUG: TP-07

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 3:1




520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com


DESCRIPTION:


2mm TERMINAL/SOCKET COMBO

LS2-1XX-XX-XX-D-XXX-X-XX BY: DEAN P

4/24/2002 SHEET 2 OF 4










STYLE-01-RA1 PACKAGING VIEW

PARTS MUST BE ORIENTED PER THE DESIGN OF THE POCKET AND POCKET TOOL. POCKETS DESIGNED AFTER REVISION Q MUST ORIENT PARTS PER THIS VIEW.




PARALLEL

BOARD-TO-BOARD

PERPENDICULAR

BOARD-TO-BOARD



IN-LINE PARALLEL BOARD-TO-BOARD

BOARD-TO-BOARD

F:\DWG\MISC\MKTG\LS2-1XX-XX-XX-D-XXX-X-X-XX-MKT.SLDDRW

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS

DO NOT SCALE DRAWING

PROPRIETARY NOTE

SHEET SCALE: 3:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:

2mm TERMINAL/SOCKET COMBO

DWG. NO.
LS2-1XX-XX-XX-D-XXX-X-X-XX
BY: DEAN P 4/24/2002 SHEET 3 OF 4

