


REVISION BQ








FIG 2 -LC: LOCKING CLIP OPTION (QSE-060-01-XXX-D-LC SHOWN) (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)

TABLE 3								
No OF POS	"R"				"S"			
	-LC, -A, -FL	-GP	-RT1	-L	-LC, -A, -FL	-GP	-RT1	-L
-020	.839 [21.31]	1.216 [30.89]	1.438 [36.51]	1.048 [26.61]	.257 [6.53]	.446 [11.32]	.556 [14.13]	.361 [9.18]
-040	1.627 [41.31]	2.004 [50.89]	2.225 [56.52]	1.835 [46.61]	.651 [16.53]	.839 [21.32]	.950 [24.13]	.755 [19.18]
-060	2.417 [61.38]	2.791 [70.89]	3.013 [76.52]	N/A	1.046 [26.56]	1.233 [31.32]	1.344 [34.13]	N/A
*-080	3.204 [81.38]	3.579 [90.89]	3.800 [96.52]	N/A	1.440 [36.56]	1.627 [41.32]	1.738 [44.13]	N/A
*-100	3.991 [101.37]	4.366 [110.90]	N/A	N/A	1.833 [46.56]	2.021 [51.32]	N/A	N/A

(*= SEE NOTE 17)



F:\DWG\MISC\MKTG\QSE-XXX-01-XXX-D-XXX-XX-XX-MKT.SLDDRW







TABLE 4				
POS	"C"	"D"		
-020	1.216 [30.89]	1.013 [25.72]		
-040	2.004 [50.89]	1.800 [45.72]		
-060	2.791 [70.89]	2.588 [65.72]		
*-080	3.579 [90.89]	3.375 [85.73]		
*-100	4.366 [110.90]	4.163 [105.73]		

(*= SEE NOTE 17)

FIG 4
-GP: GUIDE POST OPTION
(QSE-060-01-XXX-D-A-GP SHOWN)
(DIFFERNT AS SHOWN, OTHERWISE SAME AS FIG 1)
(40 POS MAX WITH T & R PACKAGING)






TABLE 5			
POS	"E"	"F"	
-020	1.438 [36.51]	1.129 [28.66]	
-040	2.225 [56.52]	1.916 [48.67]	
-060	3.013 [76.52]	2.704 [68.67]	
*-080	3.800 [96.52]	3.491 [88.67]	
*-100	N/A	N/A	

(*= SEE NOTE 17)





FIG 6 -RT1: RETENTION OPTION (QSE-060-01-XXX-D-A-RT1 SHOWN) (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1) (MUST USE -A OPTION) (NOT AVAILABLE WITH -LC, -GP, OR -FL OPTIONS) (NOT AVAILABLE WITH -100 POS)







FIG 7 -L: LATCHING OPTION (QSE-040-01-XXX-D-A-L SHOWN) (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1) (MUST USE -A OPTION) (40 POS MAX) (NOT AVAILABLE WITH -LC, -GP, -FL, OR -RT1 OPTIONS)

F:\DWG\MISC\MKTG\QSE-XXX-01-XXX-D-XXX-XX-XX-MKT.SLDDRW

TABLE 6				
POS	"G"	"H"	"J"	
-020	1.048 [26.61]	.897 [22.78]	.959 [24.36]	
-040	1.835 [46.61]	1.684 [42.78]	1.747 [44.36]	
-060	N/A	N/A	N/A	
*-080	N/A	N/A	N/A	
*-100	N/A	N/A	N/A	

(*= SEE NOTE 17)



* PROPRIETARY NOTE *	
THIS DOCUMENT CONTAINS CONFIDENTIAL AND	
PROPRIETARY INFORMATION AND ALL DESIGN,	
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS	
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,	
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE	
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR	520 PARK EAST BLVD, NEW ALBANY, IN 47150
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY	
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS	PHONE: 812-944-6733 FAX: 812-948-5047
WRITTEN CONSENT OF SAMTEC, INC.	e-Mail info@SAMTEC.com code 55322

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

DESCRIPTION:


.8mm DOUBLE ROW HS SOCKET ASSEMBLY

DWG. NO. QSE-XXX-01-XXX-D-XXX-XX-XX

BY: ERIC M

05/20/1999 SHEET 4 OF 5

FIG 8
-TR: PACKAGING OPTION
(QSE-060-01-XXX-D-LC-TR SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)
(60 POS MAX)
(40 POS MAX WITH -GP OPTION)



USER DIRECTION OF UNREELING POCKET NOT DETAILED



* PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,

INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS

WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

.8mm DOUBLE ROW HS SOCKET ASSEMBLY

SHEET SCALE: 2:1

DWG. NO.

QSE-XXX-01-XXX-D-XXX-XX-XX

520 PARK EAST BLVD, NEW ALBANY, IN 47150

PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

BY: ERIC M 05/20/1999 SHEET 5 OF 5

F:\DWG\MISC\MKTG\QSE-XXX-01-XXX-D-XXX-XX-XX-MKT.SLDDRW