
REVISION CK

DO NOT SCALE FROM THIS PRINT

NOTES:

- 1. © REPRESENTS A CRITICAL DIMENSION.
- 2. MINIMUM PUSHOUT FORCE: .5 LB. (C) 3. COPLANARITY: .004[0.10] = POS 02 THRU 26 .006[0.15] = POS 27 THRU 50 4. TUBE PACKAGE ONLY POSITIONS -04 THRU -50;
 - LAYER PACKAGE POSITIONS -02 THRU -03.
 - 5. MAXIMUM CUT FLASH TO BE: .010 (NO FLASH EXTENDING BELOW LEADS OR IN HOLES OF BODY.
- (C) 6. MAXIMUM PIN HEIGHT VARIATION: .003[0.08] FROM PIN TO PIN AND ROW TO ROW, MUST BE MEASURED BETWEEN ADJACENT PINS
 - 7. PINS CAN BE ORIENTED IN ANY DIRECTION; BOTH ROWS MUST FACE SAME WAY.
 - 8. DIMENSION TO BE MEASURED AT BEND 9. MIXED PIN ORIENTATION ACCEPTABLE.
 - 10. ORDERS WILL BE PACKAGED ACCORDING TO THE SAMTEC PACKAGING EFFICIENCY STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM.
 - 11. ATTACH LABEL TO EACH REEL
 - 12. LOAD VISION TRAYS WITH PIN #1 OPPOSITE STANDARD -AWAY FROM THE TERMINAL INDICATOR SIDE OF TRAY.



SFMC-1XX-XX-XXX-D-XX-XX

No OF POSITIONS ALL POSITIONS AVAILABLE -02 THRU -50 (USE BODY: SFMC-50-D)

LEAD STYLE

- -01: THROUGH HOLE (USE CONTACT: C-44-01-XXX)
- SEE FIG 1, SHT 1) -02: SURFACE MOUNT
- (USE CONTACT: C-44-02-XXX) SEE FIG 2, SHT 2)
- -03: ŠTRAIGHT MODIFIED (USE CONTACT: C-44-03-XXX) SEE FIG 1, SHT 1)
- -L1: THROUGH HOLE (LOW INSERTION) (USE CONTACT: C-61-01-XXX) SEE FIG 1, SHT 1)
- -L2: SURFACE MOUNT (LOW INSERTION) (USE CONTACT: C`-61-02-XXX)
- (SEE FIG 2, SHT 2)
 -L3: STRAIGHT MODIFIED (LOW INSERTION)
 (USE CONTACT: C-61-03-XXX) SEE FIG 1, SHT 1)
- -T1: THROUGH HOLE (PHOS BRONZE) (USE CONTACT: C-119-01-XXX) SEE FIG 1, SHT 1)
- -T2: SURFACE MOUNT (PHOS BRONZE) (USE CONTACT: C-119-02-XXX) (SEE FIG 2, SHT 2)

PACKAGING

BLANK: TUBES (SEE NOTE 4) -TR: TAPE & REEL (SEE NOTÉS 10 & 11) -FR: FULL REEL QTY TAPE & REEL (SEE NOTES 10 & 11)

PICK & PLACE OPTION


(LEAVE BLANK FOR STANDARD

- -P: PICK AND PLACE PAD (SEE FIG 3, SHT 2) (USE PPP-02) (5 POSITION MINIMUM)
 -K: POLYIMIDE FILM PAD (.005[0.13] THICKNESS)
- (SEE FIG 4, SHT 2) (USE K-DOT-.157-.250-.005) (4 POSITION MINÍMUM)

BODY SPECIFICATION -D: DOUBLE ROW

PLATING SPECIFICATION

- -S: 30µ" SELECTIVE GOLD IN CONTACT AREA, MÄTTE TIN ON TAIL
- -F: 3µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- -H: 30µ" GOLD IN CONTACT AREA, 3µ" GOLD ON TAIL (ONLY AVAILABLE ON -02, -L2 & -T2 LEAD STYLE)
- -L: 10µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- -SM: 30µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- -FM: 3µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- -STL: 30µ" SELECTIVE GOLD IN CONTACT AREA, TIN/LEAD (90/10±5%) ON TAIL (ONLY AVAILABLE ON LEAD STYLES -02 & -L2)






FIG 1 -X1: THROUGH HOLE

SECTION "A"-"A" PROPRIETARY NOTE

TABLE 1		
SUFFIX	TAIL LENGTH "A"	TAIL WIDTH "B"
-X1	.120[3.05]	.020[0.51]
-X3	.075[1.91]	.016[0.41]

UNLESS OTHERWISE SPECIFIED. DIMENSIONS ARE IN INCHES. TOLERANCES ARE:

DECIMALS ANGLES .XX: ±.01 [.3] .XXX: ±.005 [.13] 2° .XXXX: ±.0020 [.051]

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING SHEET SCALE: 4:1 BODY: LCP UL 94V-O, COLOR: BLACK

CONTACTS: C-44 & C-61: #25 BeCu, 1/2 HARD C-119: PHOSPHOR BRONZE 521

F:\DWG\MISC\MKTG\SFMC-1XX-XX-XXX-D-XX-XX-MKT.slddrw




520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322


.050 x .050 CUTTABLE SOCKET STRIP DOUBLE ROW ASSEMBLY

SFMC-1XX-XX-XXX-D-XX-XX


BY: BRATCHER 10/5/94

SHEET 1 OF 3





PACKAGING VIEW
-TR: TAPE AND REEL SURFACE MOUNT



NOTES:

1. MIXED PIN ORIENTATION ACCEPTABLE.

TABLE 3 (SEE NOTE 4)			
LEAD STYLE	PACKAGING TUBE	PLUG	
-X1, -X3	PT-1-24-15-09	TP-12	
-X2	PT-1-24-14-09	TP-24-02	
-X2-K	PT-1-24-14-09	TP-24-02	
-X2-P	PT-1-24-01-38	TP-24	
ITEM DELETED			
-X1-P, -X3-P	PT-1-24-01-09	TP-24	
-X1-K, -X3-K	PT-SFM004-X1-X3-D	TP-24-02	

F:\DWG\MISC\MKTG\SFMC-1XX-XXX-D-XX-XXX-MKT.slddrv

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMFLE, INC. THIS DOCUMENT SHALL NOT BE OBCLOSED, IN WHOLE OF PART, TO ARY UNALTHORIZE PERSON OR ENTITY NOR REPRODUCED, TRANSFERED ON RIGHTS OF REPRODUCED, TRANSFERED ON RIGHTS OF REPRODUCED, TRANSFERED ON RIGHTS OF REPRODUCED THOS OF SAMFLE, INC. WRITTEN CONSENT OF SAMFLE, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1.5:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

DESCRIPTION:

.050 x .050 CUTTABLE SOCKET STRIP DOUBLE ROW ASSEMBLY

SFMC-1XX-XX-XXX-D-XX-XX

BY: BRATCHER 10/5/94

SHEET 3 OF 3