



N D	TABLE 1									
	LEAD STYLE	"A"	"B"	"C"	"D"	"E"	"F"			
	-2426	1.18	1.15	1.92	2.13	2.54	4.92			
	-2830	0.86	0.87	1.45	1.45	1.98	3.28			

TABLE 2												
P/N	AWG	"G"	"H"	"J"	"K"	"L"	"M" MAX	"N" MAX	PULL FORCE			
F/IN							(TAB LENGTH)	(VESTIGE LENGTH)	(LBS)			
T1M82-X-2426-01-XX	24	0.711	0.838	1.676	1.397	3.175	0.025	0.191	5			
1 11VIOZ-A-2420-01-AA	26	0.584	0.838	1.448	1.397	3.175	0.025	0.191	3			
T1M82-X-2830-01-XX	28	0.457	0.838	1.016	1.067	3.175	0.025	0.191	2			
1 11VIOZ-A-2030-0 1-AA	30	0.432	0.838	0.889	1.067	3.175	0.025	0.191	1.5			







UNWINDING DIRECTION

REVISIO

NOTES:


1. PLATED T-1M82 PARTS ARE TO BE UNWOUND, THEN REWOUND AND COUNTED, 17,000 ± 15 PCS, POSITIONED AS SHOWN ON SAMTEC REEL WITH VIEWPORTS, LABELED T1M82 WITH APPROPRIATE PLATING CALL OUT AND LABEL PLACED AS SHOWN.


2. MAXIMUM NO OF SPLICES PER REEL: 2. SPLICES ARE NOT TO BE CONNECTED.

NUMBER OF SPLICES TO BE MARKED ON EACH REEL.


3. REELED PARTS TO BE INTERLEAVED WITH PAPER BETWEEN EACH LAYER OF PARTS. ONE SPLICE IN INTERLEAF ALLOWED PER REEL. SECURELY CONNECT INTERLEAF SPLICE.

4. OUTER WRAP SHALL RECEIVE RB-24-0.75-P PROTECTITVE REEL BAND.





SCALE 20:1 WIRE CRIMP



INSULATION STRIP LENGTH

FIG 2 RECOMENDED PROCESSING

PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED. IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322

DO NOT SCALE DRAWING

SHEET SCALE: 8:1

DESCRIPTION

2mm C.L. DISCRETE WIRE TERMINAL

DWG. NO.

T1M82-X-XXXX-01-XX

BY: J. BORGELT 08-09-2010 SHEET 2 OF 2

F:\DWG\MISC\MKTG\T1M82-X-XXXX-01-XX-MKT.SLDDRW