1.14.012.505/0000



RACON 12 S vertical, THT, 3,6^{±0,7} N, 1 NO



fields of application

- > Measurement-control-regulation
- > Mechanical and system engineering
- > Automotive
- > Electro-medical

special features

Gold contacts, reliable switching with low currents

Special tactile feedback

Different operating forces

Variable overall heights due to plunger

Terminal technology: SMT or THT

Traceability through product identification sealable (tested media see Downloads)



description

Our top-quality RACON 12 tactile switches – in the dimensions 12 x 12 mm – feature an unmistakeable click, high switching reliability, a sealed contact system and castability. That has made RACON the standard in many industries. Whether for automotive applications, systems with keycaps, or membrane keyboards, RACON impresses in the THT or SMT versions – for your application too.

RACON 12 tactile switches can be arranged individually, in rows or as key blocks. When used beneath membrane overlays, the RACON key switches should be combined with plungers. Suitable for the most important soldering techniques

Soldering bath for THT versions

Reflow soldering for SMT versions

Vapor phase soldering for SMT versions

Manual soldering

Processing of the SMT designs with SMT automatic assembly machines

IMDS entry

technical data

I		
r	blue	direct links
rating temperature, min.	-40 °C	> RAFI eCatalog
age temperature, min.	-50 °C	
erating temperature, max.	80 °C	
rage temperature, max.	90 °C	
ninated	No	
dering time for manual	5 sec	
dering, max.		
ldering temperature for manual	350 °C	
ldering		

The information in this data sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which my change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights.

date: Jul 6, 2022 page: 1/3

RAFI GmbH & Co. KG

1.14.012.505/0000



Soldering temperature for wave

soldering

Soldering Manual / wave
Solder heat resistance according DIN EN 60068-2-20

260 °C

to standard

Packaging unit 100 pcs. net weight 1.5 g

Operating life 1,000,000 cycles B10 1,300,000 cycles

Degree of protection, front side, according to DIN EN 60529 IPx7
Degree of protection, rear side, according to DIN EN 60529 IPx7
MSL Moisture Sensitivity Level 1
Corrosive gas testing according to Yes

standard

MOQ order 300 pcs.

RoHS compliant Yes

REACH compliant Yes

Component material Elastomer

Product code 1F

> mounting diameters

Grid. min. 12.5 x 15.24 mm

Outside dimension, length 14.6 mm
Outside dimension, width 13.6 mm
Outside dimension, height 15.55 mm

> mechanical data

Actuation function momentary contact function

Operating force, max. 8 NOperating force, min. $3,6^{\pm 0,7} \text{ N}$ Switching travel $0,61^{\pm 0,1} \text{ mm}$

Contact function 1 NO

Contact system Snap-action contact

Contact material Gold
Terminal on the rear THT
Solderability Yes

> electrical data

Rated voltage, min.

Rated voltage, max.

Rated current, min.

Rated current, max.

0.1 A

Rated power, max.


1 W

1.14.012.505/0000



drawings

Dimensioned drawing



Product labeling drawing

