TX6000™ Category 6 Copper Cable – UTP



specifications

Category 6 U/UTP cable shall exceed ANSI/TIA-568-C.2 and IEC 61156-5 Category 6 component standards. The conductors shall be 23 AWG copper insulated with HDPE. The copper conductors shall be twisted in pairs, separated by a cross-divider and covered by a low smoke zero halogen (LSZH) jacket.



technical information

Electrical performance:	Certified channel performance in a 4-connector configuration up to 100 meters and exceeds the requirements of ISO 11801 Class E and ANSI/TIA-568-C.2 Category 6 standards at swept frequencies up to 250 MHz Certified component performance up to 100 meters and exceeds the component requirement of the IEC 61156-5 and ANSI/TIA-568-C.2 Category 6 component standards at swept frequencies up to 250 MHz	
Conductors/ insulators:	23 AWG solid copper insulated with HDPE	
Flame rating:	LSZH – IEC 60332-3-25 (-3d), IEC 60754-1 and -2, IEC 61034-2, NBN C 30-004 (F2) EN50575: Euroclass Dca – s1a, d2, a1	
PoE compliance:	Meets IEEE 802.3af and IEEE 802.3at for PoE applications	
Installation tension:	110 N (25 lbf) maximum	
Temperature rating:	0°C to 50°C (32°F to 122°F) during installation -20°C to 75°C (-4°F to 167°F) during operation	
Cable jacket:	LSZH – Low Smoke Zero Halogen	
Cable diameter:	6.2mm (0.244 in.) nominal	
Cable weight:	13 kg/305m (29 lbs./1000 ft.)	
Packaging:	Packaged 305 meters (1000 feet) or 500 meters (1640 feet) on a reel Package tested to ISTA Procedure 1A	

key features and benefits

Third party tested	Cable has been tested as part of the TX6000 ⁻ Category 6 U/UTP Copper Cabling System by an independent laboratory and complies with the electrical channel requirements of ANSI/TIA-568-C.2 Category 6 and ISO 11801 Class E standards	
Integrated pair divider	Separates pairs for exceptional cable performance	
Descending length cable markings	Easy identification of remaining cable reduces installation time and cable scrap	
Tested beyond the standards	Cable has been characterized to 550 MHz, 300 MHz above the standard	
Packaged on a reel	Ensures proper performance and provides quick installation	

applications

TX6000" U/UTP Copper Cable is a component of the Panduit "TX6000" U/UTP Copper Cabling System. This end-to-end system provides Gigabit Ethernet performance with usable bandwidth beyond 250 MHz. With certified performance to the ANSI/TIA-568-C.2 Category 6 and ISO 11801 Class E standards, this system will support the following applications:

- Ethernet 10BASE-T, 100BASE-T (Fast Ethernet), 1000BASE-T (Gigabit Ethernet)
- 155 Mb/s ATM, 622 Mb/s ATM, 1.2 Gb/s ATM
- Token ring 4/16

TX6000™ UTP Copper Cabling System

TX6000™ UTP Copper Cable

LSZH: PUZ6004*

Mini-Com® TX6™ PLUS UTP Jack Module

Jack module: CJ688TGIW**

TX6™ PLUS

UTP Patch Cords - LSZH

Meter lengths: UTPSPL^MY

DP6™ PLUS

Angled Punchdown Patch Panels

24-port, 1 RU: DPA24688TGY **48-port, 2 RU:** DPA48688TGY

DP6™ PLUS

Flat Punchdown Patch Panels

12-port, 1 RU: DP12688TGY **24-port, 1 RU:** DP24688TGY **48-port, 2 RU:** DP48688TGY

Mini-Com® Angled Flush Mount Modular Patch Panels

24-port, 1 RU: CPPA24FMWBLY **48-port, 2 RU:** CPPA48FMWBLY

Mini-Com® Flat Flush Mount Modular Patch Panels

24-port, 1 RU: CPP24FMWBLY **48-port, 2 RU:** CPP48FMWBLY

Termination and Cable Prep Tools

Termination

tools: EGJT or TGJT

Wire

snipping tool: CWST

Wire

stripping tool: CJAST

*Color and pallet configurations: Replace * with BU-CEG (Blue) or WH-CEG (White) to designate that color in a Euro pallet of 24 reels, 305m each. Replace * with BU-CED (Blue) or WH-CED (White) to designate that color in a Euro pallet of 18 reels, 500m each.

**To designate color, replace suffix IW (Off White) with AW (Arctic White), EI (Electric Ivory), IG (International Gray), WH (White), BL (Black), OR (Orange), RD (Red), BU (Blue), GR (Green), YL (Yellow), or VL (Violet). Add -24 to end of part number for 24-pack convenience package.


AFor lengths 1 to 10 meters (increments of one meter) and 0.5, 1.5, 2.5, 15, 20 meters, change the length designation in the part number to the desired length. For standard cable colors other than Off White, add suffix BL (Black), BU (Blue), RD (Red), GR (Green), YL (Yellow), OR (Orange), or VL (Violet) after the M in the part number. For example, the part number for a blue 15-meter patch cord is UTPSPL15MBUY.

TX6000™ Category 6 Copper Cable – UTP

additional specifications

Mechanical Test	
Ultimate Breaking Strength	>400 N (90 lbf.)
Minimum Bend Radius	4 x cable diameter
Electrical Test	
Nominal Velocity of Propagation (NVP)	65%
Operating Voltage, Maximum	80V

cable construction



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico cs-la@panduit.com Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



©2017 Panduit Corp.