




Item (Detail view)

2-conductor ground terminal block; 16 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®



Item no.	2016-1207	GTN / EAN	4017332076654
Content	1 piece	Order unit	piece
Order quantity	20 piece	Increase in order quantity	(20, 40, 60, 80, ...)
Customer item no.		Customs tariff no.	85369010000
Customs duty for the country of origin	DE	Available	-
List price	On request	Net price	On request
Availability	On request		

Note: Some items may not be available from your local WAGO company. Please note that the quantities ordered in the shopping cart are rounded up to the PU (SPU).

RoHS
 Compliant

Article details Approvals Downloads/Certificates Accessories

Description 2-conductor ground terminal block; 16 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®

Remarks **Safety information 1:** 15 mm high DIN-35 rails shall be used for a current load higher than 76 A!

Item properties

Miscellaneous		
Name	Value	Unit
Connection technology	Push-in CAGE CLAMP®	
Actuation type	Push-in	
Connectable conductor materials	Copper	
Nominal cross section	16 mm ²	
Solid conductor	0.5 ... 16 mm ² / 20 ... 6 AWG	
Solid conductor, push-in termination	2.5 ... 16 mm ² / 14 ... 6 AWG	
Fine-stranded conductor	0.5 ... 25 mm ² / 20 ... 4 AWG	
Fine-stranded conductor with ferrule, push-in termination 1	2.5 mm ² / 14 AWG	
Strip length	18 ... 20 mm / 0.71 ... 0.79 inch	
Total number of connection points	2	
Total number of potentials	1	
Number of levels	1	
Type of wiring	Front-entry wiring	
Width	12 mm / 0.472 in	
Height from upper-edge of DIN-35 rail	36.9 mm / 1.453 in	
Depth	69.8 mm / 2.748 in	
Design	horizontal	
Type of mounting	Carrier rail 35 x 15	
Marking level	Center/side marking	
Color	green-yellow	
Insulating material	Polyamide 66 (PA 66)	
Fire load (MJ)	0.26	MJ
Weight (g)	38.5	g
Packaging type	BOX	
[mm]	12	mm
Product Family	TOPJOB® S	
Main product function	GND coord. term. block	
Product type	Through rail-mount term. blocks	

Upwards