





Item (Detail view)

Socket with miniature switching relay; AC/DC 115 V; Relay with 1 changeover contact (1u); for normal switching power

Item no.	857-357	GTN / EAN	4045454994029
Content	1 piece	Order unit	piece
Order quantity	1 piece	Increase in order quantity	(1, 2, 3, 4, ...)
Customer item no.		Customs tariff no.	85364900990
Customs duty for the country of origin	CN	Available	-
List price	On request	Net price	On request
Availability	On request		

Note: Some items may not be available from your local WAGO company. Please note that the quantities ordered in the shopping cart are rounded up to the PU (SPU).

RoHS Compliant



Article details Approvals Downloads/Certificates Accessories

Description Socket with miniature switching relay; AC/DC 115 V; Relay with 1 changeover contact (1u); for normal switching power

Remarks **Note:**
Inductive loads have to be attenuated by an appropriate protective circuit in order to protect relay coils and contacts.

Item properties

Miscellaneous		
Name	Value	Unit
Connection technology	Push-in CAGE CLAMP®	
Solid conductor	0.34 ... 2.5 mm ² / 22 ... 14 AWG	
Free-stranded conductor	0.34 ... 2.5 mm ² / 22 ... 14 AWG	
Strip length	9 ... 10 mm / 0.35 ... 0.39 inch	
Width	6 mm / 0.236 in	
Height from upper-edge of DIN-35 rail	61 mm / 2.399 in	
Depth	64 mm / 2.520 in	
Type of mounting	DIN-35 rail	
Color	gray	
Fire load [MJ]	0.481	MJ
Weight [g]	31.47	g
Permissible surrounding air (operating) temperature at U	-40 ... 60 °C	
Surrounding air (storage) temperature	-40 ... 70 °C	
Processing temperature	-25 ... 50 °C	
Standards/specifications	EN 61010-2-201; EN 61810-1; EN 61373; UL 508; ATEX; IEC Ex	
WAGO elementary relay	857-355	
Packaging type	BOX	
Main product function	Relay module	
Product type	Relay modules	
Number of changeover contacts	1	
Number of make contacts	1	
Number of break contacts	1	
Min. nominal input voltage (AC) [V]	AC115	V
Max. nominal input voltage (AC) [V]	AC115	V
Min. nominal input voltage (DC) [V]	DC115	V
Max. nominal input voltage (DC) [V]	DC115	V
Min. input voltage (AC) [V]	138	V
Max. input voltage (AC) [V]	92	V
Min. input voltage (DC) [V]	138	V
Max. input voltage (DC) [V]	92	V
Switching voltage (max.) AC [V]	AC250	V

Upwards