

PIN RECEPTACLES

FOR .022" - .034" DIAMETER PINS AND .025" SQUARE PINS

<p>9808 9808-0-15-XX-16-XX-04-0 Press-fit in .067 mounting hole</p>	<p>9101 9101-0-15-XX-16-XX-10-0 Press-fit in .067 mounting hole</p>	<p>5650 5650-0-19-XX-16-XX-10-0 Press-fit in .067 mounting hole</p>	<p>8679 8679-0-15-XX-16-XX-10-0 Solder mount in .071 min. mounting hole Also available on 24mm wide carrier tape: 800 parts per 13" reel See page 194.11 for Tape & Reel details</p>						
<p>6021 6021-0-15-XX-16-XX-10-0 Solder mount in .062 min. mounting hole Also available on 24mm wide carrier tape: 1,500 parts per 13" reel See page 194.11 for Tape & Reel details</p>	<p>1873 1873-0-15-XX-16-XX-04-0 Press-fit in .066 mounting hole</p>	<p>8827 8827-0-15-XX-16-XX-04-0 Press-fit in .061 mounting hole</p>	<p>5070 5070-0-18-XX-16-XX-10-0 Press-fit in .061 mounting hole</p>						
<p>7620 7620-0-34-XX-16-XX-10-0 Double Ended Receptacle. See chart for Contact number & acceptance ranges</p>	<table border="1"> <thead> <tr> <th>Contact Number</th> <th>Acceptance Range</th> </tr> </thead> <tbody> <tr> <td>(a) #16</td> <td>.022 - .034 and .025 □</td> </tr> <tr> <td>(b) #34</td> <td>.032 - .046</td> </tr> </tbody> </table> <p>(Data on Page 258)</p>	Contact Number	Acceptance Range	(a) #16	.022 - .034 and .025 □	(b) #34	.032 - .046	<p>5135 5135-0-19-XX-16-XX-10-0 Wire crimp termination. Accepts wire sizes 20 AWG Max. / 24 AWG Min.</p>	<p>5448 5448-0-33-XX-16-XX-10-0 Wire crimp termination. Accepts wire sizes 20 AWG Max. / 24 AWG Min.</p>
Contact Number	Acceptance Range								
(a) #16	.022 - .034 and .025 □								
(b) #34	.032 - .046								

SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard
Contact Material: Beryllium Copper Alloy 172, HT
Dimensions: Inches
Tolerances On: Lengths: ±.005
 Diameters: ±.002
 Angles: ± 2°



ORDER CODE: XXXX - X - XX - XX - 16 - XX - 10 - 0

BASIC PART #

- SPECIFY SHELL FINISH:**
- 01 200 μ" TIN/LEAD OVER NICKEL
 - ◆ 80 200 μ" TIN OVER NICKEL (RoHS)
 - ◆ 15 10 μ" GOLD OVER NICKEL (RoHS)

- SPECIFY CONTACT FINISH:**
- 01 200 μ" TIN/LEAD OVER NICKEL
 - ◆ 80 200 μ" TIN OVER NICKEL (RoHS)
 - ◆ 27 30 μ" GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#16 CONTACT (DATA ON PAGE 256)

(For alternate contact choices, see group D on page 248)

