P-Channel 60-V (D-S) MOSFET

Key Features:

- Low r_{DS(on)} trench technology
- · Low thermal impedance
- · Fast switching speed


Typical Applications:

- · White LED boost converters
- Automotive Systems
- Industrial DC/DC Conversion Circuits

PRODUCT SUMMARY				
V _{DS} (V)	$r_{DS(on)}(m\Omega)$ $I_D(A$			
-60	17 @ V _{GS} = -10V	-11.1		
	$23 @ V_{GS} = -4.5V$	-9.5		







ABSOLUTE MAXIMUM RATINGS ($T_A = 25^{\circ}$ C UNLESS OTHERWISE NOTED)					
Parameter			Limit	Units	
Drain-Source Voltage	V_{DS}	-60	V		
Gate-Source Voltage	V_{GS}	±20	V		
Continuous Drain Current a	T _A =25°C	l_	-11.1		
Continuous Drain Current	T _A =70°C	I _D	-9.3	Α	
Pulsed Drain Current ^b	I _{DM}	-50			
Continuous Source Current (Diode Conduction) a	I _S	-5.1	Α		
Power Dissipation ^a	T _A =25°C	P_{D}	3.1	W	
Fower Dissipation	T _A =70°C	' D	2.2	V V	
Operating Junction and Storage Temperature Range			-55 to 150	°C	

THERMAL RESISTANCE RATINGS						
Parameter		Symbol	Maximum	Units		
Maximum Junction-to-Ambient ^a	t <= 10 sec	$R_{\theta JA}$	40	°C/W		
Maximum Junction-to-Ambient	Steady State	IXOJA	80	C/VV		

1

Notes

- a. Surface Mounted on 1" x 1" FR4 Board.
- b. Pulse width limited by maximum junction temperature

Electrical Characteristics


Parameter	Symbol	ymbol Test Conditions		Тур	Max	Unit	
Static							
Gate-Source Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_{D} = -250 \text{ uA}$	-1			V	
Gate-Body Leakage	I _{GSS}	$V_{DS} = 0 \text{ V}, V_{GS} = \pm 20 \text{ V}$			±100	nA	
Zara Cata Valta da Drain Comand	1	$V_{DS} = -48 \text{ V}, V_{GS} = 0 \text{ V}$			-1	uA	
Zero Gate Voltage Drain Current	I _{DSS}	$V_{DS} = -48 \text{ V}, V_{GS} = 0 \text{ V}, T_{J} = 55^{\circ}\text{C}$			-25	uA	
On-State Drain Current a	I _{D(on)}	$V_{DS} = -5 \text{ V}, V_{GS} = -10 \text{ V}$	-20			Α	
Dunin Course On Bonisters a	r	$V_{GS} = -10 \text{ V}, I_D = -8.9 \text{ A}$			17	mΩ	
Drain-Source On-Resistance ^a	r _{DS(on)}	$V_{GS} = -4.5 \text{ V}, I_D = -7.2 \text{ A}$			23	11177	
Forward Transconductance a	g _{fs}	$V_{DS} = -15 \text{ V}, I_{D} = -8.9 \text{ A}$		15		S	
Diode Forward Voltage ^a	V_{SD}	$I_S = -2.6 \text{ A}, V_{GS} = 0 \text{ V}$		-0.73		V	
Dynamic ^b							
Total Gate Charge	Q_g	$V_{DS} = -30 \text{ V}, V_{GS} = -4.5 \text{ V},$		90		nC	
Gate-Source Charge	Q_gs	$I_{DS} = -30 \text{ V}, \text{ V}_{GS} = -4.3 \text{ V},$ $I_{D} = -8.9 \text{ A}$		23			
Gate-Drain Charge	Q_{gd}	1B = 0.5 A		37]	
Turn-On Delay Time	t _{d(on)}	$V_{DS} = -30 \text{ V}, R_1 = 3.4 \Omega,$		14			
Rise Time	t _r	$V_{DS} = -30 \text{ V}, K_L - 3.4 \Omega,$ $I_D = -8.9 \text{ A},$		17		ne	
Turn-Off Delay Time	$t_{d(off)}$	$V_{GEN} = -10 \text{ V}, R_{GEN} = 6 \Omega$		309		ns	
Fall Time	t _f	V GEN = 10 V, 1 (GEN = 0.12		104			
Input Capacitance	C _{iss}			9258			
Output Capacitance	C _{oss}	$V_{DS} = -15 \text{ V}, V_{GS} = 0 \text{ V}, f = 1 \text{ MHz}$		619		pF	
Reverse Transfer Capacitance	C_{rss}]		500			

Notes


- Pulse test: PW <= 300us duty cycle <= 2%.
- Guaranteed by design, not subject to production testing. b.

Analog Power (APL) reserves the right to make changes without further notice to any products herein. APL makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does APL assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in APL data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. APL does not convey any license under its patent rights nor the rights of others. APL products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the APL product could create a situation where personal injury or death may occur. Should Buyer purchase or use APL products for any such unintended or unauthorized application, Buyer shall indemnify and hold APL and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that APL was negligent regarding the design or manufacture of the part. APL is an Equal Opportunity/Affirmative Action Employer.


Typical Electrical Characteristics



1. On-Resistance vs. Drain Current



3. On-Resistance vs. Gate-to-Source Voltage



TJ = 25°C

40

40

40

40

20


10

0


1 2 3 4

VGS - Gate-to-Source Voltage (V)


2. Transfer Characteristics





4. Drain-to-Source Forward Voltage




Typical Electrical Characteristics








8. Normalized On-Resistance Vs Junction Temperature



VDS Drain to Source Voltage (V)

9. Safe Operating Area


10. Single Pulse Maximum Power Dissipation




11. Normalized Thermal Transient Junction to Ambient


Package Information


Land Pattern (Only for Reference)





D.11.4	MILLIMETERS					
DIM.	MIN.	NOM.	MAX.			
Α	1.35	1.55	1.75			
A(1)	0.10	0.18	0.25			
В	0.38	0.45	0.51			
С	0.19	0.22	0.25			
D	4.80	4.90	5.00			
Е	3.80	3.90	4.00			
е	1.27 BSC					
Н	5.80	6.00	6.20			
L	0.50	0.72	0.93			
α	0°	4°	8°			
h	0.25	0.38	0.50			





Note:

- 1. All Dimension Are In mm.
- Package Body Sizes Exclude Mold Flash, Protrusion Or Gate Burrs. Mold Flash, Protrusion Or Gate Burrs Shall Not Exceed 0.10 mm Per Side.
- 3. Package Body Sizes Determined At The Outermost Extremes Of The Plastic Body Exclusive Of Mold Flash, Tie Bar Burrs, Gate Burrs And Interlead Flash, But Including Any Mismatch Between The Top And Bottom Of The Plastic Body.
- 4. The Package Top May Be Smaller Than The Package Bottom.
- Dimension "B" Does Not Include Dambar Protrusion. Allowable Dambar Protrusion Shall Be 0.08 mm Total In Excess Of "B" Dimension At Maximum Material Condition. The Dambar Cannot Be Located On The Lower Radius Of The Foot.