

Features

- High Frequency Operation
- Low Forward Voltage Drop
- Lead Free Finish/RoHS Compliant(Note 1) ("P" Suffix Designates Compliant. See Ordering Information)
- Halogen Free Available Upon Request By Adding Suffix "-HF"
- Epoxy Meets UL 94 V-0 Flammability Rating
- Moisture Sensitivity Level 1

Maximum Ratings

- Operating Junction Temperature Range: -55°C to +150°C
- Storage Temperature Range: -55°C to +150°C
- Thermal Resistance : 2.0°C/W Junction to Case

MCC Part Number	Device Marking	Maximum Recurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
MBRBL40100CT	MBRBL40100CT	100V	70V	100V

Electrical Characteristics @ 25°C Unless Otherwise Specified


Average Forward Current	I _{F(AV)}	40A	T _C =100°C
Peak Forward Surge Current	I _{FSM}	300A	8.3ms,Half Sine
Current Squared Time	l²t	373A ² S	1ms≤t<8.3ms
Instantaneous Forward Voltage	V _F	0.65V(Typ.) 0.71V(Max.) 0.61V(Typ.) 0.75V(Max.)	I _{FM} =20A T _J =25°C I _{FM} =20A T _J =25°C I _{FM} =20A T _J =125°C I _{FM} =20A T _J =125°C
Maximum DC Reverse Current at Rated DC Blocking Voltage	I _R	0.08mA 20mA	T _J =25°C T _J =100°C
Typical Junction Capacitance	CJ	1nF	Measured at 1.0MHz, V _R =4.0V

Note :1. High Temperature Solder Exemption Applied, See EU Directive Annex 7a.


Internal Structure:

PIN 1	PIN 2
PIN 3 -	CASE

40 Amp Low VF Schottky Barrier Rectifier 100 Volts




		DIN	IENSIO	NS	
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	NOTE
А	0.331	0.370	8.40	9.40	
В	0.378	0.417	9.60	10.60	
С	0.165	0.189	4.20	4.80	
D	0.027	0.037	0.68	0.94	
Е	0.045	0.055	1.14	1.40	
G	0.0	010	2.	54	TYP.
Н	0.096	0.134	2.43	3.40	
J	0.011	0.025	0.28	0.64	
Κ	0.071	0.131	1.80	3.32	
S	0.575	0.625	14.60	15.87	
V	0.042	0.058	1.07	1.47	
W	0.000	0.010	0.00	0.25	






Curve Characteristics



Instantaneous Forward Voltage (V)



T,=25°C≣

80

0.1

0.01

0.001

20

40

60

Percent of Rated Peak Reverse Voltage (%)

100



Ordering Information

Device	Packing	
Part Number-TP	Tape&Reel: 800pcs/Reel	
Part Number-BP	Tube: 5Kpcs/Ctn	

Note : Adding "-HF" Suffix For Halogen Free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. *Micro Commercial Components Corp*. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold *Micro Commercial Components Corp*. and all the companies whose products are represented on our website, harmless against all damages. *Micro Commercial Components Corp*. products are sold subject to the general terms and conditions of commercial sale, as published at

https://www.mccsemi.com/Home/TermsAndConditions.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources**. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.