

MM-2J2-031-PS1-22WA MN-2J1-031-PS1-22WA XX-XXX-XXX-XXX-XXX

**SERIES** MM .050" Rugged Metal I/O Connector MN .050" Rugged Plastic I/O Connector (MM & MN mate with MK, ML, MM, MN assemblies) **BODY** 2 2-Row (Sizes 9 thru 51\*\*\*\*) 3-Row (Size 51 & 69\*\*\*) 4-Row (Size 100) BODY STYLE: Jumper assembly, straight, with ears BODY MATERIAL: Polyphenylene Sulfide (MN only) 1 2 Polyphenylene Sulfide with electroless nickel shell Polyphenylene Sulfide with electrodeposited cadmium shell 3 Polyphenylene Sulfide with hard anodized black shell 4 Polyphenylene Sulfide with stainless steel shell 5 Pure Electro-Deposited Aluminum Zinc Nickel Plating Т Nickel Polymer Plating SIZE XXX 009, 015, 021, 025, 031, 037, 051\*\*\*\*, 069\*\*\*, 100 CONTACTS TYPE CONTACTS/TERMINATIONS: PP Plug to plug PS Plug to receptacle SS Receptacle to receptacle PLATING OPTIONS: 50 µ" Au contacts (crimp wire) **HARDWARE** STYLE OF HARDWARE: 00 None 22 Four fixed jacknut assemblies (62\*) 41 Four turning jackscrews, allen head, retaining ring (81\*) 43 Four turning jackscrews, slot head, retaining ring (83\*) 45 Four turning jackscrews, allen head, captivated\*\* (85\*) 46 Two fixed jacknuts and two turning jackscrews, allen head, uninstalled (86\*) 47 Two fixed jacknuts and two turning jackscrews, slot head, uninstalled (87\*) Keying hardware, see options below. (Body material 2, 3 and 4 only) POLARIZATION / WIRING: XX For wiring codes, see page MA-3 & MA-4 **OPTIONS** KSXX Four turning jackscrews. Receptacles supplied with interfacial sealing gasket. See page MA-6 for keying options (KJ\*) KPXX Four fixed jacknuts. Receptacles supplied with interfacial sealing gasket. See page MA-6 for keying options (KN\*) 900 Interfacial sealing gasket \* = Use numbers or letters in parenthesis when ordering size 100.

\*\* = Captive hardware is factory installed and non-removable.

\*\*\* = 69 position connectors are available in metal only.

\*\*\*\* = 2 row, 51 position connectors are available in metal only (non Mil-Spec interface).