



Data Sheet AB2036B-2


Features:


- Ultrathin and lightweight 20mm bender
- 3,600 Hz resonant frequency
- Low Power consumption

Specifications

Parameters	Values	Units	
Resonant Frequency	$3,600 \pm 600$	Hz	
Resonant Impedance (Max)	≤ 500	Ohms	
Max Input Voltage	30	Vp-p	
Capacitance (@ 120 Hz)	20,000 ± 30%	pF	
Plate Material	Brass	-	
Storage Temperature	-30 ~ 70	°C	
Operating Temperature	-20 ~ 70	°C	
Environmental Compliances	RohS/Reach	Exempt. 7c-1	

Dimensions





Packaging

100pcs/roll, foam packaging 20 rolls/layer = 2000pcs total 5 layers = 10,000pcs

Specifications Revisions

opecinications (cations				
Revision	Description	Date	Approved	
Α	Released from Engineering	3/6/2024	JD	

Note:

- 1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are ±0.5mm and angles are ±3°.
- 2. Specifications subject to change or withdrawal without notice.