

Data Sheet AB4122BF


### Features:


- Ultrathin and lightweight 41mm bender
- 2,200 Hz resonant frequency
- Low power consumption

## **Specifications**

Parameters	Values	Units	
Resonant Frequency	2,200 ± 300	Hz	
Resonant Impedance (Max)	350	Ohms	
Max Input Voltage	30	Vp-p	
Capacitance (@ 120 Hz)	24,000 ± 30%	рF	
Plate Material	Brass	-	
Storage Temperature	-30 ~ 80	°C	
Operating Temperature	-20 ~ 70	°C	
Environmental Compliances	Rohs/Reach	Exempt. 7c-1	

### **Dimensions**





This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited.

© 2024, PUI Audio Inc.

# **Packaging**

100pcs/roll, foam packaging 10 rolls/layer = 1000pcs total 5 layers = 5,000pcs

### **Specifications Revisions**

Revision	Description	Date	Approved
Α	Released from Engineering	3/6/2024	JD

### Note:

- 1. Unless otherwise specified:
  - A. All dimensions are in millimeters.
  - B. Default tolerances are ±0.5mm and angles are ±3°.
- 2. Specifications subject to change or withdrawal without notice.