



PRODUCT DATA DRAWING









.250±.002[6.35±0.05] .096±.002[2.43±0.05] 2X 2-56 UNC-2B 2X .410±.002 \[10.41±0.05 \] THRU

MATERIAL:

BODY & RETAINING CAP: STAINLESS STEEL PER AMS 5640, ALLOY UNS S30300, TYPE 1

OR ASTM A582 TYPE 303, CONDITION A.

SPRING PINS: 420 SERIES STAINLESS STEEL

FINISH:

BODY & RETAINING CAP: PASSIVATED PER AMS 2700

NOTES:

DESIGNED TO CARRY THREE (3) 12 OR 24 FIBER MT FERRULES.

	MATERIAL:	SEE NOTES
	FINISH:	SEE NOTES
	SURFACE ARE	^{EA:} N/A
	!	PROPRIETARY
	IS THE SOLE PE ANY REPRODU	ION CONTAINED IN THIS DRAWIN ROPERTY OF SV MICROWAVE, IN CTION IN PART OR AS A WHOLE WILLTEN DEPMISSION OF

DIMENSIONS ARE IN INCHES TOLERANCES:
FRACTIONAL: ±1/64 ANGULAR: X° ±1°0 X°X' +15'
DECIMAL: .X ±.030 .XX +.010
.XXX ±.005

INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994 THII

IRD ANGLE PROJECTION	DRAWN:
	CHECKED:
	APPROVED


UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS] 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX.	Ampheno MICROWAVE www.svmicrowave.com
4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63.ML-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS	3 PORT FIBER MT PLUC


JPM 08/17/22

SEE PDM SEE PDM

TITLE: 3 PORT FIBER MT PLUG-IN **MODULE VITA 66.5**

SIZE DWG. NO. 9301-60048





RECOMMENDED PCB CUTOUT FOR PLUG-IN MODULE TYPE C

CONNECTOR LOCATION ON DAUGHTER CARD PCB				
POSITION	DIM 'X'			
P2A	2.312" [58.730]			
P2B	2.874" [72.990]			
P3A	3.859" [98.010]			
P3B	4.426" [112.410]			
P4A	5.192" [131.880]			
P4B	5.759" [146.280]			
P5A	6.326" [160.680]			
P5B	6.893" [175.080]			
P6A	7.474" [189.830]			
P6B	8.041" [204.230]			

MATERIAL:	SEE NOTES		
FINISH:	SEE NOTES		
SURFACE AREA: N/A			
PROPRIETARY			
IS THE SOLE PRO ANY REPRODUC WITHOUT THE W	ON CONTAINED IN THIS DRAWING OPERTY OF SV MICROWAVE, INC. TION IN PART OR AS A WHOLE RITTEN PERMISSION OF , INC IS PROHIBITED.		

DIMENSIONS ARE IN INCHES TOLERANCES:

FRACTIONAL: ±1/64 ANGULAR: X° ±1°0'

DECIMAL: X ±.030
 .XX ±.010
 .XXX ±.005

INTERPRET DIMENSIONS AND TOLERANCES

INTERPRET DIMENSIONS AND TOLERANCES
PER ASME Y14.5M - 1994

THIRD ANGLE PROJECTION

HIRD ANGLE PROJECTION —

UNLESS OTHERWISE SPECIFIED

1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS]
2) ALL DIMENSIONS ARE AFTER PLATING.
3) BREAK CORNERS & EDGES. JOS R. MAX.
4) CHAM. 1ST & LAST THREADS.
5) SURFACE ROUGHNESS 63*MIL-STD-10.
6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN JOST-LIR.
7) REMOVE ALL BURRS

DRAWN: JPM 08/17/22

CHECKED: SEE PDM

APPROVED: SEE PDM



3 PORT FIBER MT PLUG-IN MODULE VITA 66.5

SIZE DWG. NO. 9301-60048

SCALE: 4:1 SHEET 2 OF