#### EMC Components

Common mode filters Ultra high-speed differential signal line (USB4.0, USB3.2/3.1/3.0, HDMI, DisplayPort) **TCM-U** series

# TCM06U type


#### FEATURES

- This product is a thin-film common mode filter with a wide frequency range that can be used for ultra high-speed differential signal interfaces such as USB4.0 (Data speed : 20Gbps).
- OIn improved common mode attenuation of 10GHz (or 2.4GHz, 5.0GHz), produces a sufficient anti effect to common mode noise of high-frequency. Also, to realizing remarkable band differential mode transmission, do not have an impact almost to transmission speed difference differential line signal.
- Operating temperature range: -25 to +85°C

#### APPLICATION

Noise countermeasure for ultra-high-speed differential interfaces (USB4.0, USB3.2/3.1/3.0, HDMI, Display Port etc.) for Note PC, Set top box and general consumer products such as smartphone and tablet device.

### PART NUMBER CONSTRUCTION



#### CHARACTERISTICS SPECIFICATION TABLE

Common mode attenuation	Cutoff frequency	DC resistance	Rated current	Rated voltage	Insulation resistance	Part No.
		[1 line]				
(dB)	(GHz)typ.	(Ω)	(A)max.	(V)max.	(MΩ)min.	
25min. @10.0GHz	-20.0 over	0.5±30%	0.1	10	10	TCM06UX-020-2P-T201
18min. @9.0 to 11.0GHz	-20.0 over	0.5±30%	0.1	10	10	<u>100000-020-2F-1201</u>
30min. @5.0GHz	-20.0 over	0.9±30%	0.1	10	10	TCM06U5-050-2P-T201
18min. @4.0 to 6.0GHz						
30min. @2.4GHz	—13.0	2.5±30% 0.	0.1	10	10	TCM06U2-150-2P-T201
18min. @1.9 to 3.3GHz						<u>1010002-150-2P-1201</u>

#### **Measurement equipment**

Measurement item	Product No.	Manufacturer
Common mode impedance	4291A	Keysight Technologies
DC resistance	4338A	Keysight Technologies
Insulation resistance	4339A	Keysight Technologies

\* Equivalent measurement equipment may be used.



(1/4)

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. 20240312




O,





# TCM06U type


#### IMPEDANCE VS. FREQUENCY CHARACTERISTICS



#### Measurement equipment

Product No.	Manufacturer	
4991A	Keysight Technologies	
* Equivalent measurement equipment may be used.		

### INSERTION LOSS VS. FREQUENCY CHARACTERISTICS



#### **Measurement equipment**


Product No.	Manufacturer	
E5071B	Keysight Technologies	
* Equivalent measurement equipment may be used		

Equivalent measurement equipment may be used.

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. 20240312

## TCM06U type

#### SHAPE & DIMENSIONS




### RECOMMENDED LAND PATTERN




Dimensions in mm


## **CIRCUIT DIAGRAM**



### RECOMMENDED REFLOW PROFILE




#### PACKAGING STYLE







#### **TAPE DIMENSIONS**



Dimensions in mm





#### **PACKAGE QUANTITY**

Package quantity	10,000 pcs/reel

### TEMPERATURE RANGE, INDIVIDUAL WEIGHT

	Operating temperature range	Storage temperature range *	Individual weight
	–25 to +85 °C	–25 to +85 °C	0.5 mg
4	* The storege temperature renge is far ofter the secondly		

The storage temperature range is for after the assembly.

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. (3/4)

20240312

#### EMC Components

## **REMINDERS FOR USING THESE PRODUCTS**

Before using these products, be sure to request the delivery specifications.

## SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products

## REMINDERS

The storage period is within 6 months. Be sure to follow the storage conditions (temperature: 5 to 40°C, humidity: 20 to 70% RH or less).

If the storage period elapses, the soldering of the terminal electrodes may deteriorate.

Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).

- Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.
- Owhen embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.
- Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.
- Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference.
- Use a wrist band to discharge static electricity in your body through the grounding wire.
- ODo not expose the products to magnets or magnetic fields.
- Obo not use for a purpose outside of the contents regulated in the delivery specifications.
- OThe products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications) equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/ or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions set forth in the each catalog, please contact us.

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment

- (7) Transportation control equipment
- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.