

157-00283

HellermannTyton

Article Number: 157-00283

Description: Wide Strap Cable Tie with 6mm Stud Mount, 15.7" Long, .5" Wide, PA66HIRHSUV, Black, 300/Bag



Base Data	
Local Order Number	157-00283
Type	WSR6MM
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> • Mount provides low insertion and high extraction forces which makes for a strong and easy installation. • Clamping rails increase grip on round bundles. • Thinner strap provides increased flexibility for improved ergonomics. • Tie utilizes a strong hinge between the stud mount and strap head to provide superior holding ability.
Quantity Per	bag
Product Description	Wide Strap Heavy Duty Cable Ties features a stud mount for direction application onto a 6 mm threaded stud. The tie is 0.5" wide, and handles bundles from 0.38" - 4.2". The low profile mount design engages a minimum of 4 threads on the stud which makes it easier to apply additional mounts onto one stud.
GLOBAL PART NAME	WSR6MM-PA66HIRHSUV-BK
Short Description	Wide Strap Cable Tie with 6mm Stud Mount, 15.7" Long, .5" Wide, PA66HIRHSUV, Black, 300/Bag
Product Dimensions	
Minimum Tensile Strength (Imperial)	120.0lbs
Minimum Tensile Strength (Metric)	534N
Length L (Imperial)	15.7"
Length L (Metric)	398.8mm
Fixation Method	Weld Stud Fixing
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.5"
Width W (Metric)	12.7mm
Bundle Diameter Min. (Imperial)	0.38"

157-00283



Product Dimensions	Bundle Diameter Min. (Metric)	9.5mm
	Bundle Diameter Max. (Imperial)	4.1"
	Bundle Diameter Max. (Metric)	104.1mm
	Stud Diameter (Imperial)	0.236"
	Stud Diameter (Metric)	6.0 mm
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
	Material Shortcut	PA66HIRHSUV
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +230°F (-40°C to +110°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	300
	Package Quantity (Metric)	300Bag
	Customs Number(Schedule B)	3926909987