




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS		DATE	APPROVED
REV. 1	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE	07/Feb/2023	
A1	Show all the actual pin locations	08/Feb/2023	
A2	Correction of the wiring error	09/Feb/2023	



- Note:
- Material:
 - High temperature thermoplastic PBT with 30%GF, UL94V-0
 - Contact: Copper Alloy, thickness=0.2mm, Gold flash plated on contact area over Nickel
 - Front Shell: Steel, thickness=0.4mm, Nickel Plated
 - Back Shell: Steel, thickness=0.4mm, Tin Plated over Nickel
 - Specification:
 - Current rating: 1 A Max.
 - Dielectric withstanding voltage: 500 V(ac) for 1 min.
 - Contact resistance: 30 mΩ Max.
 - Insulation resistance: 1000 MΩ Min.
 - Total mating force: 9.0 Kgf Max.
 - Total unmating force: 1.5 Kgf Min.
 - Temperature range: -55°C~85°C
 - Mating Cycle: 500 cycles min
 - ROHS(Directive 2011/65/EU Consolidated version of 24 June 2015)Compliant



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MM TOLERANCES ARE:		EAR NO.		APPROVALS		DATE		SIZE	
DECIMALS	ANGLES			DRAWN	DATE			A	
.X	±X°			LF	07/Feb/2023			P/N	CN-DSUB37PIN0-000
.XX	±XX°			CHECKED				REV	A2
.XXX	±XXX°			BA	07/Feb/2023			D-Sub Connector (Solder-Cup) Connector Type: DB37 Male	
THIRD ANGLE PROJECTION				RESR ENG					
				MFG ENG					

20 VALLEY ST. ENDICOTT, NY 13760

Amphenol Cables on Demand

SCALE SHEET OF

NOTES: UNLESS OTHERWISE SPECIFIED