




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES IN PART OR WHOLE WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.



Note:

- 1. Material:**
- 1.1 High temperature thermoplastic: PBT with 30%GF, UL94V-0
 - 1.2 Contact: Copper Alloy, thickness=0.2mm,
Gold flash plated on contact area over Nickel
 - 1.3 Front Shell: Steel, thickness=0.4mm, Tin Plated
 - Back Shell: Steel, thickness=0.4mm, Tin Plated over Nickel
- 2. Specification:**
- 2.1 Current rating: 1 A Max.
 - 2.2 Dielectric withstanding voltage: 500 V(ac) for 1 min.
 - 2.3 Contact resistance: 30 mΩ Max.
 - 2.4 Insulation resistance: 1000 MΩ Min.
 - 2.5 Total mating force: 7.0 Kgf Max.
 - 2.6 Total unmating force: 1.5 Kgf Min.
 - 2.7 Temperature range: -55°C~85°C
 - 2.8. Mating Cycle: 500 cycles min
- 3. ROHS(Directive 2011/65/EU Consolidated version of 24 June 2015)Compliant**

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A1	NEW RELEASE		27/Feb/2019	
A1	Updated the description.		10/Feb/2023	
A2	change the Description		13/Feb/2023	



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MM TOLERANCES ARE:		EAR NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDDCOTT, NY 13760	
DECIMALS	ANGLES	DRAWN	APPROVALS	DATE	SIZE
±.X	±X°	LF		27/Feb/2019	A
±.XX	±XX	CHECKED	BA	27/Feb/2019	P/N CN-DSUBHD15SK-000
±.XXX	±XXX	RESP' ENG			REV. A2
THIRD ANGLE PROJECTION		MFG ENG			

NOTES: UNLESS OTHERWISE SPECIFIED