

BC337/BC338 TRANSISTOR(NPN)

FEATURE

- Power dissipation



Package TO-92

MAXIMUM RATINGS* ($T_a=25^{\circ}\text{C}$ unless otherwise noted)


Parameter	Symbol	Value	UNIT
Collector-Base Voltage	V_{CBO}	BC337 50	V
		BC338 30	
Collector-Emitter Voltage	V_{CEO}	BC337 45	V
		BC338 25	
Emitter-Base Voltage	V_{EBO}	5	V
Collector Current - Continuous	I_C	800	mA
Total Device Dissipation	P_D	625	mW
Junction Temperature	T_J	150	$^{\circ}\text{C}$
Junction and Storage Temperature	T_{stg}	-55~+150	$^{\circ}\text{C}$

*These ratings are limiting values above which the serviceability of any semiconductor device may be impaired.

ELECTRICAL CHARACTERISTICS ($T_a=25^{\circ}\text{C}$ unless otherwise specified)



Parameter	Symbol	Test conditions	MIN	TYP	MAX	UNIT
Collector-base breakdown voltage	V_{CBO}	$I_C=100\mu\text{A}$, $I_E=0$	BC337 50			V
			BC338 30			
Collector-emitter breakdown voltage	V_{CEO}	$I_C=10\text{mA}$, $I_B=0$	BC337 45			V
			BC338 25			
Emitter-base breakdown voltage	V_{EBO}	$I_E=10\mu\text{A}$, $I_C=0$	5			V
Collector cut-off current	I_{CBO}	$V_{CB}=45\text{V}$, $I_E=0$ $V_{CB}=25\text{V}$, $I_E=0$	BC337		0.1	μA
			BC338		0.1	
Collector cut-off current	I_{CEO}	$V_{CE}=40\text{V}$, $I_B=0$ $V_{CE}=20\text{V}$, $I_B=0$	BC337		0.2	μA
			BC338		0.2	
Emitter cut-off current	I_{EBO}	$V_{EB}=4\text{V}$, $I_C=0$			0.1	μA
DC current gain	$h_{FE(1)}$	$V_{CE}=1\text{V}$, $I_C=100\text{mA}$	BC337/BC338 100		630	
			BC337-16/BC338-16 100		250	
			BC337-25/BC338-25 160		400	
			BC337-40/BC338-40 250		630	
	$h_{FE(2)}$	$V_{CE}=1\text{V}$, $I_C=300\text{mA}$	60			
Collector-emitter saturation voltage	$V_{CE(sat)}$	$I_C=500\text{mA}$, $I_B=50\text{mA}$			0.7	V
Base-emitter saturation voltage	$V_{BE(sat)}$	$I_C=500\text{mA}$, $I_B=50\text{mA}$			1.2	V
Base-emitter voltage	V_{BE}	$V_{CE}=1\text{V}$, $I_C=300\text{mA}$			1.2	V
Transition frequency	f_T	$V_{CE}=5\text{V}$, $I_C=10\text{mA}$, $f=100\text{MHz}$	210			MHz
Collector output capacitance	C_{OB}	$V_{CB}=10\text{V}$, $I_E=0$, $f=1\text{MHz}$		15		pF

TYPICAL CHARACTERISTICS




All products, product specifications and data are subject to change without notice to improve reliability, function or design or otherwise.

TO-92 Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	3.300	3.700	0.130	0.146
A1	1.100	1.400	0.043	0.055
b	0.380	0.550	0.015	0.022
c	0.360	0.510	0.014	0.020
D	4.300	4.700	0.169	0.185
D1	3.430		0.135	
E	4.300	4.700	0.169	0.185
e	1.270 TYP		0.050 TYP	
e1	2.440	2.640	0.096	0.104
L	14.100	14.500	0.555	0.571
Φ		1.600		0.063
h	0.000	0.380	0.000	0.015

TO-92 Suggested Pad Layout




Note:

1. Controlling dimension: in millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.


TO-92 Tape and Reel

TO-92 PACKAGE TAPEING DIMENSION



Dimiensions are in millimeter

A1	A	T	P	P0	P2	F1	F2	W
4.5	4.5	3.5	12.7	12.7	6.35	2.5	2.5	18.0
W0	W1	W2	H	H0	D0	t1	t2	ΔP
6.0	9.0	1.0 MAX.	19.0	16.0	4.0	0.4	0.2	0



Package	Box	Box Size(mm)	Carton	Carton Size(mm)
TO-92	2000 pcs	333×162×43	20,000 pcs	350×340×250

All products, product specifications and data are subject to change without notice to improve reliability, function or design or otherwise.