


**Type SEI(G)**

10.1×3.1×3.1mm

Slow-Blow Fuse Series



**Approval**

Recognized Component for Canada and U.S.  
TUV

A~ A  
A~ A

**Electrical Characteristic**

Rated current	1 In	2.5 In
	MIN	MAX
500mA~5A	4 hr	120 sec

**Interrupting Rating**

50 amperes at 250V AC

**Environmental Specification**

**Operating Temperature**  
-55°C to +125°C

**Vibration**

MIL-STD-202G, Method 201(10-55 Hz, 0.06 inch, total excursion)

**Salt Spray**

MIL-STD-202G, Method 101, Test Condition B (48Hrs)

**Insulation Resistance**

MIL-STD-202G, Method 302, Test Condition A


**Resistance to Solder Heat**

MIL-STD-202G, Method 210, Test Condition B (10sec, at 260°C)

**Thermal Shock**

MIL-STD-202G, Method 107, Test Condition B (-65°C to +125°C)

**Mechanical Dimension(mm)**



Catalog Number	Ampere Rating [ In ]	Voltage Rating ( V )	Nominal Resistance Cold Ohms	Nominal Melting I <sup>2</sup> t A <sup>2</sup> Sec
SEI .500	500mA	250V	0.5479	1.963
SEI .750	750mA		0.2600	3.375
SEI 001	1A		0.1800	11.22
SEI 1.50	1.5A		0.1027	14.85
SEI 002	2A		0.0504	19.84
SEI 2.50	2.5A		0.0370	20.50
SEI 003	3A		0.0280	54.00
SEI 3.50	3.5A		0.0199	57.82
SEI 004	4A		0.0158	125.6
SEI 005	5A		0.0120	185.0

**Physical Specification**

**Material**

Body: Ceramic  
Terminations: Gold Plated Brass Caps

**Packaging**

1. Tape & Reel: 24mm tape
2. Packing Specification: EIA RS-481-2
3. Quantity: 2,500 pcs per reel.

