

# SAC-4P-0,34-OE-OE-PUR-100,0 SH - Cable reel



1422090

<https://www.phoenixcontact.com/us/products/1422090>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



By the meter, Cable reel, shielded, PUR halogen-free, black-gray RAL 7021, 4-wire, color single wire: brown, white, blue, black, cable length: 100 m

## Commercial Data

Item number	1422090
Packing unit	1 pc
Note	Made to Order (non-returnable)
Sales Key	BF16
Product Key	BF1IIB
GTIN	4055626325439
Weight per Piece (including packing)	22.22 g
Weight per Piece (excluding packing)	22.22 g
Customs tariff number	85444995
Country of origin	DE

# SAC-4P-0,34-OE-OE-PUR-100,0 SH - Cable reel



1422090

<https://www.phoenixcontact.com/us/products/1422090>

## Technical Data

### Product properties

Product type	Cable by the meter
Number of positions	4
Application	Connector


### Electrical properties

Nominal voltage $U_N$	300 V
-----------------------	-------

### Cable/line

Cable length	100 m
--------------	-------

### PUR halogen-free black [PUR]

Dimensional drawing	
Cable weight	36 kg/km
UL AWM Style	20549 / 10493 (80°C/300 V)
Number of positions	4
Shielded	yes
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross section	4x 0.34 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1.27 mm ±0.02 mm (Signal line)
External cable diameter	4.95 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, white, blue, black
Thickness, insulation	≥ 0.21 mm
Thickness, outer sheath	approx. 0.5 mm
Overall twist	4 wires, twisted
Optical shield covering	80 %
Max. conductor resistance	max. 58 Ω/km (at 20 °C)
Insulation resistance	≥ 100 GΩ*km (at 20 °C)
Wave impedance	≥ 62 Ω (f = 10 MHz)

# SAC-4P-0,34-OE-OE-PUR-100,0 SH - Cable reel



1422090

<https://www.phoenixcontact.com/us/products/1422090>

Cable capacity	≤ 80 pF/m (Conductor-Conductor)
	≤ 135 pF/m (Wire/shield)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Max. bending cycles	10000000
Halogen-free	in accordance with DIN VDE 0472 part 815
	in accordance with DIN EN 50267-2-1
Flame resistance	in accordance with UL 758/1581 FT2
	DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents
	hydrolysis and microbe resistant
	Resistant to salt water
	partly UV-resistant in accordance with DIN EN ISO 4892-2-A
	abrasion-resistant
Special properties	Flexible cable conduit capable
	Silicone-free
	Free of substances which would hinder coating with paint or varnish
	Low adhesion surface
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-25 °C ... 80 °C (Cable, flexible installation)

# SAC-4P-0,34-OE-OE-PUR-100,0 SH - Cable reel



1422090

<https://www.phoenixcontact.com/us/products/1422090>

## Approvals



**cUL Recognized**

Approval ID: FILE E 344675



**UL Recognized**

Approval ID: FILE E 344675



**EAC**

Approval ID: RU C-DE.BL08.B.00286

# SAC-4P-0,34-OE-OE-PUR-100,0 SH - Cable reel



1422090

<https://www.phoenixcontact.com/us/products/1422090>

## Classifications

### ECLASS

ECLASS-11.0	27061801
ECLASS-12.0	27061801
ECLASS-13.0	27061801

### ETIM

ETIM 7.0	EC003249
----------	----------

# SAC-4P-0,34-OE-OE-PUR-100,0 SH - Cable reel



1422090

<https://www.phoenixcontact.com/us/products/1422090>

## Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

# SAC-4P-0,34-OE-OE-PUR-100,0 SH - Cable reel



1422090

<https://www.phoenixcontact.com/us/products/1422090>

## Accessories

### WIREFOX SAC - Stripping tool

1212623

<https://www.phoenixcontact.com/us/products/1212623>



Stripping pliers, for halogen-free sensor/actuator cables (SAC cables), with PUR and PVC insulation, from Ø of 4.4 to 7 mm, any stripping length

---

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)