MOTORS

0.5 Nm 3 Watts 3 Watts Part number made to order



02/11/2015


- Mechanical strength : 0,5 Nm
- Constant speed, dependent on supply frequency
- Wide range of speeds available
- Direction of rotation controlled by long-life mechanical anti-return device
- Permanent magnet rotor

Part numbers

Туре	Туре	Output speed	Ratios (i)	Direction of rotation	Voltages/Frequencies
82 344 780 3 Watts	82 344 0	0,33 rpm	1800	Clockwise	230 V 50 Hz

Specifications

Motor	82 340 0
Gearbox	81 021 0
Maximum permitted torque from gearmotor under continuous conditions for 1 millions turns of the gearmotor (Nm)	0.5
Axial load static (daN)	1
Radial load static (daN)	8
Absorbed power (W)	3
Motor output (W)	0,16
Maximum temperature rise (°C)	55
Ambient temperature (°C)	-5 →+60
Weight (g)	160
Wires length mm (approximately)	250
Protection rating	IP40




This device is situated inside the gearbox and is particularly recommended when gearbox protection is required in the event of accidental overloading. In this system, the final gear is connected to the gearbox output shaft by means of a friction assembly. In some cases, this device can be used for time adjustment or zero reset on timers.

The standard torque setting is from : - 1.8 to 2.5 cm/kg for gearbox 810210

- 7 to 10 cm/kg for gearbox 810330

Principl



This device, situated inside the gearbox, enables the output shaft to be rotated by an external force (manual or mechanical) independently of the final wheel of the gearbox.

Description

A specially shaped cam (1) is directly fitted on the gearbox output shaft. The final wheel (2) of the gearbox pivots freely on this shaft and has a housing into which the cam fits (1).

Between the cam and final wheel two rollers are symmetrically located held in place under the pressure of two springs (4).


When the geared motor is energised, it causes the final wheel (2) to rotate which, via the two rollers (3), in turn drives the output shaft.

If, under external force, the output shaft is turned in the same direction as the final wheel but at a higher speed, the two rollers (3) release the final wheel and the shaft speed becomes independent of the speed of the final wheel.

The rollers can be located according to whether the final wheel is rotating clockwise or anti-clockwise. Can be used with gearboxes 81 021 0 and 81 033 0.


No	Legend





Nº	Legend
1	2 fixing holes Ø 3.2
0	(pushed-in shaft)
0	3.5 across flat
	Fixing clip

Dimensions (mm)




N°	Legend
0	(pushed-in shaft)

Dimensions (mm


Shaft 79 200 779



nsions	



Nº	Legend
0	Across flat



Unless otherwise specified, the characteristics given are applicable to all or part of the product range selected

N°	Legend	
0	RPM	

•	Different voltages available	
<u> </u>	Special cable lengths	
-	Special connectors	
-	Special output shafts	
	Special gearbox ratios	
	Special gear wheel material	
	Special output bearings	