



# Technical Data Sheet

## 3M™ Scotch® Colored Film Tape 690



[Product Details](#)



[Regulatory Info/SDS](#)

### Product Description

Scotch® Tape 690 is a colored film tape featuring a durable, moisture- and chemical resistant 3M™ Paklon™ film backing with a rubber resin adhesive. This decorative colored film is excellent for various packaging, color-coding, bag sealing, combining, and attaching applications.

### Product Features

- Meets CID A-A-113 Type 1 Class B.
- Long-aging construction.
- Good “wet grab” adhesion.
- Extended life, good aging.
- Resists turning brittle with age.
- Heat shrinks bi-directionally to provide a secure closure.
- Color-coding is simple; provides visual inventory and security closure.
- Color coordination with consumer packaging.
- Controlled unwind for reliable hand dispensing.
- Sticks to the job for customer satisfaction.
- Immediate adhesion to film, chipboard, glass, plastic, metals and other surfaces.
- Can be used in applications where the presence of moisture or chemicals would cause other films to fail.

### Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

### Typical Physical Properties

Attribute Name	Test Method	Value
Color		Black, blue, green, red, white, and yellow
Adhesive Type		Pressure sensitive rubber resin
Backing		3M™ Paklon™ film
Backing Thickness	ASTM D3652	0.037 mm (1.5 mil)
Total Tape Thickness	ASTM D3652	0.058 mm (2.3 mil)

### Typical Performance Characteristics

Attribute Name	Test Method	Temperature	Value
180° Peel Adhesion	ASTM D3330	22 °C (72 °F)	3.3 N/cm (30 oz/in) <sup>1</sup>
Elongation at Break	ASTM D3759		45 %
Longitudinal Tensile Strength	ASTM D3759		61.3 N/cm (35 lb/in)

<sup>1</sup> 12 in/min (300 mm/min)

### Handling/Application Information

#### Application Techniques

An extensive line of manual, semi-automatic, and automatic equipment is available to facilitate application of Scotch® Tape 690. Recommended dispensers are Scotch® Bag Sealer P400 and P410.

## Industry Specifications

CID A-A-113 Type 1 Class B

## Storage and Shelf Life

Storage of tape at 70°F (21°C) and 40-50% relative humidity is recommended.  
To obtain best performance, use this product within 18 months from date of manufacture.

## Available Sizes

Attribute Name	Value
Core Size (ID)	76.2 mm (3 in)
Standard Roll Length	66 m (72 yd)
Standard Width	9, 12, 24, 48 mm
Standard Width	9, 12, 24, 48 mm <sup>1</sup>

<sup>1</sup> Not all colors are available in all widths. Please check the price page.

## Information

**Technical Information:** The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

**Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

**Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

**Disclaimer:** 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit [www.3M.com](http://www.3M.com).

## ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

## For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-362-3550 or visit [www.3M.com/packaging](http://www.3M.com/packaging). Address correspondence to: 3M Industrial Adhesives and Tapes Division, Building 21-1W-10, 900 Bush Avenue, St. Paul, MN 55144-1000. Our fax number is 651-778-4244. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.

3M  
Closure and Masking Systems Division  
3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000  
800-362-3550 • 877-369-2923 (Fax)  
[www.3M.com](http://www.3M.com)

©3M 2003 (4/03)