

**Female Header**  
Pitch 2.54 mm straight, elevated

Double row, pitch 2.54 mm



**SPECIFICATION:**

Current rating: 3 A  
 Insulation resistance: 1000 MΩ min.  
 Contact resistance: 20 mΩ max.  
 Dielectric voltage: 1000 V AC  
 Operation temperature: -40 °C to +105 °C

**MATERIAL:**






Housing: PBT UL94V-0  
 Contacts: Copper alloy

**HANDLING:**

Processing: Wave soldering  
 Packing: Tray

**TOLERANCE:**

.X ± 0.25  
 .XX ± 0.20



**Order-Information**

Identifier:	No. of contacts:	Contact Plating:	Height:	Insulator Material:
FME25D	#	#	#	L
Female Header Pitch 2.54 mm double row, straight, elevated	4: 2 x 2 6: 2 x 3 8: 2 x 4 : 80: 2 x 40	G: Gold Flash * R: 3 μ" Gold A: 5 μ" Gold B: 10 μ" Gold K: 15 μ" Gold D: 30 μ" Gold Z: Selective	A: A=11.0 B=2.30 * F: A=13.50 B=2.70 G: A=16.1 B=2.30 H: A=16.1 B=7.10 I: A=18.6 B=4.60	L: PBT

\* = standard